




**74V1G384**

## SINGLE HIGH SPEED BUS SWITCH

- HIGH SPEED:  $t_{PD} = 0.5ns$  (TYP.) at  $V_{CC} = 5V$
- LOW POWER DISSIPATION:  
 $I_{CC} = 1\mu A$  (MAX.) at  $T_A = 25^\circ C$
- LOW "ON" RESISTANCE at  $V_{CC} = 5.0V$ :  
 $R_{ON} = 7\Omega$  (TYP),  $V_{IN} = 0V$ ,  $I_{I/O} = 30mA$   
 $R_{ON} = 14\Omega$  (TYP),  $V_{IN} = 2.4V$ ,  $I_{I/O} = 15mA$
- OPERATING VOLTAGE RANGE:  
 $V_{CC}$  (OPR.) = 3.0V TO 5.5V
- 5V TOLERANT ON CONTROL PIN
- HIGH NOISE IMMUNITY:  
 $V_{NIH} = V_{NIL} = 28\% V_{CC}$  (MIN.)

### DESCRIPTION

The 74V1G384 is an advanced high-speed CMOS SINGLE HIGH SPEED BUS SWITCH fabricated in silicon gate C<sup>2</sup>MOS technology. It's designed to operate from 3V to 5.5V, making this device ideal for portable applications. It's offers 7Ω Resistance typical value at  $V_{CC} = 5V$ . Additional key feature are fast switching speed ( $t_{ON} = 3.8ns$ ,  $t_{OFF} = 3.3ns$  Typical) and Low Power Consumption.




### ORDER CODES

| PACKAGE  | T & R       |
|----------|-------------|
| SOT23-5L | 74V1G384STR |
| SC70-5L  | 74V1G384CTR |

The  $\overline{OE}$  input is provided to control the switch; the switch is ON when the  $\overline{OE}$  input is held low and OFF when  $\overline{OE}$  is held high.

It's available in the commercial and extended temperature range in SOT23-5L and SC-70-5L package.

### PIN CONNECTION AND IEC LOGIC SYMBOLS



\* High Impedance State

Absolute Maximum Ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied.

1)  $V_{IN}$  from 30% to 70% of  $V_{CC}$  on control pin

## DC SPECIFICATIONS

| Symbol           | Parameter                                 | Test Condition         |                                                                                                                           | Value                 |      |                    |                    |                    |                    | Unit               |      |
|------------------|-------------------------------------------|------------------------|---------------------------------------------------------------------------------------------------------------------------|-----------------------|------|--------------------|--------------------|--------------------|--------------------|--------------------|------|
|                  |                                           | V <sub>CC</sub><br>(V) |                                                                                                                           | T <sub>A</sub> = 25°C |      |                    | -40 to 85°C        |                    | -55 to 125°C       |                    |      |
|                  |                                           |                        |                                                                                                                           | Min.                  | Typ. | Max.               | Min.               | Max.               | Min.               |                    | Max. |
| V <sub>IH</sub>  | High Level Input Voltage                  | 2.0                    |                                                                                                                           | 1.5                   |      |                    | 1.5                |                    | 1.5                |                    | V    |
|                  |                                           | 3.0 to 5.5             |                                                                                                                           | 0.7V <sub>CC</sub>    |      |                    | 0.7V <sub>CC</sub> |                    | 0.7V <sub>CC</sub> |                    |      |
| V <sub>IL</sub>  | Low Level Input Voltage                   | 2.0                    |                                                                                                                           |                       |      | 0.5                |                    | 0.5                |                    | 0.5                | V    |
|                  |                                           | 3.0 to 5.5             |                                                                                                                           |                       |      | 0.3V <sub>CC</sub> |                    | 0.3V <sub>CC</sub> |                    | 0.3V <sub>CC</sub> |      |
| R <sub>ON</sub>  | ON Resistance                             | 3.0                    | V <sub>IC</sub> = V <sub>IL</sub><br>V <sub>I/O</sub> = GND<br>I <sub>I/O</sub> ≤ 30 mA                                   |                       | 9    |                    |                    | 13                 |                    | 20                 | Ω    |
|                  |                                           | 4.5                    | V <sub>IC</sub> = V <sub>IL</sub><br>V <sub>I/O</sub> = GND<br>I <sub>I/O</sub> ≤ 30 mA                                   |                       | 7    |                    |                    | 10                 |                    | 15                 | Ω    |
| R <sub>ON</sub>  | ON Resistance                             | 3.0                    | V <sub>IC</sub> = V <sub>IL</sub><br>V <sub>I/O</sub> = 1.5V<br>I <sub>I/O</sub> ≤ 15 mA                                  |                       | 20   |                    |                    | 40                 |                    | 60                 | Ω    |
|                  |                                           | 4.5                    | V <sub>IC</sub> = V <sub>IL</sub><br>V <sub>I/O</sub> = 2.4V<br>I <sub>I/O</sub> ≤ 15 mA                                  |                       | 14   |                    |                    | 28                 |                    | 40                 | Ω    |
| I <sub>OFF</sub> | Input/Output Leakage Current (SWITCH OFF) | 5.5                    | V <sub>OS</sub> = V <sub>CC</sub> to GND<br>V <sub>IS</sub> = V <sub>CC</sub> to GND<br>V <sub>IC</sub> = V <sub>IL</sub> |                       |      | ±0.1               |                    | ± 1                |                    | ± 10               | μA   |
| I <sub>IN</sub>  | Control Input Leakage Current             | 0 to 5.5               | V <sub>IC</sub> = 5.5V or GND                                                                                             |                       |      | ± 0.1              |                    | ± 1.0              |                    | ± 1.0              | μA   |
| I <sub>CC</sub>  | Quiescent Supply Current                  | 5.5                    | V <sub>I</sub> = V <sub>CC</sub> or GND                                                                                   |                       |      | 1                  |                    | 10                 |                    | 20                 | μA   |

AC ELECTRICAL CHARACTERISTICS (C<sub>L</sub> = 50pF, Input t<sub>r</sub> = t<sub>f</sub> = 3ns)

| Symbol                               | Parameter           | Test Condition         |                                                | Value                 |      |      |             |      |              | Unit |      |
|--------------------------------------|---------------------|------------------------|------------------------------------------------|-----------------------|------|------|-------------|------|--------------|------|------|
|                                      |                     | V <sub>CC</sub><br>(V) |                                                | T <sub>A</sub> = 25°C |      |      | -40 to 85°C |      | -55 to 125°C |      |      |
|                                      |                     |                        |                                                | Min.                  | Typ. | Max. | Min.        | Max. | Min.         |      | Max. |
| t <sub>PD</sub>                      | Delay Time          | 3.3 <sup>(*)</sup>     | t <sub>r</sub> = t <sub>f</sub> = 6ns          |                       | 0.8  | 1.2  |             | 1.5  |              | 2.0  | ns   |
|                                      |                     | 5.0 <sup>(**)</sup>    | t <sub>r</sub> = t <sub>f</sub> = 6ns          |                       | 0.5  | 0.8  |             | 1.0  |              | 1.5  |      |
| t <sub>PLZ</sub><br>t <sub>PHZ</sub> | Output Disable Time | 3.3 <sup>(*)</sup>     | R <sub>1</sub> = 500Ω<br>V <sub>IN</sub> =1.5V |                       | 8.5  | 12.0 |             | 14.0 |              | 16.0 | ns   |
|                                      |                     | 5.0 <sup>(**)</sup>    | R <sub>1</sub> = 500Ω<br>V <sub>IN</sub> =2.4V |                       | 3.8  | 6.5  |             | 9.0  |              | 10.0 |      |
| t <sub>PZL</sub><br>t <sub>PZH</sub> | Output Enable Time  | 3.3 <sup>(*)</sup>     | R <sub>1</sub> = 1KΩ<br>V <sub>IN</sub> =1.5V  |                       | 7.3  | 12.0 |             | 14.0 |              | 16.0 | ns   |
|                                      |                     | 5.0 <sup>(**)</sup>    | R <sub>1</sub> = 1KΩ<br>V <sub>IN</sub> =2.4V  |                       | 3.3  | 5.0  |             | 7.5  |              | 8.5  |      |

(\*) Voltage range is 3.3V ± 0.3V

(\*\*) Voltage range is 5.0V ± 0.5V


## CAPACITIVE CHARACTERISTICS

| Symbol           | Parameter                              | Test Condition         |  | Value                 |      |      |             |      |              | Unit |      |
|------------------|----------------------------------------|------------------------|--|-----------------------|------|------|-------------|------|--------------|------|------|
|                  |                                        | V <sub>CC</sub><br>(V) |  | T <sub>A</sub> = 25°C |      |      | -40 to 85°C |      | -55 to 125°C |      |      |
|                  |                                        |                        |  | Min.                  | Typ. | Max. | Min.        | Max. | Min.         |      | Max. |
| C <sub>IN</sub>  | Input Capacitance                      |                        |  |                       | 4    | 10   |             | 10   |              | 10   | pF   |
| C <sub>I/O</sub> | Output Capacitance                     |                        |  |                       | 7    |      |             |      |              |      | pF   |
| C <sub>PD</sub>  | Power Dissipation Capacitance (note 1) | 3.3                    |  |                       | 2.5  |      |             |      |              |      | pF   |
|                  |                                        | 5.0                    |  |                       | 3    |      |             |      |              |      |      |

1) C<sub>PD</sub> is defined as the value of the IC's internal equivalent capacitance which is calculated from the operating current consumption without load. (Refer to Test Circuit). Average operating current can be obtained by the following equation.  $I_{CC(opr)} = C_{PD} \times V_{CC} \times f_{IN} + I_{CC}$

## SOT23-5L MECHANICAL DATA


| DIM. | mm.  |      |      | mils  |      |       |
|------|------|------|------|-------|------|-------|
|      | MIN. | TYP  | MAX. | MIN.  | TYP. | MAX.  |
| A    | 0.90 |      | 1.45 | 35.4  |      | 57.1  |
| A1   | 0.00 |      | 0.10 | 0.0   |      | 3.9   |
| A2   | 0.90 |      | 1.30 | 35.4  |      | 51.2  |
| b    | 0.35 |      | 0.50 | 13.7  |      | 19.7  |
| C    | 0.09 |      | 0.20 | 3.5   |      | 7.8   |
| D    | 2.80 |      | 3.00 | 110.2 |      | 118.1 |
| E    | 1.50 |      | 1.75 | 59.0  |      | 68.8  |
| e    |      | 0.95 |      |       | 37.4 |       |
| H    | 2.60 |      | 3.00 | 102.3 |      | 118.1 |
| L    | 0.10 |      | 0.60 | 3.9   |      | 23.6  |



7049676C


## SOT323-5L MECHANICAL DATA

| DIM. | mm.  |      |      | mils |      |      |
|------|------|------|------|------|------|------|
|      | MIN. | TYP  | MAX. | MIN. | TYP. | MAX. |
| A    | 0.80 |      | 1.10 | 31.5 |      | 43.3 |
| A1   | 0.00 |      | 0.10 | 0.0  |      | 3.9  |
| A2   | 0.80 |      | 1.00 | 31.5 |      | 39.4 |
| b    | 0.15 |      | 0.30 | 5.9  |      | 11.8 |
| C    | 0.10 |      | 0.18 | 3.9  |      | 7.1  |
| D    | 1.80 |      | 2.20 | 70.9 |      | 86.6 |
| E    | 1.80 |      | 2.40 | 70.9 |      | 94.5 |
| E1   | 1.15 |      | 1.35 | 45.3 |      | 53.1 |
| e    |      | 0.65 |      |      | 25.6 |      |
| e1   |      | 1.3  |      |      | 51.2 |      |
| L    | 0.10 |      | 0.30 | 3.9  |      | 11.8 |




## Tape &amp; Reel SOT23-xL MECHANICAL DATA

| DIM. | mm.  |      |      | inch  |       |       |
|------|------|------|------|-------|-------|-------|
|      | MIN. | TYP  | MAX. | MIN.  | TYP.  | MAX.  |
| A    |      |      | 180  |       |       | 7.086 |
| C    | 12.8 | 13.0 | 13.2 | 0.504 | 0.512 | 0.519 |
| D    | 20.2 |      |      | 0.795 |       |       |
| N    | 60   |      |      | 2.362 |       |       |
| T    |      |      | 14.4 |       |       | 0.567 |
| Ao   | 3.13 | 3.23 | 3.33 | 0.123 | 0.127 | 0.131 |
| Bo   | 3.07 | 3.17 | 3.27 | 0.120 | 0.124 | 0.128 |
| Ko   | 1.27 | 1.37 | 1.47 | 0.050 | 0.054 | 0.058 |
| Po   | 3.9  | 4.0  | 4.1  | 0.153 | 0.157 | 0.161 |
| P    | 3.9  | 4.0  | 4.1  | 0.153 | 0.157 | 0.161 |



## Tape &amp; Reel SOT323-xL MECHANICAL DATA

| DIM. | mm.  |      |      | inch  |       |       |
|------|------|------|------|-------|-------|-------|
|      | MIN. | TYP  | MAX. | MIN.  | TYP.  | MAX.  |
| A    | 175  | 180  | 185  | 6.889 | 7.086 | 7.283 |
| C    | 12.8 | 13   | 13.2 | 0.504 | 0.512 | 0.519 |
| D    | 20.2 |      |      | 0.795 |       |       |
| N    | 59.5 | 60   | 60.5 |       | 2.362 |       |
| T    |      |      | 14.4 |       |       | 0.567 |
| Ao   |      | 2.25 |      |       | 0.088 |       |
| Bo   |      | 2.7  |      |       | 0.106 |       |
| Ko   |      | 1.2  |      |       | 0.047 |       |
| Po   | 3.9  | 4    | 4.1  | 0.153 | 0.157 | 0.161 |
| P    | 3.8  | 4    | 4.2  | 0.149 | 0.157 | 0.165 |





Obsolete Product(s) - Obsolete Product(s)

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a registered trademark of STMicroelectronics  
All other names are the property of their respective owners

© 2004 STMicroelectronics - All Rights Reserved  
STMicroelectronics GROUP OF COMPANIES

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -  
Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States.  
<http://www.st.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[74V1G384STR](#) [74V1G384CTR](#)