

25U 2-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: **SR2POST25**



Highlights

- 25U 2-post open frame rack
- Black aluminum with round threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR2POST25
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual

Description

Tripp Lite's SR2POST25 2-Post SmartRack Open Frame Rack is an economical way to accommodate 25U of rack space for 19-inch rackmount applications in limited spaces that do not require a lockable enclosure. Its heavy-duty, aluminum construction can safely support 800 lbs. of rackmount equipment, and its open design provides easy access to equipment and cabling. The black, textured powder coat finish makes it resistant to scratching while giving it a "classic," attractive appearance. The SR2POST25 is easy to install due to a self-squaring design combined with numbered mounting positions and bolt down provisions. It uses toolless button-hole mounting for vertical PDUs and cable managers. In high-density environments, multiple units can be bolted together side by side for easy expansion or customization. The SR2POST25 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100, DIN 41494 and RoHS, and is backed by a 5-year warranty.

Features

- Supports 800lbs of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

| SELECTOR | |
|---------------|----------------|
| Selector Type | RACK EQUIPMENT |
| General Info | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|---|---|
| Product Group | RACKS |
| TAA Compliant | No |
| OVERVIEW | |
| Style | 2-Post |
| Rack Type | Open-Frame |
| PHYSICAL | |
| Installed Whole System Maximum Rack Depth (in.) | 4.8 |
| Installed Whole System Maximum Rack Depth (cm) | 12.19 |
| Rack Height (U Spaces) | 25 |
| Shipping Dimensions (hwd / in.) | 7 x 3 x 49 |
| Shipping Dimensions (hwd / cm) | 17.78 x 7.62 x 124.46 |
| Shipping Weight (lbs.) | 24 |
| Shipping Weight (kg) | 10.89 |
| Unit Dimensions (hwd / in.) | 49 x 20.3 x 4.75 |
| Unit Weight (lbs.) | 23 |
| Unit Weight (kg) | 10.43 |
| Unit Dimensions (cm) | 124.46 x 51.56 x 12.07 |
| Color | Black |
| Weight Capacity - Stationary (lbs.) | 800 |
| Weight Capacity - Stationary (kg) | 362.9 |
| CERTIFICATIONS | |
| NOM (Mexico) | Tested to NOM (Mexico) |
| Approvals | EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.