


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0592335201
Status: Obsolete
Description: 2.00mm (.079") and 0.80mm (.031") Pitch IEEE 1394-1995 IEEE/P1394a Shielded I/O Cable Assembly Plug; 6-4 Pin Harness, Gray, 2.0m (6.56') Length, (S400)

Documents:
[Drawing \(PDF\)](#)

Agency Certification	
CSA	LR19980
General	
Product Family	Cable Assemblies
Series	59233
Connector to Connector	IEEE 1394-1995-to-IEEE P1394a
Product Name	IEEE 1394
Physical	
Cable Length	2.0m (6.56')
Circuits (Loaded)	6 TO 4
Color - Resin	Black, Gray
Flammability	94V-0
Gender	Male-Male
Lock to Mating Part	None
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold, Tin
Material - Plating Termination	Tin, Tin-Lead
Material - Resin	High Temperature Thermoplastic, Polyester, PVC
Packaging Type	Bag
Pitch - Mating Interface	0.80mm (.031"), 2.00mm (.079")
Plating min - Mating	0.762µm (30µ"), 0.889µm (35µ")
Plating min - Termination	0.889µm (35µ"), 1.016µm (40µ"), 3.048µm (120µ")
Single Ended	No
Termination Interface: Style	Crimp or Compression, Surface Mount
Wire Insulation Diameter	0.68mm (.027") max.
Wire Size AWG	32
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	40V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-59233-52**



EU RoHS	China RoHS
Compliance Status	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
59233Series

Mates With
54516 , 54642 , 54775 , 53984 , 53462 , 53460 , 54818 , 54030

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION