

LOW CAPACITANCE TVS ARRAY

APPLICATIONS

- ✓ Ethernet - 10/100 Base T
- ✓ FireWire
- ✓ SCSI
- ✓ Bluetooth & RF

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns
- ✓ 61000-4-5 (Surge): 24A, 8/20 μ s - Level 2(Line-Gnd) & Level 3(Line-Line)

FEATURES


- ✓ 500 Watts Peak Pulse Power per Line ($t_p=8/20\mu$ s)
- ✓ Bidirectional Configuration
- ✓ Available in 4 Voltage Types: 3.3V to 15V
- ✓ Protects Up to Six (6) Lines
- ✓ ESD Protection > 40 kilovolts
- ✓ **LOW CAPACITANCE: 8pF**

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SO-8 Package
- ✓ Weight 15 milligrams (Approximate)
- ✓ Flammability rating UL 94V-0
- ✓ 12mm Tape and Reel Per EIA Standard 481
- ✓ Marking: Logo, Marking Code, Date Code & Pin One Defined By Dot on Top of Package



PIN CONFIGURATION





DEVICE CHARACTERISTICS






MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	500	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE	MINIMUM BREAKDOWN VOLTAGE	MAXIMUM CLAMPING VOLTAGE (See Fig. 2)	MAXIMUM CLAMPING VOLTAGE (See Fig. 2)	MAXIMUM LEAKAGE CURRENT	TYPICAL CAPACITANCE (See Note 1)
		V_{WM} VOLTS	@ 1mA $V_{(BR)}$ VOLTS	@ $I_p = 1A$ V_C VOLTS	@ 8/20 μs V_C @ I_{PP}	@ V_{WM} I_D μA	0V @ 1 MHz C pF
PLCDA03C-6	PRS	3.3	4.5	7.0	10.9V @ 43.0A	125	8
PLCDA05C-6	PRT	5.0	6.0	9.8	13.5V @ 42.0A	20	8
PLCDA08C-6	PRW	8.0	8.5	13.4	16.9V @ 34.0A	10	8
PLCDA15C-6	PRU	15.0	16.7	22.0	30.0V @ 17.0A	2	8

Note 1: Capacitance between I/O pins and ground (pins 4 & 5) is typically 8pF. Capacitance between I/O pins is typically 4 pF.



GRAPHS



APPLICATION NOTE

The PLCDAxxC-6 Series are low capacitance, bidirectional TVS arrays that are designed to protect I/O or high speed data lines from the damaging effects of ESD or EFT. This product series has a surge capability of 500 Watts P_{PP} per line for an 8/20 μ s waveshape and offers ESD protection > 40kv.

BIDIRECTIONAL COMMON-MODE CONFIGURATION (Figure 1)

Ideal for use multimode transceiver I/O lines, the PLCDAxxC-6 Series provides up to six (6) lines of protection in a common-mode configuration as depicted in Figure 1.

Circuit connectivity is as follows:

- ✓ Line 1 is connected to Pin 1.
- ✓ Line 2 is connected to Pin 2.
- ✓ Line 3 is connected to Pin 3.
- ✓ Line 4 is connected to Pin 8.
- ✓ Line 5 is connected to Pin 7.
- ✓ Line 6 is connected to Pin 6.
- ✓ Pins 4 and 5 are connected to Ground.

BIDIRECTIONAL COMMON-MODE CONFIGURATION (Figure 2)

The PLCDAxxC-6 Series also provides video line applications six (6) lines of protection in a common-mode configuration as depicted in Figure 2.

Circuit connectivity is as follows:

- ✓ Line 1 (Red) is connected to Pin 1.
- ✓ Line 2 (Green) is connected to Pin 2.
- ✓ Line 3 (Blue) is connected to Pin 3.
- ✓ Line 4 (VSYNC) is connected to Pin 6.
- ✓ Line 5 (HSYNC) is connected to Pin 7.
- ✓ Pins 4 and 5 are connected to Ground.

CIRCUIT BOARD LAYOUT RECOMMENDATIONS

Circuit board layout is critical for Electromagnetic Compatibility (EMC) protection. The following guidelines are recommended:

- ✓ The protection device should be placed near the input terminals or connectors, the device will divert the transient current immediately before it can be coupled into the nearby traces.
- ✓ The path length between the TVS device and the protected line should be minimized.
- ✓ All conductive loops including power and ground loops should be minimized.
- ✓ The transient current return path to ground should be kept as short as possible to reduce parasitic inductance.
- ✓ Ground planes should be used whenever possible. For multilayer PCBs, use ground vias.

Figure 1: Typical Transceiver Protection Circuit






Figure 2: Typical Video Line Protection Circuit



PACKAGE OUTLINE & DIMENSIONS



COPYRIGHT © ProTek Devices 2003
SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.

ProTek Devices
2929 South Fair Lane, Tempe, AZ 85282
Tel: 602-431-8101 Fax: 602-431-2288
E-Mail: sales@protekdevices.com
Web Site: www.protekdevices.com