




PRODUCT NUMBER
73305-XXXLF

PLATING OPTION
1= GXT 0.76 μm
3= GOLD 0.76 μm
5= GOLD 1.27 μm

PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG

TERMINAL LOADING
1= FULLY LOADED
2= POS 2,3,4,5
3= POS 1,2,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.



REFERENCE PLAN
DEFINED BY THE
2 HOLD DOWN
BEARING SURFACE

NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.


c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004

- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.

VIEW ACCORDING "V"








SEE NOTE 3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		MOD JACK
ltr	ecn no	dr	date	title
H	F06-0240	DLE	06.07.18	SMT RA JACK
J	F09-0070	LSA	09.07.23	6 POS OUTSIDE
K	B-15798	JFA	13.09.09	
L	F-21888	AMA	15.09.09	
		dr	D LEGRAND	04.10.18
		enr	P NIZZI	04.10.18
F	F04-0363	DLE	04.10.18	
G	F05-0247	DLE	05.09.12	
		chr	D LEGRAND	04.10.18
		appd	P.NZ	04.10.18
sheet	revision	L	E	B
index	sheet	1	2	3

PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		MOD-JACK
ltr	ecn no	dr	date	title
D	F80620	DLE	98.11.26	SMT RA JACK
E	F06-024Q	DLE	06.07.18	6 POS. OUTSIDE
			angles	linear
			dr	D LEGRAND 06.07.18
			enr	P NIZZI 06.07.18
			chr	D LE 06.07.18
			appd	P NZ 06.07.18
sheet	revision			
index	sheet			




dwg no	73305	sheet 2 of 3	size
			A3
type	CUSTOMER Drawing		



FCIconnect.com

Copyright FCI



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family MOD JACK	
ltr		ecn no		dr		date		title	
A		F04-0363		DLE		04.10.18		SMT RA JACK	
B		F06-0240		DLE		06.07.18		6 POS OUTSIDE	
				angles		linear		scale 2:1	
				±2°					
				dr		D LEGRAND		04.10.18	
				engr		P NIZZI		04.10.18	
				chr		D LEGRAND		04.10.18	
				appd		P NZ		04.10.18	
sheet index		revision sheet						dwg no	
								73305	
								sheet 3 of - size	
								A4	
								type	
								CUSTOMER Drawing	

form: A4