


SMD Power Inductor CDRH103R




Halogen
Free



Description

- Ferrite drum core construction.
- Magnetically shielded.
- L × W × H: 10.5 × 10.3 × 3.1mm Max.
- Product weight: 1.0g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.
- Halogen Free available.

Dimension - [mm]




Environmental Data

- Operating temperature range: -40°C ~ +100°C (including coil's self temperature rise)
- Storage temperature range: -40°C ~ +100°C
- Solder reflow temperature: 260 °C peak.

Packaging

- Carrier tape and reel packaging.
- 12.9" diameter reel.
- 1000pcs per reel.

Land pattern and Schematics - [mm]



Applications

- Ideally used in Notebook PC, LCD TV, DVD, Game machine, STB, Projector etc as DC-DC converter inductors.

SMD Power Inductor

CDRH103R



Electrical Characteristics

Part Name	Stamp	Inductance (μ H) [within] ※1	D.C.R. (m Ω) Max. (Typ.) (at 20°C)	Saturation Current (A) ※2	Temperature Rise Current (A) ※3
CDRH103RNP-0R8NC-B	0R8	0.8 $\pm$ 30%	5.7(4.4)	11.2	8.30
CDRH103RNP-1R5NC-B	1R5	1.5 $\pm$ 30%	11.0(8.5)	8.0	5.80
CDRH103RNP-2R2NC-B	2R2	2.2 $\pm$ 30%	16.9(13)	6.7	5.10
CDRH103RNP-3R3NC-B	3R3	3.3 $\pm$ 30%	21.0(16)	5.56	4.70
CDRH103RNP-4R7NC-B	4R7	4.7 $\pm$ 30%	30.0(23)	4.65	4.00
CDRH103RNP-6R8NC-B	6R8	6.8 $\pm$ 30%	35.0(27)	3.84	3.60
CDRH103RNP-8R2NC-B	8R2	8.2 $\pm$ 30%	50.0(38)	3.54	3.00
CDRH103RNP-100NC-B	100	10 $\pm$ 30%	59.0(45)	3.18	2.80
CDRH103RNP-150NC-B	150	15 $\pm$ 30%	91.0(70)	2.60	2.05
CDRH103RNP-220NC-B	220	22 $\pm$ 30%	143(110)	2.16	1.60
CDRH103RNP-330NC-B	330	33 $\pm$ 30%	202(155)	1.74	1.35
CDRH103RNP-470NC-B	470	47 $\pm$ 30%	299(230)	1.43	1.20
CDRH103RNP-560NC-B	560	56 $\pm$ 30%	325(250)	1.36	1.15
CDRH103RNP-680NC-B	680	68 $\pm$ 30%	429(330)	1.22	0.95
CDRH103RNP-820NC-B	820	82 $\pm$ 30%	494(380)	1.14	0.80
CDRH103RNP-101NC-B	101	100 $\pm$ 30%	683(525)	1.02	0.70
CDRH103RNP-121NC-B	121	120 $\pm$ 30%	754(580)	0.89	0.65
CDRH103RNP-151NC-B	151	150 $\pm$ 30%	871(670)	0.84	0.51

※1 Inductance measuring condition: at 100kHz.


※2 The saturation current: This indicates the value of DC current when the inductance decreases to 65% of it's nominal.

※3 The temperature rise: The value of DC current when the temperature rise is $\Delta T=40^{\circ}\text{C}$ ($T_a=20^{\circ}\text{C}$).







SMD Power Inductor CDRH103R





Saturation Current & Temperature Rise Graph



SMD Power Inductor CDRH103R



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong
Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com
Saitama(Japan)
Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com
Chicago
Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai
Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com
Seoul
Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com
Obernzell
Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen
Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com
Singapore
Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com
Neumarkt
Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei
Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com
San Jose
Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com