

CMMR1 SERIES
SURFACE MOUNT
GENERAL PURPOSE
SILICON RECTIFIER
1.0 AMP, 200 THRU 1000 VOLTS



SOD-123F CASE

CentralTM

Semiconductor Corp.

DESCRIPTION:

The Central Semiconductor CMMR1 Series of High Current Density Rectifiers, in a SOD-123F surface mount package are designed for all types of commercial, industrial computer and automotive applications.

MARKING CODES:

CMMR1-02: C02F
CMMR1-04: C04F
CMMR1-06: C06F
CMMR1-10: C10F


MAXIMUM RATINGS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

	SYMBOL	CMMR1 <u>-02</u>	CMMR1 <u>-04</u>	CMMR1 <u>-06</u>	CMMR1 <u>-10</u>	UNITS
Peak Repetitive Reverse Voltage	V_{RRM}	200	400	600	1000	V
DC Blocking Voltage	V_R	200	400	600	1000	V
RMS Reverse Voltage	$V_{R(RMS)}$	140	280	420	700	V
Average Forward Current ($T_L=75^{\circ}\text{C}$)	I_O			1.0		A
Peak Forward Surge Current (8.3ms)	I_{FSM}			30		A
Operating and Storage						
Junction Temperature	T_J, T_{stg}		-65 to +150			$^{\circ}\text{C}$
Typical Thermal resistance	θ_{JA}		65			$^{\circ}\text{C/W}$

ELECTRICAL CHARACTERISTICS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNITS
V_F	$I_F=1.0\text{A}$			1.1	V
I_R	$V_R=\text{Rated } V_{RRM}$			10	μA
I_R	$V_R=\text{Rated } V_{RRM}; T_A=125^{\circ}\text{C}$			50	μA
C_J	$V_R=4.0\text{V}, f=1.0\text{MHz}$		4.0		pF

SOD-123F CASE - MECHANICAL OUTLINE



DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.035	0.043	0.88	1.08
B	0.020	0.031	0.50	0.80
C	0.004	0.008	0.10	0.20
D	0.065	0.077	1.65	1.95
E	0.104	0.116	2.65	2.95
F	0.140	0.156	3.55	3.95
G	0.030	0.041	0.75	1.05

SOD-123F (REV:R1)

MARKING CODE

DEVICE	MARKING CODE
CMMR1-02	C02F
CMMR1-04	C04F
CMMR1-06	C06F
CMMR1-10	C10F

LEAD CODE:

- 1) CATHODE
- 2) ANODE