





REVISIONS				
REV.	ECO. NO	DESCRIPTION	DATE	BY
F	3177	UPDATE DWG FORMAT, UPDATE INSERT INSTALLATION IN 'V' MOUNTING	3/10/2015	MG
H	3182	UPDATE GAP FROM PIN TO BODY TO .050 FROM .030	4/23/2015	MG
J	3613	ADD S2196, REMOVE 'A' MATERIAL, ADD 'Q' MATERIAL, UPDATE 'R' MATERIAL OPERATING TEMPERATURE, REMOVE 'Y' & 'S' PLATING	2/2/2017	EP


- NOTES:
1. INSULATOR MATERIAL: SEE PART NUMBER CODING
 2. CONTACT MATERIAL: SEE PART NUMBER CODING
 3. PLATING: SEE PART NUMBER CODING
 4. OPERATING TEMPERATURE: SEE PART NUMBER CODING
 5. PROCESSING TEMP: SEE PART NUMBER CODING
 6. UL FLAMMABILITY RATING: 94V-0
 7. OPERATION VOLTAGE: 700 VAC
 8. CURRENT RATING: 3 AMP
 9. CONTACT RESISTANCE: 30 MILLI OHMS MAX
 10. INSULATION RESISTANCE: 5000 MEGA OHMS
 11. CONNECTOR IDENTIFICATION: PART SHALL BE MARKED WITH A PART NUMBER AND LOT CODE
 12. MODIFICATION: SEE PART NUMBER CODING

RECOMMENDED PCB LAYOUT


CUSTOMER COPY



UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM]		DRAWN	DATE	NAME		
			02/05/08	MNH		
TOLERANCES: ANGULAR: $\pm 1^{\circ}$ DECIMALS XX = $\pm .02$ [.5] .XXX = $\pm .005$ [.13] .XXXX = $\pm .0005$ [.013]		THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.			TITLE MALE, RIGHT ANGLE BEND, .100 CC	
					PART NUMBER __C__M__(MA,MV,MB,MD,MJ,MK)_(S189,S2196)	
		SIZE	CAGE CODE	DWG. NO.	REV	
		C	54453	C11052	J	
		SCALE: 4:1		SHEET 1 OF 3		



CUSTOMER COPY



RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM]		DRAWN	DATE	NAME		
TOLERANCES:			02/05/08	MNH		
ANGULAR: $\pm 1^\circ$		THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.			TITLE MALE, RIGHT ANGLE BEND, .100 CC	
DECIMALS XX= $\pm .02 [.5]$.XXX= $\pm .005 [.13]$.XXXX= $\pm .0005 [.013]$					PART NUMBER __C__M__(MA,MV,MB,MD,MJ,MK)_(S189,S2196)	
					SIZE C	CAGE CODE 54453
					DWG. NO. C11052	
					REV J	
					SCALE: 3:1	
					SHEET 2 OF 3	

