

8 PIN DIP 400 V BREAKDOWN VOLTAGE 2-CH OPTICAL COUPLED MOSFET

PS7141-2A
PS7141L-2A

FEATURES

- **2 CHANNEL TYPE:**
(1a + 1a output)
- **DESIGNED FOR AC/DC SWITCHING LINE CHANGER**
- **SMALL PACKAGE:**
8 pin DIP
- **LOW OFFSET VOLTAGE**
- **LOW LED OPERATING CURRENT:**
($I_F = 2 \text{ mA}$)
- **SURFACE MOUNT AVAILABLE:**
PS7141-2A

DESCRIPTION

PS7141-2A and PS7141L-2A are solid state relays containing GaAs LEDs on the light emitting side (input side) and MOSFETs on the output side. They are suitable for analog signal control because of their low offset and high linearity.

APPLICATIONS



- EXCHANGE EQUIPMENT
- MEASUREMENT EQUIPMENT
- FA/OA EQUIPMENT

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$)


PART NUMBER				PS7141-2A, PS7141L-2A		
SYMBOLS		PARAMETERS	UNITS	MIN	TYP	MAX
Diode	V_F	Forward Voltage, $I_F = 10 \text{ mA}$	V		1.2	1.4
	I_R	Reverse Current, $V_R = 5 \text{ V}$	μA			5.0
MOS FET	I_{LOFF}	Off-State Leakage Current, $V_D = 400 \text{ V}$	μA		0.03	1.0
	C_{OUT}	Output Capacitance, $V_D = 0 \text{ V}$, $f = 1 \text{ MHz}$	pF/ch		65	
Coupled	I_{Fon}	LED On-state Current, $I_L = 150 \text{ mA}$	mA			2.0
	R_{on1} R_{on2}	On-State Resistance, $I_F = 10 \text{ mA}$, $I_L = 10 \text{ mA}$ $I_F = 10 \text{ mA}$, $I_L = 150 \text{ mA}$, $t \leq 10 \text{ ms}$	Ω		20	30
					16	25
	t_{ON}	Turn-on Time ¹	ms		0.35	1.0
	t_{OFF}	Turn-off Time ¹			0.06	0.2
	$R_{\text{I-O}}$	Isolation Resistance, $V_{\text{I-O}} = 1.0 \text{ kV}$	Ω	10^9		
	$C_{\text{I-O}}$	Isolation Capacitance, $V = 0 \text{ V}$, $f = 1 \text{ MHz}$	pF/ch		1.1	

Note:

1. Test Circuit for Switching Time:









PS7141-2A, PS7141L-2A




1. LED Anode1
2. LED Cathode1
3. LED Anode2
4. LED Cathode2
5. MOSFET 2
6. MOSFET 2
7. MOSFET 1
8. MOSFET 1

TYPICAL PERFORMANCE CURVES (T_A = 25 °C)




TYPICAL PERFORMANCE CURVES (T_A = 25 °C)


NORMALIZED ON-STATE RESISTANCE
vs. AMBIENT TEMPERATURE




ON-STATE DISTRIBUTION




TURN-ON TIME
vs. FORWARD CURRENT




TURN-OFF TIME
vs. FORWARD CURRENT





TURN-ON TIME DISTRIBUTION



TURN-OFF TIME DISTRIBUTION




TYPICAL PERFORMANCE CURVES (TA = 25 °C)




TAPING SPECIFICATIONS (Units in mm)


OUTLINE AND DIMENSIONS (TAPE)



TAPING DIRECTION



OUTLINE AND DIMENSIONS (REEL)




Notes:
1. Packaging : 1000 pcs/reel

RECOMMENDED SOLDERING CONDITIONS

(1) Infrared reflow soldering

- Peak reflow temperature 235 °C or below (package surface temperature)
- Time of temperature higher than 210 °C 30 seconds or less
- Number of reflows Two
- Flux Rosin flux containing small amount of chlorine
(The flux with a maximum chlorine content of 0.2 Wt % is recommended.)

Recommended Temperature Profile of Infrared Reflow



(2) Dip soldering

- Temperature 260 °C or below (molten solder temperature)
- Time 10 seconds or less
- Number of times One
- Flux Rosin flux containing small amount of chlorine
(The flux with a maximum chlorine content of 0.2 Wt % is recommended.)

(3) Cautions

- Fluxes
Avoid removing the residual flux with freon-based cleaning solvent.

Life Support Applications

These NEC products are not intended for use in life support devices, appliances, or systems where the malfunction of these products can reasonably be expected to result in personal injury. The customers of CEL using or selling these products for use in such applications do so at their own risk and agree to fully indemnify CEL for all damages resulting from such improper use or sale.

EXCLUSIVE NORTH AMERICAN AGENT FOR NEC RF, MICROWAVE & OPTOELECTRONIC SEMICONDUCTORS



CALIFORNIA EASTERN LABORATORIES • Headquarters • 4590 Patrick Henry Drive • Santa Clara, CA 95054-1817 • (408) 988-3500 • Telex 34-6393 • FAX (408) 988-0279
DATA SUBJECT TO CHANGE WITHOUT NOTICE Internet: <http://WWW.CEL.COM>

10/30/2001