


## Ring Lug Terminal Blocks ST5, ST5-16mm<sup>2</sup>, ST6 and ST25



Weidmuller's comprehensive range of bolt-type screw terminals offers secure connections for all power transmission applications. Bolt-type screw terminals with threads from M3.5 to M5 can be used depending on the conductor cross-section.

- Touch-safe (Premium line)
- Self-locking nut
- Combi-foot for use with TS 35 and TS 32
- CSA / UL approved
- Standard screw or test sleeve
- High Voltage Capacity

### Weidmuller, Canada

10 Spy Court  
Markham, Ontario L3R 5H6  
Telephone: (800) 268-4080  
Facsimile: (877) 300-5635  
Email: [info1@weidmuller.ca](mailto:info1@weidmuller.ca)  
Website: [www.weidmuller.ca](http://www.weidmuller.ca)

### Weidmuller, Mexico


Blvd. Hermanos Serdán 698  
Col. San Rafael Oriente  
Puebla, Puebla, Mexico  
C.P. 72029  
Telephone: 01 222 2686267  
Facsimile: 01 222 2686219  
Email: [clientes@weidmuller.com.mx](mailto:clientes@weidmuller.com.mx)  
Website: [www.weidmuller.com.mx](http://www.weidmuller.com.mx)

### Weidmuller, United States


821 Southlake Blvd.  
Richmond, Virginia 23236  
Telephone: (800) 849-9343  
Facsimile: (804) 379-2593  
Email: [info@weidmuller.com](mailto:info@weidmuller.com)  
Website: [www.weidmuller.com](http://www.weidmuller.com)

# Ring Lug Terminal Blocks

# Premium Line ("New" Touch-Safe)




**ST5 N / EN**  
Feed through



**Self-locking Nut**

10.2 / 0.402

**ST5PN / EN**  
Feed through



**Self-locking Nut**

13.2 / 0.519




|                                      |                            |             |                            |            |
|--------------------------------------|----------------------------|-------------|----------------------------|------------|
| Width (mm / Inch)                    | PA ( V0 )                  |             | PA ( V0 )                  |            |
| Insulating material ( UL94 )         |                            |             |                            |            |
| <b>Rated data</b>                    | <b>IEC/DIN-VDE</b>         |             | <b>IEC/DIN-VDE</b>         |            |
| Voltage                              | 800 V                      | 600 V       | 800 V                      | 600 V      |
| Current                              | 35 A                       | 35 A        | 46 A                       | 46 A       |
| Cross-section                        | 4 mm²                      | 22 - 10 AWG | 6 mm²                      | 22 - 8 AWG |
| Impulse voltage                      | 8 KV                       |             | 8 KV                       |            |
| Pollution severity                   | 3                          |             | 3                          |            |
| Torque range                         | 1.0 Nm                     |             | 1.2 Nm                     |            |
| Torque range - connections           | 0.5 - 0.8 Nm               |             | 0.5 - 0.8 Nm               |            |
| (See Lug Dimensions Chart P7) Thread | M3.5                       |             | M4                         |            |
| <b>Ordering Data</b>                 |                            |             |                            |            |
| (Beige)                              | <b>Part No.</b>            |             | <b>Part No.</b>            |            |
|                                      | <b>C905234600</b> (screw)  |             | <b>C905221600</b> (screw)  |            |
| (Beige)                              | <b>Part No.</b>            |             | <b>Part No.</b>            |            |
|                                      | <b>C905381600</b> (sleeve) |             | <b>C905382600</b> (sleeve) |            |
| Disconnect* (Beige)                  |                            |             |                            |            |
| Disconnect* (Beige)                  |                            |             |                            |            |

## Accessories

| End plate                    | Width (mm/Inch) | Part No.          | Width (mm/Inch) | Part No.          |
|------------------------------|-----------------|-------------------|-----------------|-------------------|
| (Beige) AP PA                | 1.5/059         | <b>C905235600</b> | 1.5/059         | <b>C905222600</b> |
| Adapter sleeve - Pin         | Width (mm/Inch) | Part No.          | Width (mm/Inch) | Part No.          |
| STB 21.6 (Beige)             |                 | <b>Part No.</b>   |                 | <b>Part No.</b>   |
| Pin PS4                      |                 | <b>1071000000</b> |                 | <b>1071000000</b> |
|                              |                 | <b>0299600000</b> |                 | <b>0299600000</b> |
| Partition plate              | Width (mm/Inch) | Part No.          | Width (mm/Inch) | Part No.          |
| (BG) TW PA                   |                 |                   |                 |                   |
| (BG) TW HP                   |                 |                   |                 |                   |
| (BG) TW PA                   |                 |                   |                 |                   |
| TW HP - TS 32                |                 |                   |                 |                   |
| Cross-connection             | Width (mm/Inch) | Part No.          | Width (mm/Inch) | Part No.          |
| Kit                          |                 |                   |                 |                   |
| VH                           |                 |                   |                 |                   |
| Q2                           |                 | <b>C905236600</b> |                 | <b>C905223600</b> |
| Q3                           |                 | <b>C905237600</b> |                 | <b>C905224600</b> |
| Q4                           |                 | <b>C905238600</b> |                 | <b>C905225600</b> |
| Q5                           |                 |                   |                 |                   |
| Q7                           |                 |                   |                 |                   |
| Q10                          |                 | <b>C905239600</b> |                 | <b>C905226600</b> |
| Q50                          |                 |                   |                 |                   |
| QL2                          |                 |                   |                 |                   |
| QL3                          |                 |                   |                 |                   |
| QL4                          |                 |                   |                 |                   |
| QL5                          |                 |                   |                 |                   |
| QL7                          |                 |                   |                 |                   |
| QL10                         |                 |                   |                 |                   |
| QL50                         |                 |                   |                 |                   |
| Sleeve VH 13.5               |                 |                   |                 |                   |
| Kit (1 Screw + 1 Washer)     |                 |                   |                 |                   |
| Connection for short-circuit | Width (mm/Inch) | Part No.          | Width (mm/Inch) | Part No.          |
| ZQV 10/2                     |                 |                   |                 |                   |
| End brackets                 | Width (mm/Inch) | Part No.          | Width (mm/Inch) | Part No.          |
| EW35 - TS 35                 | 8.5/334         | <b>0383560000</b> | 8.5/334         | <b>0383560000</b> |
| WEW35/2 - TS 35              | 8.0/315         |                   | 8.0/315         |                   |
| EWK1 - TS 32                 | 8.5/334         | <b>0206160000</b> | 8.5/334         | <b>0206160000</b> |
| EWK2 - TS 32                 | 15.0/59         |                   | 15.0/59         |                   |
| WEW35 - TS 35                | 12.2/48         |                   | 12.2/48         |                   |
| Rails                        | Width (mm/Inch) | Part No.          | Width (mm/Inch) | Part No.          |
| TS 35 steel                  |                 | <b>0383400000</b> |                 | <b>0383400000</b> |
| TS 35 steel slotted          |                 | <b>0514500000</b> |                 | <b>0514500000</b> |
| TS 32 steel                  |                 | <b>0122800000</b> |                 | <b>0122800000</b> |

\*Quick connection, incorporated test-point, circuit disconnecting

ST6 / EN  
Feed through

Self-locking Nut

11.2 / 0.441


PA ( V0 )

| IEC/DIN-VDE       |  |
|-------------------|-----------------------------------------------------------------------------------|
| 800 V             | 600 V                                                                             |
| 41 A              | 40 A                                                                              |
| 6 mm <sup>2</sup> | 26 - 10 AWG                                                                       |
| 8 kV              |                                                                                   |
| 3                 |                                                                                   |
| 1.5 - 1.8 Nm      |                                                                                   |
| 0.5 - 0.8 Nm      |                                                                                   |
| M4                |                                                                                   |

Part No.

C904908601 (screw)

C904908600 (sleeve)

ST6 T / EN  
Test disconnect

Self-locking Nut

11.2 / 0.441


PA ( V0 )

| IEC/DIN-VDE       |  |
|-------------------|-----------------------------------------------------------------------------------|
| 800 V             | 600 V                                                                             |
| 41 A              | 40 A                                                                              |
| 6 mm <sup>2</sup> | 26 - 10 AWG                                                                       |
| 8 kV              |                                                                                   |
| 3                 |                                                                                   |
| 1.5 - 1.8 Nm      |                                                                                   |
| 0.5 - 0.8 Nm      |                                                                                   |
| M4                |                                                                                   |

Part No.

C904909601 (screw)

C904909600 (sleeve)

ST25 / EN  
Feed through

Self-locking Nut

18.2 / 0.716

PA ( V0 )

| IEC/DIN-VDE         |  |
|---------------------|-------------------------------------------------------------------------------------|
| 1000 V              | 1000 V                                                                              |
| 101 A               | 100 A                                                                               |
| 25 mm <sup>2</sup>  | 20 - 3 AWG                                                                          |
| 8 kV                |                                                                                     |
| 3                   |                                                                                     |
| 2.5 (M5) / 3.2 (M6) |                                                                                     |
| 1.2 - 1.9 Nm        |                                                                                     |
| M5 & M6             |                                                                                     |

Part No.

C905265600 (M5) (screw)

C905379600 (M5) (sleeve)

Part No.

C905264600 (M6) (screw)


C905380600 (M6) (sleeve)

| Width<br>(mm/Inch) | Part No.   | Width<br>(mm/Inch) | Part No.   | Width<br>(mm/Inch) | Part No.   |
|--------------------|------------|--------------------|------------|--------------------|------------|
| 1.0/.039           | C904910600 | 1.0/.039           | C905222600 | 1.5/.059           | C905266600 |
|                    | Part No.   |                    | Part No.   |                    | Part No.   |
|                    | 0299600000 |                    | 0299600000 |                    | 0299600000 |
| Width<br>(mm/Inch) | Part No.   | Width<br>(mm/Inch) | Part No.   | Width<br>(mm/Inch) | Part No.   |
|                    |            |                    |            |                    |            |
|                    |            |                    |            |                    |            |
|                    |            |                    |            |                    |            |
|                    | Part No.   |                    | Part No.   |                    | Part No.   |
|                    | C905064600 |                    | C905064600 |                    | C012361000 |
|                    | C905065600 |                    | C905065600 |                    | C012371000 |
|                    | C905066600 |                    | C905066600 |                    | C012381000 |
|                    |            |                    |            |                    |            |
|                    | C905067600 |                    | C905067600 |                    | C033861000 |
|                    |            |                    |            |                    |            |
|                    | C904925600 |                    | C904925600 |                    |            |
|                    | C904926600 |                    | C904926600 |                    |            |
|                    | C904927600 |                    | C904927600 |                    |            |
|                    |            |                    |            |                    |            |
|                    |            |                    |            |                    |            |
|                    | C904929600 |                    | C904929600 |                    |            |
|                    |            |                    |            |                    |            |
|                    | C904288000 |                    | C904288000 |                    |            |
|                    | C904940600 |                    | C904940600 |                    |            |
|                    | Part No.   |                    | Part No.   |                    | Part No.   |
|                    | 1739680000 |                    | 1739680000 |                    |            |
| Width<br>(mm/Inch) | Part No.   | Width<br>(mm/Inch) | Part No.   | Width<br>(mm/Inch) | Part No.   |
| 8.5/.334           |            | 8.5/.334           |            | 8.5/.334           |            |
| 8.0/.315           | 1061200000 | 8.0/.315           | 1061200000 | 8.0/.315           |            |
| 8.5/.334           |            | 8.5/.334           |            | 8.5/.334           |            |
| 15.0/.59           | 0199360000 | 15.0/.59           | 0199360000 | 15.0/.59           | 0199360000 |
| 12.2/.48           |            | 12.2/.48           |            | 12.2/.48           | 1059000000 |
|                    | Part No.   |                    | Part No.   |                    | Part No.   |
|                    | 0383400000 |                    | 0383400000 |                    | 0383400000 |
|                    | 0514500000 |                    | 0514500000 |                    | 0514500000 |
|                    | 0122800000 |                    | 0122800000 |                    | 0122800000 |

## Accessories


### Lug Dimensions Chart (Terminals DIN 46237)

| Terminal Type         | Ø    | A (Max) mm/Inch |
|-----------------------|------|-----------------|
| ST5 N / EN            | M3.5 | 8.0/.315        |
| ST5PN / EN            | M4   | 10.0/.394       |
| ST6 / EN              | M4   | 8.0/.315        |
| ST6 T / EN            | M4   | 8.0/.315        |
| ST25 V1 / EN          | M5   | 15.0/.590       |
| ST25 V1 / EN          | M6   | 15.0/.590       |
| ST25 V2 / EN          | M5   | 15.0/.590       |
| ST25 V2 / EN          | M6   | 15.0/.590       |
| ST5 16mm <sup>2</sup> | M5   | 12.0/.473       |
| ST5 / EN              | M3.5 | 8.0/.315        |
| ST5P / EN             | M4   | 10.0/.394       |
| ST5P1 V1 / EN         | M4   | 10.0/.394       |
| ST5P1 V2 / EN         | M4   | 10.0/.394       |
| ST5P1 V4 / EN         | M4   | 10.0/.394       |
| ST5P1 V5 / EN         | M5   | 12.0/.473       |



### Dekafix Preprinted Markers for Terminals

| Length x Pitch | Vertical Print | Horizontal Print |
|----------------|----------------|------------------|
|                | 5 x 5mm        | 5 x 5mm          |
|                | DEK 5/5        | DEK 5/5          |
| Model          |                |                  |
| 1-50           | 0473560001     | 0473460001       |
| 51-100         | 0473560051     | 0473460051       |
| 101-150        | 0473560101     | 0473460101       |
| 151-200        | 0473560151     | 0473460151       |
| 201-250        | 0473560201     | 0473460201       |
| 251-300        | 0473560251     | 0473460251       |
| 301-350        | 0473560301     | 0473460301       |
| 351-400        | 0473560351     | 0473460351       |
| 401-450        | 0473560401     | 0473460401       |
| 451-500        | 0473560451     | 0473460451       |




Additional number sequences, letters and symbols are available.

### Dekafix Multi-Card Markers (Blank & Custom Print)

| Model      | Type         | Part Number |
|------------|--------------|-------------|
| DEK 5/5 MC | Blank        | 1609801044  |
| DEK 5/5 MC | Custom Print | 1854500000  |

## Support and Hoods


| Terminal Block                        | ADP                    | HP               |
|---------------------------------------|------------------------|------------------|
| ST5<br>ST5P<br>ST5P1 / ST5 N / ST5 PN | ADP - 0485300000 (1m)  | HP2 - 0485660000 |
| ST5 - 16mm <sup>2</sup>               | ADP - 0447700000 (1m)  | ---              |
| ST25                                  | ADP - 04854000000 (1m) | HP3 - 0485760000 |
| ST6<br>ST6T                           | ADP3 - 0485400000 (1m) | HP4 - 0485860000 |



## Screwdrivers

For Screw, Sleeve or Self-locking versions only.

| Terminal Type              | Description    | a (mm/Inch) | b (mm/Inch) | c (mm/Inch) | Part Number |
|----------------------------|----------------|-------------|-------------|-------------|-------------|
| ST5 N / EN                 | SD 1.0x5.5x150 | 1.0/.039    | 5.5/.216    | 150/5.91    | 9008350000  |
| ST5PN / EN                 | SD 1.0x5.5x150 | 1.0/.039    | 5.5/.216    | 150/5.91    | 9008350000  |
| ST6 / EN                   | SD 1.0x5.5x150 | 1.0/.039    | 5.5/.216    | 150/5.91    | 9008350000  |
| ST6 T / EN<br>(Terminal)   | SD 1.0x5.5x150 | 1.0/.039    | 5.5/.216    | 150/5.91    | 9008350000  |
| ST6 T / EN<br>(Disconnect) | SD 0.5x3.0x8.0 | 0.5/.019    | 3.0/.118    | 8.0/.314    | 9008320000  |
| ST25 V1 / EN               | SD 1.2x6.5x150 | 1.2/.047    | 6.5/.255    | 150/5.91    | 9009010000  |
| ST25 V2 / EN               | SD 1.2x6.5x150 | 1.2/.047    | 6.5/.255    | 150/5.91    | 9009010000  |
| ST5 / EN                   | SDK PH1        |             |             | 80/3.14     | 9008480000  |
| ST5P / EN                  | SDK PH1        |             |             | 80/3.14     | 9008480000  |
| ST5P1 V2 / EN              | SDK PH1        |             |             | 80/3.14     | 9008480000  |
| ST5P1 V4 / EN              | SDK PH1        |             |             | 80/3.14     | 9008480000  |
| ST5P1 V5 / EN              | SDK PH2        |             |             | 100/3.93    | 9008490000  |



## Ring Lug Terminal Blocks

## Standard Line



|                                      |  |                          |             |                           |             |            |
|--------------------------------------|--|--------------------------|-------------|---------------------------|-------------|------------|
|                                      |  | ST5 / EN<br>Feed through |             | ST5P / EN<br>Feed through |             |            |
|                                      |  |                          |             |                           |             |            |
|                                      |  | Screw                    |             | Screw                     |             |            |
| Width ( mm / Inch )                  |  | 9.7 / 0.382              |             | 9.7 / 0.382               |             |            |
| Insulating material ( UL94 )         |  | PA ( V2 )                |             | PA ( V2 )                 |             |            |
| Rated data                           |  | IEC/DIN-VDE              | /UL         | IEC/DIN-VDE               | /UL         |            |
| Voltage                              |  | 800 V                    | 600 V       | 800 V                     | 600 V       |            |
| Current                              |  | 35 A                     | 35 A        | 35 A                      | 45 A        |            |
| Cross-section                        |  | 4 mm²                    | 20 - 10 AWG | 4 mm²                     | 22 - 10 AWG |            |
| Impulse voltage                      |  | 6 kV                     |             | 6 kV                      |             |            |
| Pollution severity                   |  | 3                        |             | 3                         |             |            |
| Torque range                         |  | 0.8 - 1.6 Nm             |             | 0.8 - 1.6 Nm              |             |            |
| Torque range - connections           |  |                          |             |                           |             |            |
| (See Lug Dimensions Chart P7) Thread |  | M3.5                     |             | M3.5                      |             |            |
| Ordering Data                        |  | Part No.                 |             | Part No.                  |             |            |
|                                      |  | C9000676                 |             | C9001456                  |             |            |
| (Beige)                              |  |                          |             |                           |             |            |
| (Beige)                              |  |                          |             |                           |             |            |
| Disconnect (Beige)                   |  |                          |             |                           |             |            |
| Disconnect (Beige)                   |  |                          |             |                           |             |            |
| Accessories                          |  |                          |             |                           |             |            |
| End plate                            |  | Width (mm/Inch)          | Part No.    | Width (mm/Inch)           | Part No.    |            |
|                                      |  | (Beige) AP PA            | 1.5/.059    | C9000686                  | 1.5/.059    | C9000686   |
| Adapter sleeve - Pin                 |  | Part No.                 |             | Part No.                  |             |            |
|                                      |  | STB 21.6 (Beige)         |             |                           |             |            |
|                                      |  | Pin PS4                  |             |                           |             |            |
| Partition plate                      |  | Width (mm/Inch)          | Part No.    | Width (mm/Inch)           | Part No.    |            |
|                                      |  | (BG) TW PA               | 1.5/.059    | C904318600                | 1.5/.059    | C904318600 |
|                                      |  | (BG) TW HP               | 0.5/.019    | 0474700000                | 0.5/.019    | 0474700000 |
|                                      |  | (BG) TW PA               |             |                           |             |            |
|                                      |  | TW HP - TS 32            |             |                           |             |            |
| Cross-connection                     |  | Part No.                 |             | Part No.                  |             |            |
| Kit                                  |  | Q2                       |             |                           |             |            |
| VH                                   |  | Q3                       |             |                           |             |            |
| Q2                                   |  | Q4                       |             |                           |             |            |
| Q3                                   |  | Q5                       |             |                           |             |            |
|                                      |  | Q7                       |             |                           |             |            |
|                                      |  | Q10                      |             |                           |             |            |
|                                      |  | Q50                      |             |                           |             |            |
|                                      |  | QL2                      |             | C9001370                  | C9001370    |            |
|                                      |  | QL3                      |             | C9001380                  | C9001380    |            |
|                                      |  | QL4                      |             | C9001390                  | C9001390    |            |
|                                      |  | QL5                      |             |                           |             |            |
|                                      |  | QL7                      |             |                           |             |            |
|                                      |  | QL10                     |             | C9000750                  | C9000750    |            |
|                                      |  | QL50                     |             |                           |             |            |
|                                      |  | Sleeve VH 13.5           |             |                           |             |            |
|                                      |  | Kit (1 Screw + 1 Washer) |             |                           |             |            |
| Connection for short-circuit         |  | Part No.                 |             | Part No.                  |             |            |
|                                      |  | ZQV 10/2                 |             |                           |             |            |
| End brackets                         |  | Width (mm/Inch)          | Part No.    | Width (mm/Inch)           | Part No.    |            |
|                                      |  | EW35 - TS 35             | 8.5/.334    | 0383560000                | 8.5/.334    | 0383560000 |
|                                      |  | WEW35/2 - TS 35          | 8.0/.315    |                           | 8.0/.315    |            |
|                                      |  | EWK1 - TS 32             | 8.5/.334    | 0206160000                | 8.5/.334    | 0206160000 |
|                                      |  | EWK2 - TS 32             | 15.0/.59    |                           | 15.0/.59    |            |
|                                      |  | WEW35 - TS 35            | 12.2/.48    |                           | 12.2/.48    |            |
| Rails                                |  | Part No.                 |             | Part No.                  |             |            |
|                                      |  | TS 35 steel              |             | 0383400000                | 0383400000  |            |
|                                      |  | TS 35 steel slotted      |             | 0514500000                | 0514500000  |            |
|                                      |  | TS 32 steel              |             | 0122800000                | 0122800000  |            |


# Standard Line

# Ring Lug Terminal Blocks

## ST5P1 V2 / EN

Feed through

42.6



Screw


13.2 / 0.519

PA ( V2 )

## ST5P1 V1 / EN

Feed through

42.6



Nut


13.2 / 0.519

PA ( V2 )

## ST5P1 V4 and 5 / EN

Feed through

42.6



Self-locking Nut


13.2 / 0.519

PA ( V2 )

## ST5S-16mm<sup>2</sup>

Feed through

54.3



Nut


16.5 / 0.642

PA ( V0 )

## STL5-16mm<sup>2</sup>

Test disconnect

54.3



Nut

16.5 / 0.642

PA ( V0 )

| IEC/DIN-VDE       | UL         | IEC/DIN-VDE       | UL         | IEC/DIN-VDE       | UL         | IEC/DIN-VDE        | UL          | IEC/DIN-VDE        | UL          |
|-------------------|------------|-------------------|------------|-------------------|------------|--------------------|-------------|--------------------|-------------|
| 500 V             | 300 V      | 500 V             | 300 V      | 500 V             | 300 V      | 800 V              | 600 V       | 800 V              | 600 V       |
| 46 A              | 46 A       | 46 A              | 46 A       | 46 A              | 46 A       | 76 A               | 65 A        | 76 A               | 65 A        |
| 6 mm <sup>2</sup> | 24 - 6 AWG | 6 mm <sup>2</sup> | 24 - 6 AWG | 6 mm <sup>2</sup> | 24 - 6 AWG | 16 mm <sup>2</sup> | AWG 12...10 | 16 mm <sup>2</sup> | AWG 12...10 |
| 6 kV              |            | 6 kV              |            | 6 kV              |            | 8 kV               |             | 8 kV               |             |
| 3                 |            | 3                 |            | 3                 |            | 3                  |             | 3                  |             |
| 1.2 - 1.9 Nm      |            | 1.2 - 2.4 Nm      |            | 1.2 - 2.4 Nm      |            | 2.0 - 4.0 Nm       |             | 2.0 - 4.0 Nm       |             |
| 0.8 - 1.6 Nm      |            | 0.8 - 1.6 Nm      |            | 0.8 - 1.6 Nm      |            | 0.8 - 1.6 Nm       |             | 0.8 - 1.6 Nm       |             |
| M4                |            | M4                |            | M4 & M5           |            | M5                 |             | M5                 |             |
| Part No.          |            | Part No.          |            | Part No.          |            | Part No.           |             | Part No.           |             |
| C904916600        |            | C904904600        |            | C904922600 (M4)   |            | 0448360000         |             |                    |             |
|                   |            |                   |            | C904915600 (M5)   |            |                    |             |                    |             |
|                   |            |                   |            |                   |            |                    |             | 0448460000         |             |

| Width (mm/Inch) | Part No. | Width (mm/Inch) | Part No. | Width (mm/Inch) | Part No. | Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   |
|-----------------|----------|-----------------|----------|-----------------|----------|-----------------|------------|-----------------|------------|
| 1.5/059         | C9001506 | 1.5/059         | C9001506 | 1.5/059         | C9001506 | 1.5/059         | 0447260000 | 1.5/059         | 0447260000 |

| Part No. | Part No. | Part No. | Part No. | Part No. |
|----------|----------|----------|----------|----------|
|----------|----------|----------|----------|----------|

| Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   |
|-----------------|------------|-----------------|------------|-----------------|------------|-----------------|------------|-----------------|------------|
| 1.5/059         | C904319600 | 1.5/059         | C904319600 | 1.5/059         | C904319600 | 1.5/059         | 0477660000 | 1.5/059         | 0477660000 |
| 0.5/019         | 0474700000 | 0.5/019         | 0474700000 | 0.5/019         | 0474700000 |                 |            |                 |            |

| Part No.   | Part No.   | Part No.   | Part No.   | Part No.   |
|------------|------------|------------|------------|------------|
|            |            |            |            |            |
|            |            |            |            |            |
|            |            |            |            |            |
|            |            |            |            |            |
|            |            |            |            |            |
|            |            |            |            |            |
|            |            |            |            |            |
| C904913600 | C904913600 | C904913600 | 3834300000 | 3834300000 |
| C904914600 | C904914600 | C904914600 |            |            |
| C904917600 | C904917600 | C904917600 |            |            |
|            |            |            |            |            |
|            |            |            |            |            |
| C904918600 | C904918600 | C904918600 |            |            |
|            |            |            |            |            |
|            | C904919600 |            |            |            |
| C904919600 |            | C904919600 |            |            |
| Part No.   | Part No.   | Part No.   | Part No.   | Part No.   |

| Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   | Width (mm/Inch) | Part No.   |
|-----------------|------------|-----------------|------------|-----------------|------------|-----------------|------------|-----------------|------------|
| 8.5/334         | 0383560000 | 8.5/334         | 0383560000 | 8.5/334         | 0383560000 | 8.5/334         | 0383560000 | 8.5/334         | 0383560000 |
| 8.0/315         |            | 8.0/315         |            | 8.0/315         | 1061200000 | 8.0/315         | 1061200000 | 8.0/315         | 1061200000 |
| 8.5/334         | 0206160000 | 8.5/334         | 0206160000 | 8.5/334         | 0206160000 | 8.5/334         | 0206160000 | 8.5/334         | 0206160000 |
| 15.0/59         |            | 15.0/59         |            | 15.0/59         |            | 15.0/59         |            | 15.0/59         |            |
| 12.2/48         |            | 12.2/48         |            | 12.2/48         |            | 12.2/48         |            | 12.2/48         |            |
| Part No.        | Part No.   | Part No.        | Part No.   | Part No.        | Part No.   | Part No.        | Part No.   | Part No.        | Part No.   |
| 0383400000      | 0383400000 | 0383400000      | 0383400000 | 0383400000      | 0383400000 | 0383400000      | 0383400000 | 0383400000      | 0383400000 |
| 0514500000      | 0514500000 | 0514500000      | 0514500000 | 0514500000      | 0514500000 | 0514500000      | 0514500000 | 0514500000      | 0514500000 |
| 0122800000      | 0122800000 | 0122800000      | 0122800000 | 0122800000      | 0122800000 | 0122800000      | 0122800000 | 0122800000      | 0122800000 |