




CATALOG LISTING
1EN380-6
PAGE 1 OF 1
RELEASE NO. PR-12941-T REPLACES


ISSUE
6

REVISIONS

DDM/CAD
DRAWN

M A M 26MAR97
CHECK J A F 14 APR 97
CHECK



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA			SCALE FULL
OPERATING FORCE — — — — 6 —12 LB		CONTACT ARRANGEMENT 2X S P D T			DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE --- 30 LB MAX					
RELEASE FORCE — — — — — 4 LB MIN		28 VDC			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT 9.0 OZ MIN
PRETRAVEL — — — — — .040 MAX		LOAD	SEA LEVEL 50,000 FT.		
DIFFERENTIAL TRAVEL — — — .020 MAX		RES	4	4	
OVERTRAVEL — — — — — .250 MIN		IND	2	2	
		MOTOR	4		

- NOTES
- 1 – CORROSION RESISTANT STEEL ENCLOSURE
 - 2 – SWITCH SEALED PER MIL-S-8805 SYMBOL 4
 - 3 – CIRCUIT DIAGRAM, CATALOG LISTING AND DATE CODE ARE SHOWN ON NAMEPLATE
 - 4 – COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN380-6](#)