

Surface Mount TRANSZORB® Transient Voltage Suppressors


DO-215AB (SMCG)

FEATURES

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- Available in uni-directional and bi-directional
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS	
V_{WM}	5.0 V to 188 V
P_{PPM}	1500 W
P_D	6.5 W
I_{FSM} (uni-directional only)	200 A
T_J max.	150 °C

DEVICES FOR BI-DIRECTION APPLICATIONS

For bi-directional devices use CA suffix (e.g. SMCG188CA).

Electrical characteristics apply in both directions.

TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, automotive, and telecommunication.

MECHANICAL DATA

Case: DO-215AB (SMCG)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-E3 - RoHS compliant, commercial grade
Base P/NHE3 - RoHS compliant, AEC-Q101 qualified

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: For uni-directional types the band denotes cathode end, no marking on bi-directional types

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with a 10/1000 μ s waveform ⁽¹⁾⁽²⁾	P_{PPM}	1500	W
Peak pulse current with a 10/1000 μ s waveform ⁽¹⁾	I_{PPM}	See next table	A
Peak forward surge current 8.3 ms single half sine-wave uni-directional only ⁽²⁾	I_{FSM}	200	A
Power dissipation on infinite heatsink, $T_A = 50$ °C	P_D	6.5	W
Operating junction and storage temperature range	T_J, T_{STG}	- 55 to + 150	°C

Notes

⁽¹⁾ Non-repetitive current pulse, per fig. 3 and derated above $T_A = 25$ °C per fig. 2.

⁽²⁾ Mounted on 0.31" x 0.31" (8.0 mm x 8.0 mm) copper pads to each terminal

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)								
DEVICE TYPE MODIFIED GULL WING	DEVICE MARKING CODE		BREAKDOWN VOLTAGE V_{BR} AT I_T ⁽¹⁾ (V)		TEST CURRENT I_T (mA)	STAND-OFF VOLTAGE V_{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_D (μA) ⁽³⁾	MAXIMUM PEAK PULSE SURGE CURRENT I_{PPM} (A) ⁽²⁾
	UNI	BI	MIN.	MAX.				
(+)SMCG5.0A ⁽⁵⁾	GDE	GDE	6.40	7.07	10	5.0	1000	163.0
(+)SMCG6.0A	GDG	GDG	6.67	7.37	10	6.0	1000	145.6
(+)SMCG6.5A	GDK	BDK	7.22	7.98	10	6.5	500	133.9
(+)SMCG7.0A	GDM	GDM	7.78	8.60	10	7.0	200	125.0
(+)SMCG7.5A	GDP	BDP	8.33	9.21	1.0	7.5	100	116.3
(+)SMCG8.0A	GDR	BDR	8.89	9.83	1.0	8.0	50	110.3
(+)SMCG8.5A	GDT	BDT	9.44	10.4	1.0	8.5	20	104.2
(+)SMCG9.0A	GDV	BDV	10.0	11.1	1.0	9.0	10	97.4
(+)SMCG10A	GDX	BDX	11.1	12.3	1.0	10	5.0	88.2
(+)SMCG11A	GDZ	GDZ	12.2	13.5	1.0	11	5.0	82.4
(+)SMCG12A	GEE	BEE	13.3	14.7	1.0	12	5.0	75.4
(+)SMCG13A	GEG	GEG	14.4	15.9	1.0	13	1.0	69.8
(+)SMCG14A	GEK	BEK	15.6	17.2	1.0	14	1.0	64.7
(+)SMCG15A	GEM	BEM	16.7	18.5	1.0	15	1.0	61.5
(+)SMCG16A	GEP	GEP	17.8	19.7	1.0	16	1.0	57.7
(+)SMCG17A	GER	GER	18.9	20.9	1.0	17	1.0	54.3
(+)SMCG18A	GET	BET	20.0	22.1	1.0	18	1.0	51.4
(+)SMCG20A	GEV	BEV	22.2	24.5	1.0	20	1.0	46.3
(+)SMCG22A	GEX	BEX	24.4	26.9	1.0	22	1.0	42.3
(+)SMCG24A	GEZ	BEZ	26.7	29.5	1.0	24	1.0	38.6
(+)SMCG26A	GFE	BFE	28.9	31.9	1.0	26	1.0	35.6
(+)SMCG28A	GFG	BFG	31.1	34.4	1.0	28	1.0	33.0
(+)SMCG30A	GFK	BFK	33.3	36.8	1.0	30	1.0	31.0
(+)SMCG33A	GFM	BFM	36.7	40.6	1.0	33	1.0	28.1
(+)SMCG36A	GFP	BFP	40.0	44.2	1.0	36	1.0	25.8
(+)SMCG40A	GFR	BFR	44.4	49.1	1.0	40	1.0	23.3
(+)SMCG43A	GFT	BFT	47.8	52.8	1.0	43	1.0	21.6
(+)SMCG45A	GFV	GFV	50.0	55.3	1.0	45	1.0	20.6
(+)SMCG48A	GFX	GFX	53.3	58.9	1.0	48	1.0	19.4
(+)SMCG51A	GFZ	GFZ	56.7	62.7	1.0	51	1.0	18.2
(+)SMCG54A	GGE	GGE	60.0	66.3	1.0	54	1.0	17.2
(+)SMCG58A	GGG	GGG	64.4	71.2	1.0	58	1.0	16.0
(+)SMCG60A	GGK	GGK	66.7	73.7	1.0	60	1.0	15.5
(+)SMCG64A	GGM	GGM	71.1	78.6	1.0	64	1.0	14.6
(+)SMCG70A	GGP	GGP	77.8	86.0	1.0	70	1.0	13.3
(+)SMCG75A	GGR	GGR	83.3	92.1	1.0	75	1.0	12.4
(+)SMCG78A	GGT	GGT	86.7	95.8	1.0	78	1.0	11.9
(+)SMCG85A	GGV	GGV	94.4	104	1.0	85	1.0	10.9
(+)SMCG90A	GGX	GGX	100	111	1.0	90	1.0	10.3
(+)SMCG100A	GGZ	GGZ	111	123	1.0	100	1.0	9.3
(+)SMCG110A	GHE	GHE	122	135	1.0	110	1.0	8.5
(+)SMCG120A	GHG	GHG	133	147	1.0	120	1.0	7.8
(+)SMCG130A	GHK	GHK	144	159	1.0	130	1.0	7.2
(+)SMCG150A	GHM	GHM	167	185	1.0	150	1.0	6.2
(+)SMCG160A	GHP	GHP	178	197	1.0	160	1.0	5.8
(+)SMCG170A	GHR	GHR	189	209	1.0	170	1.0	5.5
SMCG188A	GHS	GHS	209	231	1.0	188	1.0	4.6
SMCG188A								

Notes

- (1) Pulse test: $t_p \leq 50$ ms
- (2) Surge current waveform per fig. 3 and derate per fig. 2
- (3) For bi-directional types having V_{WM} of 10 V and less, the I_D limit is doubled
- (4) All terms and symbols are consistent with ANSI/IEEE C62.35
- (5) For the bi-directional SMCG5.0CA, the maximum V_{BR} is 7.25 V
- (6) $V_F = 3.5$ V at $I_F = 100$ A (uni-directional only)
- (+) Underwriters laboratory recognition for the classification of protectors (QVGQ2) under the UL standard for safety 497B and file number E136766 for both uni-directional and bi-directional devices

THERMAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Typical thermal resistance, junction to ambient ⁽¹⁾	$R_{\theta JA}$	75	$^\circ\text{C}/\text{W}$
Typical thermal resistance, junction to lead	$R_{\theta JL}$	15	

Note

⁽¹⁾ Measured on minimum recommended pad layout

ORDERING INFORMATION (Example)

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SMCG5.0A-E3/57T	0.211	57T	850	7" diameter plastic tape and reel
SMCG5.0A-E3/9AT	0.211	9AT	3500	13" diameter plastic tape and reel
SMCG5.0AHE3/57T ⁽¹⁾	0.211	57T	850	7" diameter plastic tape and reel
SMCG5.0AHE3/9AT ⁽¹⁾	0.211	9AT	3500	13" diameter plastic tape and reel

Note

⁽¹⁾ AEC-Q101 qualified


RATINGS AND CHARACTERISTICS CURVES ($T_A = 25^\circ\text{C}$ unless otherwise noted)


Fig. 1 - Peak Pulse Power Rating Curve




Fig. 3 - Pulse Waveform




Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature




Fig. 4 - Typical Junction Capacitance Uni-Directional




Fig. 5 - Typical Transient Thermal Impedance








Fig. 6 - Maximum Non-Repetitive Peak Forward Surge Current
Uni-Directional Use Only

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-215AB (SMCG)



Mounting Pad Layout



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.