

Metallized Polyester Film Capacitor

Type: **ECQE(H)**

Non-inductive construction using metallized Polyester film with flame retardant epoxy resin coating for active filter

■Features

- Smaller size
- Self-healing property
- Excellent electrical characteristics
- Flame retardant epoxy resin coating
- RoHS directive compliant

■Recommended Applications

- Active filter circuit

■Explanation of Part Numbers

1

2

3

4

5

6

7

8

9

10

11

12

E

C

Q

E

2

W

H

Product code

Dielectric & construction

Rated voltage

Capacitance

Cap. Tol.

Suffix

Suffix

2 W

450 VDC

J

±5 %

K

±10 %

Suffix

Lead Form

Blank

Straight

B

Crimped lead

■Explanation of Part Number for Odd Size Taping

E

C

Q

E

2

W

R

H

Product code

Dielectric & construction

Rated voltage

Capacitance

Suffix

Cap. Tol.


Suffix

■Specifications

Category temp. range	−40 °C to +105 °C
Rated voltage	450 VDC (Derating of rated voltage by 1.25%/°C at more than 85 °C)
Capacitance range	0.10 μF to 2.2 μF (E6)
Capacitance tolerance	±5 %(J), ±10 %(K)
Dissipation factor (tanδ)	tanδ≤1.0 % (20 °C, 1 kHz)
Withstand voltage	Between terminals:Rated voltage (VDC) ×150 % 60 s Between terminals to enclosure :Rated voltage (VDC) ×200 % 1 s to 5 s
Insulation resistance (IR)	C≤0.33 μF : IR≥9000 MΩ C>0.33 μF : IR≥3000 MΩ · μF (20 °C, 100 VDC, 60 s)


※ Application of this capacitor is limited to active filter circuit after the circuit of all wave rectification.

■ Dimensions in mm (not to scale)



■ Taping Specifications for Automatic Insertion

● Taping style



■ Packaging Specifications for Bulk Package

Packing quantity: 100 pcs./bag

*Refer to the page of taping specifications.

● Packaging Specifications

Type	Rated volt.	Cap. range (μF)	Taping style						Packing	suffix
			AD	AS	B	C	D	E		
ECQE(H)	450 VDC	0.10 to 0.47					○		Ammo	R() H
		0.68 to 1.0						○	Ammo	R() H

● Lead Spacing

Style	Lead Spacing
D	7.5 mm
E	7.5 mm

*See the column "Rating, Dimensions & Quantity Box" for packing quantity.

■ Rating, Dimensions & Quantity/Ammo Box

● Rated voltage : 450 VDC, Capacitance tolerance : ±5 % (J), ±10 % (K)

【Standard type】

Part No.	Cap. (μF)	Dimensions (mm)								Quantity
		L ^{max.}	T ^{max.}	H ^{max.}		F	S	G ^{max.}	ød	Ammo 7.5 mm
				Straight	Crimped lead	Straight	Crimped lead	Straight		
ECQE2W104□H()	0.10	12.7	4.2	10.9	15.9	10.0	5.0	1.0	0.6	1500
ECQE2W154□H()	0.15	12.7	4.9	11.6	16.6	10.0	5.0	1.0	0.6	1000
ECQE2W224□H()	0.22	12.7	5.8	12.5	17.5	10.0	5.0	1.0	0.6	1000
ECQE2W334□H()	0.33	12.7	6.5	14.7	19.7	10.0	5.0	1.0	0.6	900
ECQE2W474□H()	0.47	12.7	7.7	16.0	21.0	10.0	5.0	1.0	0.6	800
ECQE2W684□H()	0.68	18.2	6.9	15.3	20.3	15.0	10.0	1.0	0.8	500
ECQE2W105□H()	1.0	18.2	8.5	16.9	21.9	15.0	10.0	1.0	0.8	400
ECQE2W155□H()	1.5	25.7	8.2	16.2	21.2	22.5	15.0	1.0	0.8	—
ECQE2W225□H()	2.2	25.7	9.4	19.7	24.7	22.5	15.0	1.0	0.8	—

↑ Suffix for lead crimped
 ↑ Capacitance tolerance code

*Please consult us for low profile type.

【Low Profile type complying with passive flammability category B based on IEC60065】

Part No.	Cap. (μF)	Dimensions (mm)						Quantity Ammo 7.5 mm
		L max.	T max.	H max.	F	G max.	ød	
ECQE2W684L24	0.68	18.2	8.1	13.3	15.0	1.0	0.8	500
ECQE2W105L24	1.0	18.2	9.7	14.9	15.0	1.0	0.8	400
ECQE2W155L02	1.5	25.7	9.4	14.2	22.5	1.0	0.8	—
ECQE2W225L02	2.2	25.7	11.3	16.2	22.5	1.0	0.8	—

*Please consult us for crimped lead and taping.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[ECQ-E2W105KH](#) [ECQ-E2W155KH](#) [ECQ-E2W225KH](#) [ECQ-E2W474KH](#) [ECQ-E2W684KH](#) [ECQ-E2W225JH](#) [ECQ-E2W474KH7](#)