

Optional Mounting Brackets

Matrix For Solid Bearing Slides & Appropriate Rear Mounting Brackets with Range of Extension

	B-131*	B-131-2	B-131-2.5	B-131-3	B-131-3.5	B-131-4	B-307-1 B-814-1	B-307-2 B-814-2	B-810-1	B-810-2
C-230-D	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06	0 to 4.00	0 to 8.00		
C-230-S	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06	0 to 4.00	0 to 8.00		
CTD	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06	0 to 4.00	0 to 8.00		
CTS	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06	0 to 4.00	0 to 8.00		
CTRD	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06	0 to 4.00	0 to 8.00		
CTRS	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06	0 to 4.00	0 to 8.00		
CTHD	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06			0 to 4.00	0 to 8.00
CTHS	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06			0 to 4.00	0 to 8.00
CTHRD	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06			0 to 4.00	0 to 8.00
CTHRS	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06			0 to 4.00	0 to 8.00
C-857	0 to .50	.44 to 1.06	.94 to 1.56	1.44 to 2.06	1.94 to 2.56	2.44 to 3.06				

Note brackets are made from 16 gauge C.R.S. — Standard finish: zinc clear chromate

*Supplied with standard slides

CATALOG NUMBER	A	
B-131	1.56	
B-131-2	2.00	
B-131-2.5	2.50	
B-131-3	3.00	
B-131-3.5	3.50	
B-131-4	4.00	

Technical drawing of a mounting bracket. Dimensions include: A (total width), B (slide width), 1.00 (top flange), .63 (TYP) (top flange thickness), 1.75 (height), .91 (bottom flange), 3.56 (height), and .218 DIA. (C) NO. OF HOLES. A leader line points to the hole pattern with the text ".218 DIA. (C) NO. OF HOLES".

Technical drawing of mounting bracket B-307. Dimensions include: .70 (top flange), .20 (top flange thickness), 3.44 (height), .63 (bottom flange), .50 (bottom flange thickness), 1.75 (height), 3.00 (height), and .63 (bottom flange).

B-307

Technical drawing of mounting bracket B-810. Dimensions include: .70 (top flange), .20 (top flange thickness), 3.63 (height), .63 (bottom flange), .50 (bottom flange thickness), 1.75 (height), 3.00 (height), and .63 (bottom flange).

B-810

Technical drawing of mounting bracket B-814. Dimensions include: .70 (top flange), .42 (top flange thickness), .20 (top flange thickness), 3.44 (height), .63 (bottom flange), .50 (bottom flange thickness), 1.75 (height), 3.00 (height), and .63 (bottom flange).

B-814

CATALOG NUMBER

A

B

C

B-307-1 / B-810-1 / B-814-1

5.94

4.38

16

B-307-2 / B-810-2 / B-814-2

9.69

8.13

28