


MF 5mmL, Low Impedance
series



- Low impedance over wide temperature range of -55 to $+105^{\circ}\text{C}$, with 5mm height.
- Suited for DC-DC converters where smaller case size and lower impedance are required.
- Compliant to the RoHS directive (2011/65/EU).


MF ← Low Impedance MT



Specifications

Item	Performance Characteristics											
Category Temperature Range	−55 to +105°C											
Rated Voltage Range	6.3 to 35V											
Rated Capacitance Range	1 to 100μF											
Rated Capacitance Tolerance	±20% at 120Hz, 20°C											
Leakage Current	After 2 minutes' application of rated voltage, leakage current is not more than 0.01CV or 3 (μA), whichever is greater.											
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C											
	Rated voltage (V)	6.3	10	16	25	35						
	tan δ (MAX.)	0.22	0.20	0.18	0.14	0.12						
Stability at Low Temperature	Measurement frequency : 120Hz											
	Rated voltage (V)		6.3	10	16	25	35					
	Impedance ratio ZT / Z20 (MAX.)	Z−25°C / Z+20°C	2	2	2	2	2					
		Z−55°C /Z+20°C	4	4	3	3	3					
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 105°C.											
							Capacitance change		Within ±20% of the initial capacitance value			
							tan δ		200% or less than the initial specified value			
	Leakage current		Less than or equal to the initial specified value									
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.											
Marking	Printed with white color letter on dark brown sleeve.											

Radial Lead Type



ϕD	4	5	6.3
P	1.5	2.0	2.5
ϕd	0.45	0.45	0.45

(mm)

Type numbering system (Example : 25V $10\mu\text{F}$)

1	2	3	4	5	6	7	8	9	10	11
U	M	F	1	E	1	0	0	M	D	D
			Configuration ※					Capacitance tolerance ($\pm 20\%$)		
								Rated capacitance ($10\mu\text{F}$)		
								Rated voltage (25V)		
								Series name		
								Type		

※ Configuration

ϕD	Pb-free leadwire Pb-free PET sleeve
4 to 6.3	DD

Dimensions

Cap. (μF)	V	6.3	10	16	25	35
Code		0J	1A	1C	1E	1V
1	010					4×5 5.0 50
1.5	1R5					4×5 5.0 50
2.2	2R2					4×5 5.0 50
3.3	3R3					4×5 5.0 50
4.7	4R7				4×5 5.0 50	4×5 5.0 50
6.8	6R8				4×5 5.0 50	5×5 2.6 80
10	100			4×5 5.0 50	5×5 2.6 80	5×5 2.6 80
15	150			5×5 2.6 80	6.3×5 1.3 115	6.3×5 1.3 115
22	220	4×5 5.0 50	5×5 2.6 80	5×5 2.6 80	6.3×5 1.3 115	6.3×5 1.3 115
33	330	5×5 2.6 80	5×5 2.6 80	6.3×5 1.3 115	6.3×5 1.3 115	
47	470	5×5 2.6 80	6.3×5 1.3 115	6.3×5 1.3 115		
68	680	6.3×5 1.3 115				
100	101	6.3×5 1.3 115				Case size $\phi D \times L$ (mm) Impedance Rated ripple

Max. Impedance (Ω) at 20°C 100kHz
Rated ripple current (mA rms) at 105°C 100kHz

Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.35	0.50	0.64	0.83	1.00

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.

CAT.8100C