


High Voltage IGBT with Diode


IXGQ 35N120BD1

$$\begin{aligned} V_{CES} &= 1200 \text{ V} \\ I_{C25} &= 75 \text{ A} \\ V_{CE(sat)} &= 3.3 \text{ V} \\ t_{fi(typ)} &= 160 \text{ ns} \end{aligned}$$



Symbol	Test Conditions	Maximum Ratings	
V_{CES}	$T_J = 25^\circ\text{C to } 150^\circ\text{C}$	1200	V
V_{CGR}	$T_J = 25^\circ\text{C to } 150^\circ\text{C}; R_{GE} = 1 \text{ M}\Omega$	1200	V
V_{GES}	Continuous	± 20	V
V_{GEM}	Transient	± 30	V
I_{C25}	$T_C = 25^\circ\text{C}$	75	A
I_{C110}	$T_C = 110^\circ\text{C}$	35	A
I_{F110}	$T_C = 110^\circ\text{C}$	8	A
I_{CM}	$T_C = 25^\circ\text{C}, 1 \text{ ms}$	200	A
SSOA (RBSOA)	$V_{GE} = 15 \text{ V}, T_J = 125^\circ\text{C}, R_G = 10 \Omega$ Clamped inductive load	$I_{CM} = 120$ @0.8 V_{CES}	A
P_C	$T_C = 25^\circ\text{C}$	400	W
T_J		-55 ... +150	$^\circ\text{C}$
T_{JM}		150	$^\circ\text{C}$
T_{stg}		-55 ... +150	$^\circ\text{C}$
M_d	Mounting torque	1.13/10 Nm/lb.in.	
	Maximum lead temperature for soldering 1.6 mm (0.062 in.) from case for 10 s	300	$^\circ\text{C}$
Weight		6	g

TO-3P (IXGQ)



G = Gate C = Collector
E = Emitter TAB = Collector

Features


- International standard packages
- IGBT and anti-parallel FRED for resonant power supplies
 - Induction heating
 - Rice cookers
- MOS Gate turn-on
 - drive simplicity
- Fast Recovery Expitaxial Diode (FRED)
 - soft recovery with low I_{RM}

Advantages

- Saves space (two devices in one package)
- Easy to mount with 1 screw (isolated mounting screw hole)
- Reduces assembly time and cost

Symbol	Test Conditions	Characteristic Values ($T_J = 25^\circ\text{C}$, unless otherwise specified)		
		min.	typ.	max.
$V_{GE(th)}$	$I_C = 250 \mu\text{A}, V_{CE} = V_{GE}$	2.5		5.0 V
I_{CES}	$V_{CE} = V_{CES}$ $V_{GE} = 0 \text{ V}$			50 μA 250 μA $T=25^\circ\text{C}$ $T=125^\circ\text{C}$
I_{GES}	$V_{CE} = 0 \text{ V}, V_{GE} = \pm 20 \text{ V}$			$\pm 100 \text{ nA}$
$V_{CE(sat)}$	$I_C = 35 \text{ A}, V_{GE} = 15 \text{ V}$ Note 2	2.7	3.3	V

Symbol	Test Conditions	Characteristic Values ($T_J = 25^\circ\text{C}$, unless otherwise specified)		
		min.	typ.	max.
g_{fs}	$I_C = 35\text{A}; V_{CE} = 10\text{V}$, Note 2.	28	38	S
C_{ies}			2300	pF
C_{oes}	$V_{CE} = 25\text{V}, V_{GE} = 0\text{V}, f = 1\text{MHz}$		190	pF
C_{res}			80	pF
Q_g			140	nC
Q_{ge}	$I_C = 40\text{A}, V_{GE} = 15\text{V}, V_{CE} = 0.5 V_{CES}$		20	nC
Q_{gc}			50	nC
$t_{d(on)}$	Inductive load, $T_J = 25^\circ\text{C}$		40	ns
t_{ri}	$I_C = 35\text{A}; V_{GE} = 15\text{V}$		50	ns
E_{on}	$V_{CE} = 0.8 V_{CES}; R_G = R_{off} = 3\ \Omega$		0.9	mJ
$t_{d(off)}$	Note 1.		270	ns
t_{fi}			160	ns
E_{off}			3.8	mJ
$t_{d(on)}$	Inductive load, $T_J = 125^\circ\text{C}$		45	ns
t_{ri}	$I_C = 35\text{A}; V_{GE} = 15\text{V}$		60	ns
E_{on}	$V_{CE} = 0.8 V_{CES}; R_G = R_{off} = 3\ \Omega$		1.9	mJ
$t_{d(off)}$	Note 1		380	ns
t_{fi}			400	ns
E_{off}			8.0	mJ
R_{thJC}				0.35 K/W
R_{thCK}			0.25	K/W

TO-3P (IXGQ) Outline


SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.185	.193	4.70	4.90
A1	.051	.059	1.30	1.50
A2	.057	.065	1.45	1.65
b	.035	.045	0.90	1.15
b2	.075	.087	1.90	2.20
b4	.114	.126	2.90	3.20
c	.022	.031	0.55	0.80
D	.780	.791	19.80	20.10
D1	.665	.677	16.90	17.20
E	.610	.622	15.50	15.80
E1	.531	.539	13.50	13.70
e	.215 BSC		5.45 BSC	
L	.779	.795	19.80	20.20
L1	.134	.142	3.40	3.60
ϕP	.126	.134	3.20	3.40
$\phi P1$	.272	.280	6.90	7.10
S	.193	.201	4.90	5.10

All metal area are tin plated.

Symbol	Test Conditions	Characteristic Values ($T_J = 25^\circ\text{C}$, unless otherwise specified)		
		min.	typ.	max.
V_F	$I_F = 10\text{A}, V_{GE} = 0\text{V}$ $I_F = 10\text{A}, V_{GE} = 0\text{V}, T_J = 125^\circ\text{C}$			3.3 V 2.2 V
I_{RM}	$I_F = 10\text{A}; -di_F/dt = 100\text{A}/\mu\text{s}, V_R = 100\text{V}$		4.0	A
t_{rr}	$V_{GE} = 0\text{V}; T_J = 125^\circ\text{C}$		190	ns
t_{rr}	$I_F = 1\text{A}; -di_F/dt = 100\text{A}/\mu\text{s}; V_R = 30\text{V}, V_{GE} = 0\text{V}$		40	ns
R_{thJC}				2.5 K/W

- Notes:
- Switching times may increase for V_{CE} (Clamp) $> 0.8 \cdot V_{CES}$, higher T_J or increased R_G .
 - Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle $d \leq 2\%$.

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:	4,835,592	4,931,844	5,049,961	5,237,481	6,162,665	6,404,065 B1	6,683,344	6,727,585
	4,850,072	5,017,508	5,063,307	5,381,025	6,259,123 B1	6,534,343	6,710,405 B2	
	4,881,106	5,034,796	5,187,117	5,486,715	6,306,728 B1	6,583,505	6,710,463	




Fig. 18. Forward current I_F versus V_F




Fig. 19. Reverse recovery charge Q_r versus $-di_F/dt$




Fig. 20. Peak reverse current I_{RM} versus $-di_F/dt$




Fig. 21. Dynamic parameters Q_r , I_{RM} versus T_{VJ}




Fig. 22. Recovery time t_{rr} versus $-di_F/dt$




Fig. 23. Peak forward voltage V_{FR} and t_{rr} versus di_F/dt




Fig. 24. Transient thermal resistance junction to case

IXYS reserves the right to change limits, test conditions, and dimensions.

Constants for Z_{thJC} calculation:

i	R_{thi} (K/W)	t_i (s)
1	1.449	0.0052
2	0.558	0.0003
3	0.493	0.017