


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MAXIMUM BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH = L ± .3 [7]
MLT2LH-LP316	2.0" [51]	50	7.9" [201]
MLT4LH-LP316	4.0" [102]	50	14.3" [362]
MLT6LH-LP316	6.0" [152]	50	20.5" [521]
MLT8LH-LP316	8.0" [203]	50	26.8" [679]




NOTES:

1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS (1112 NEWTONS) WHEN TESTED ON A 1 1/2" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = ±.010 [.25] .XX = ±.02 [.5]
.X = ±.03 [.8] ANGLES = ±2°

FULLY ROUNDED
EDGES ALONG
STRAP BODY

SECTION A - A
SCALE: 8x

TITLE						
METAL LOCKING TIE LIGHT-HEAVY SERIES 316 STAINLESS STEEL						
CUSTOMER DRAWING						
ITEM REVISION NAME			PANDUIT			
N41127BS/04						
DATASET FILE NAME			MATERIAL:			
N41127BS/04						
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			316 STAINLESS STEEL			
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °						
			DRAWING NUMBER: N41127BS_DC			
THIRD ANGLE PROJECTION						
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE A
JAMB	6/03	DPN	2:1			