




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AA	22	B2	REVISED	PER ECO-11-005033	26MAR11	RK


- 1 MATERIAL:HOUSING – PCT POLYESTER, BLACK, UL 94V-0, IR COMPATIBLE.
TERMINALS – 0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27 μ m[.000050] MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 3.81 μ m[.000150] MINIMUM THICK MATTE TIN IN SOLDER AREA OVER 1.27 μ m[.000050] MINIMUM THICK NICKEL UNDERPLATE.
SHIELD: .254mm[.010] THICK COPPER ALLOY PLATED WITH 1.27 μ m [.000050] MINIMUM NICKEL AND 2.03 μ m [.000080] MINIMUM HOT TIN DIP ON PCB GROUND TABS.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
- 4 USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN PRODUCING THESE PCB HOLES.



SCALE 2:1



SUGGESTED PC BOARD LAYOUT
(COMPONENT SIDE)



SUGGESTED PANEL CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ATTADIA – DOCKS 15/JUN/2005	5557786-1 PART NUMBER	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK J. WESTMAN 15/JUN/2005	TE Connectivity	
		RPVD S. FLICKINGER 15/JUN/2005	NAME MODULAR JACK ASSEMBLY, 8 POSITION,RIGHT ANGLE,LOW PROFILE, SHIELDED,PC BOARD GROUND	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC 108-1163	SIZE A1	
		APPLICATION SPEC 114-2048	CAGE CODE 00779	
MATERIAL △	FINISH △	WEIGHT -	5557786	
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV B2