




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REDRAWN PER EC 0020-774-94	09/15/94	-	AF
E		REVISED PER ECO-17-016115	02NOV2017	RS	MZ



- 1 THIS CONNECTOR ACCEPTS FIVE (5) SIZE 16 MULTIMATE SOCKET CONTACTS.
MAXIMUM WIRE INSULATION DIAMETER = ø.135
- 2 THIS CONNECTOR MATES WITH AMP P/N 208720-1.
- 3 PART NUMBER AND DATE CODE MARKED ON ANY ANY FLANGE EDGE.
- 4 THERMOPLASTIC, BLACK.
- 5 ZINC PER QQ-Z-363.
- 6 NICKEL PER QQ-N-290 OVER COPPER PER MIL-C-14550.

208721-1

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 3/19/82	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK B. LENKER 9/26/94			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - ANGLES ± -		APVD A. FRANTUM 9/29/94		
	FINISH		PRODUCT SPEC 108-10040 APPLICATION SPEC		
MATERIAL SOCKET HOUSING: 4 RECEPTACLE SHELL: 6		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=208721
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV E