


LTR	DATE	REVISION		CHK	APD
A	6/27/13	508692ERA-RELEASED	FYUE		



PART #	BASE PART	DESCRIPTION	FIGURE
09230025LXRED	923-025-001	STUD CAP-3/8" RED	2
09230025LXBLK	923-025-002	STUD CAP-3/8" BLACK	2
09230025LXREDM8	923-025-003	STUD CAP-M8 RED	1
09230025LXBLKM8	923-025-004	STUD CAP-M8 BLACK	1




FIGURE 2. 3/8" STUD CAP

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M	
BILL OF MATERIAL					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.					
⊙	DENOTES CRITICAL CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
COPIES TO					
MATL SPEC					
SILICONE					
1 9 18	FINISH				
2 10 19	SEE CHART FOR COLOR				
3 12 20					
4 13 21					
5 14 23					
6 15 33					
7 16 43					
8 17 53					
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-PM)					
DIMENSION	0.5 - 3	UP TO 3	OVER 3 - 6	UP TO 6	OVER 6 - 120
TOLERANCE	+0.05	+0.05	+0.1	+0.15	+0.2
3RD ANGLE PROJECTION	TITLE				
STUD CAPS					
Littelfuse®			REVISION/	DRWG. NO.	OUTLINE
CHICAGO, USA 773-628-1000			A	OL-09230025LX	SERIES

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)