

## Cable sleeve - CES-SRG-BK-2X9 - 1410411

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Small, slotted cable sleeves suitable for two cables with a diameter of 8 ... 9 mm, material: NBR

### Product Description

drilled special sleeve in IP44



### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Minimum order quantity               | 10 pc    |
| Weight per Piece (excluding packing) | 8.0 g    |
| Custom tariff number                 | 40169300 |
| Country of origin                    | Poland   |

### Technical data

#### Dimensions

|                         |                  |
|-------------------------|------------------|
| External cable diameter | 2x 8 mm ... 9 mm |
| Length                  | 29.5 mm          |
| Width                   | 19.5 mm          |
| Height                  | 17 mm            |

#### Ambient conditions

|                                 |                            |
|---------------------------------|----------------------------|
| Degree of protection            | IP44                       |
| Ambient temperature (operation) | -40 °C ... 125 °C (static) |

#### General

|                     |                                |
|---------------------|--------------------------------|
| Product description | drilled special sleeve in IP44 |
| No. of conductors   | 2                              |
| Material            | NBR                            |

## Cable sleeve - CES-SRG-BK-2X9 - 1410411

### Technical data

#### General

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27081002 |
| eCl@ss 4.1 | 27081002 |
| eCl@ss 5.0 | 27081002 |
| eCl@ss 5.1 | 27081002 |
| eCl@ss 6.0 | 27081002 |
| eCl@ss 7.0 | 27081002 |
| eCl@ss 8.0 | 27069216 |

#### ETIM


|          |          |
|----------|----------|
| ETIM 3.0 | EC000879 |
| ETIM 4.0 | EC002498 |
| ETIM 5.0 | EC000451 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212109 |
| UNSPSC 7.0901 | 39121708 |
| UNSPSC 11     | 39121708 |
| UNSPSC 12.01  | 39121708 |
| UNSPSC 13.2   | 39121708 |

### Drawings

Dimensional drawing



Dimensional drawing

