


# Ultra-Low Iq 150 mA CMOS LDO Regulator with Enable

A 1.0  $\mu\text{F}$  ceramic capacitor is the recommended value to be used with these devices on the output pin.

- Ultra-Low Dropout Voltage of 250 mV at 150 mA
- Excellent Line Regulation of 0.05%/V
- Excellent Load Regulation of 20 mV
- High Output Voltage Accuracy of  $\pm 2\%$
- Ultra-Low Iq Current of 1.0  $\mu\text{A}$
- Very Low Shutdown Current of 0.1  $\mu\text{A}$
- Wide Output Voltage Range of 1.5 V to 3.3 V
- Low Temperature Drift Coefficient on the Output Voltage of  $\pm 100 \text{ ppm}/^\circ\text{C}$
- Fold Back Protection Circuit
- Input Voltage up to 6.5 V
- These are Pb-Free Devices

- Portable Equipment
- Hand-Held Instrumentation
- Camcorders and Cameras



[www.onsemi.com](http://www.onsemi.com)

**SC-82AB**  
SQ SUFFIX  
CASE 419C

**SOT-563**  
XV SUFFIX  
CASE 463A

X = Device Code  
T = Traceability Information

See detailed ordering and shipping information in the package dimensions section on page 8 of this data sheet.

# NCP583

## PIN FUNCTION DESCRIPTION

| SOT-563 Pin | SC-82AB Pin | Symbol    | Description                 |
|-------------|-------------|-----------|-----------------------------|
| 1           | 4           | $V_{in}$  | Power supply input voltage. |
| 2           | 2           | GND       | Power supply ground.        |
| 3           | 3           | $V_{out}$ | Regulated output voltage.   |
| 4           | –           | NC        | No connect.                 |
| 5           | –           | GND       | Power supply ground.        |
| 6           | 1           | CE        | Chip enable pin.            |

## MAXIMUM RATINGS

| Rating                                                           | Symbol             | Value                  | Unit |
|------------------------------------------------------------------|--------------------|------------------------|------|
| Input Voltage                                                    | $V_{in}$           | 6.5                    | V    |
| Input Voltage (CE Pin)                                           | $V_{CE}$           | 6.5                    | V    |
| Output Voltage                                                   | $V_{out}$          | –0.3 to $V_{in} + 0.3$ | V    |
| Output Current                                                   | $I_{out}$          | 180                    | mA   |
| Thermal Junction Resistance<br>SC-82AB<br>SOT-563                | $R_{\theta JA}$    | 263<br>200             | °C/W |
| ESD Capability, Human Body Model, C = 100 pF, R = 1.5 k $\Omega$ | ESD <sub>HBM</sub> | 2000                   | V    |
| ESD Capability, Machine Model, C = 200 pF, R = 0 $\Omega$        | ESD <sub>MM</sub>  | 200                    | V    |
| Operating Ambient Temperature Range                              | $T_A$              | –40 to +85             | °C   |
| Maximum Junction Temperature                                     | $T_{J(max)}$       | 125                    | °C   |
| Storage Temperature Range                                        | $T_{stg}$          | –55 to +150            | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

## ELECTRICAL CHARACTERISTICS ( $V_{in} = V_{out} + 1.0$ V, $T_A = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$ , unless otherwise noted.)

| Characteristic                                                                                                                                                                                                                       | Symbol                           | Min                   | Typ                          | Max                          | Unit          |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|-----------------------|------------------------------|------------------------------|---------------|
| Input Voltage                                                                                                                                                                                                                        | $V_{in}$                         | 1.7                   | –                            | 6.0                          | V             |
| Output Voltage ( $1.0\ \mu\text{A} \leq I_{out} \leq 30\ \text{mA}$ )                                                                                                                                                                | $V_{out}$                        | $V_{out} \times 0.98$ | –                            | $V_{out} \times 1.02$        | V             |
| Line Regulation ( $I_{out} = 30\ \text{mA}$ )<br>( $V_{out} + 0.5\ \text{V} \leq V_{in} \leq 6.0\ \text{V}$ )                                                                                                                        | Reg <sub>line</sub>              | –                     | 0.05                         | 0.20                         | %/V           |
| Load Regulation ( $1.0\ \mu\text{A} \leq I_{out} \leq 150\ \text{mA}$ )                                                                                                                                                              | Reg <sub>load</sub>              | –                     | 20                           | 40                           | mV            |
| Dropout Voltage ( $I_{out} = 150\ \text{mA}$ )<br>$V_{out} = 1.5\ \text{V}$<br>$1.7\ \text{V} \leq V_{out} \leq 1.9\ \text{V}$<br>$2.1\ \text{V} \leq V_{out} \leq 2.7\ \text{V}$<br>$2.8\ \text{V} \leq V_{out} \leq 3.3\ \text{V}$ | $V_{DO}$                         | –<br>–<br>–<br>–      | 0.60<br>0.50<br>0.35<br>0.25 | 0.90<br>0.75<br>0.55<br>0.40 | V             |
| Quiescent Current ( $I_{out} = 0\ \text{mA}$ )                                                                                                                                                                                       | $I_q$                            | –                     | 1.0                          | 1.5                          | $\mu\text{A}$ |
| Output Current                                                                                                                                                                                                                       | $I_{out}$                        | 150                   | –                            | –                            | mA            |
| Shutdown Current ( $V_{CE} = \text{Gnd}$ )                                                                                                                                                                                           | $I_{SD}$                         | –                     | 0.1                          | 1.0                          | $\mu\text{A}$ |
| Output Short Circuit Current ( $V_{out} = 0$ )                                                                                                                                                                                       | $I_{lim}$                        | –                     | 40                           | –                            | mA            |
| Enable Input Threshold Voltage – High<br>– Low                                                                                                                                                                                       | $V_{th_{enh}}$<br>$V_{th_{enl}}$ | 1.2<br>0              | –<br>–                       | 6.0<br>0.3                   | V             |
| Output Voltage Temperature Coefficient<br>( $I_{out} = 30\ \text{mA}$ , $-40^{\circ}\text{C} \leq T_A \leq 85^{\circ}\text{C}$ )                                                                                                     | $\Delta V_{out}/\Delta T$        | –                     | $\pm 100$                    | –                            | ppm/°C        |

TYPICAL CHARACTERISTICS




Figure 2. Output Voltage vs. Output Current




Figure 3. Output Voltage vs. Input Voltage




Figure 4. Quiescent Current vs. Input Voltage




Figure 5. Output Voltage vs. Temperature




Figure 6. Quiescent Current vs. Temperature




Figure 7. Quiescent Current vs. Temperature

TYPICAL CHARACTERISTICS




Figure 8. Dropout Voltage vs. Output Current




Figure 9. Dropout Voltage vs. Output Current




Figure 10. Dropout Voltage vs. Output Current




Figure 11. Ripple Rejection vs. Frequency





Figure 12. Ripple Rejection vs. Frequency

# NCP583



## TYPICAL CHARACTERISTICS



**Figure 13. Input Transient Response**  
 $(V_{out} = 2.8 V, I_{out} = 30 mA, tr = tf = 5.0 \mu s, C_{in} = 0)$

# NCP583


## TYPICAL CHARACTERISTICS



**Figure 14. Load Transient Response**  
( $V_{out} = 2.8$  V,  $t_r = t_f = 5.0 \mu s$ ,  $V_{in} = 3.8$  V)

# NCP583

## TYPICAL CHARACTERISTICS



**Figure 15. Load Transient Response**  
( $V_{out} = 2.8$  V,  $t_r = t_f = 5.0$   $\mu s$ ,  $V_{in} = 3.8$  V)

# NCP583

## APPLICATION INFORMATION

### Input Decoupling

A 1.0  $\mu\text{F}$  ceramic capacitor is the recommended value to be connected between  $V_{\text{in}}$  and GND. For PCB layout considerations, the traces of  $V_{\text{in}}$  and GND should be sufficiently wide in order to minimize noise and prevent unstable operation.

### Output Decoupling


It is recommended to use a 0.1  $\mu\text{F}$  ceramic capacitor on the  $V_{\text{out}}$  pin. For better performance, select a capacitor with low Equivalent Series Resistance (ESR). For PCB layout considerations, place the output capacitor close to the output pin and keep the leads short as possible.

## ORDERING INFORMATION

| Device        | Output Type / Features | Nominal Output Voltage | Marking | Package           | Shipping†          |
|---------------|------------------------|------------------------|---------|-------------------|--------------------|
| NCP583SQ15T1G | Active High w/Enable   | 1.5                    | A5      | SC-82AB (Pb-Free) | 3000 / Tape & Reel |
| NCP583SQ18T1G | Active High w/Enable   | 1.8                    | A8      | SC-82AB (Pb-Free) | 3000 / Tape & Reel |
| NCP583SQ25T1G | Active High w/Enable   | 2.5                    | B5      | SC-82AB (Pb-Free) | 3000 / Tape & Reel |
| NCP583SQ27T1G | Active High w/Enable   | 2.7                    | B7      | SC-82AB (Pb-Free) | 3000 / Tape & Reel |
| NCP583SQ28T1G | Active High w/Enable   | 2.8                    | B8      | SC-82AB (Pb-Free) | 3000 / Tape & Reel |
| NCP583SQ30T1G | Active High w/Enable   | 3.0                    | C0      | SC-82AB (Pb-Free) | 3000 / Tape & Reel |
| NCP583SQ33T1G | Active High w/Enable   | 3.3                    | C3      | SC-82AB (Pb-Free) | 3000 / Tape & Reel |
| NCP583XV15T2G | Active High w/Enable   | 1.5                    | G15B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV18T2G | Active High w/Enable   | 1.8                    | G18B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV25T2G | Active High w/Enable   | 2.5                    | G25B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV26T2G | Active High w/Enable   | 2.6                    | G26B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV28T2G | Active High w/Enable   | 2.8                    | G28B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV29T2G | Active High w/Enable   | 2.9                    | G29B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV30T2G | Active High w/Enable   | 3.0                    | G30B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV31T2G | Active High w/Enable   | 3.1                    | G31B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |
| NCP583XV33T2G | Active High w/Enable   | 3.3                    | G33B    | SOT-563 (Pb-Free) | 4000 / Tape & Reel |

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.


Other voltages are available. Consult your ON Semiconductor representative.



SCALE 4:1

SC-82AB  
CASE 419C-02  
ISSUE F

DATE 22 JUN 2012




NOTES:


1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. 419C-01 OBSOLETE. NEW STANDARD IS 419C-02.
4. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

| DIM | MILLIMETERS |      | INCHES    |       |
|-----|-------------|------|-----------|-------|
|     | MIN         | MAX  | MIN       | MAX   |
| A   | 1.80        | 2.20 | 0.071     | 0.087 |
| B   | 1.15        | 1.35 | 0.045     | 0.053 |
| C   | 0.80        | 1.10 | 0.031     | 0.043 |
| D   | 0.20        | 0.40 | 0.008     | 0.016 |
| F   | 0.30        | 0.50 | 0.012     | 0.020 |
| G   | 1.10        | 1.50 | 0.043     | 0.059 |
| H   | 0.00        | 0.10 | 0.000     | 0.004 |
| J   | 0.10        | 0.26 | 0.004     | 0.010 |
| K   | 0.10        | ---  | 0.004     | ---   |
| L   | 0.05 BSC    |      | 0.002 BSC |       |
| N   | 0.20 REF    |      | 0.008 REF |       |
| S   | 1.80        | 2.40 | 0.07      | 0.09  |

SOLDERING FOOTPRINT\*



GENERIC  
MARKING DIAGRAM\*



XXX = Specific Device Code  
M = Month Code  
▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

\*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

|                  |             |                                                                                                                                                                                     |
|------------------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ARB18939C | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SC-82AB     | PAGE 1 OF 1                                                                                                                                                                         |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.



**SOT-563-6 1.60x1.20x0.55, 0.50P**  
**CASE 463A**  
**ISSUE J**


DATE 15 FEB 2024

NOTES:

1. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5-2018.
2. ALL DIMENSION ARE IN MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.



| DIM | MILLIMETERS |      |      |
|-----|-------------|------|------|
|     | MIN.        | NOM. | MAX. |
| A   | 0.50        | 0.55 | 0.60 |
| b   | 0.17        | 0.22 | 0.27 |
| c   | 0.08        | 0.13 | 0.18 |
| D   | 1.50        | 1.60 | 1.70 |
| E   | 1.10        | 1.20 | 1.30 |
| e   | 0.50 BSC    |      |      |
| H   | 1.50        | 1.60 | 1.70 |
| L   | 0.10        | 0.20 | 0.30 |



RECOMMENDED MOUNTING FOOTPRINT\*

\* FOR ADDITIONAL INFORMATION ON OUR Pb-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERM/D.

STYLE 1:  
PIN 1. EMITTER 1  
2. BASE 1  
3. COLLECTOR 2  
4. EMITTER 2  
5. BASE 2  
6. COLLECTOR 1

STYLE 2:  
PIN 1. EMITTER 1  
2. EMITTER 2  
3. BASE 2  
4. COLLECTOR 2  
5. BASE 1  
6. COLLECTOR 1

STYLE 3:  
PIN 1. CATHODE 1  
2. CATHODE 1  
3. ANODE/ANODE 2  
4. CATHODE 2  
5. CATHODE 2  
6. ANODE/ANODE 1

STYLE 4:  
PIN 1. COLLECTOR  
2. COLLECTOR  
3. BASE  
4. EMITTER  
5. COLLECTOR  
6. COLLECTOR

STYLE 5:  
PIN 1. CATHODE  
2. CATHODE  
3. ANODE  
4. ANODE  
5. CATHODE  
6. CATHODE

STYLE 6:  
PIN 1. CATHODE  
2. ANODE  
3. CATHODE  
4. CATHODE  
5. CATHODE  
6. CATHODE

STYLE 7:  
PIN 1. CATHODE  
2. ANODE  
3. CATHODE  
4. CATHODE  
5. ANODE  
6. CATHODE


STYLE 8:  
PIN 1. DRAIN  
2. DRAIN  
3. GATE  
4. SOURCE  
5. DRAIN  
6. DRAIN

STYLE 9:  
PIN 1. SOURCE 1  
2. GATE 1  
3. DRAIN 2  
4. SOURCE 2  
5. GATE 2  
6. DRAIN 1

STYLE 10:  
PIN 1. CATHODE 1  
2. N/C  
3. CATHODE 2  
4. ANODE 2  
5. N/C  
6. ANODE 1

STYLE 11:  
PIN 1. EMITTER 2  
2. BASE 2  
3. COLLECTOR 1  
4. EMITTER 1  
5. BASE 1  
6. COLLECTOR 2

**GENERIC  
MARKING DIAGRAM\***



XX = Specific Device Code  
M = Month Code  
▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                         |                                        |                                                                                                                                                                                  |
|-------------------------|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON11126D</b>                     | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SOT-563-6 1.60x1.20x0.55, 0.50P</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)