



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		F I I	REVISED PER ECO-13-007522	03MAY2013	KH	MB



CE	13	TIN	7 9	MARK 4 TO 1	20.00	4	5-796640-4
	13	TIN	7 9	MARK 3 TO 1	15.00	3	5-796640-3
	13	TIN	7 9	MARK 1 TO 3	15.00	3	5-796640-2
	13 12	TIN	7 9	MARK 1 TO 3	15.00	3	5-796640-1
	13	TIN	7 9	MARK 1 TO 4	20.00	4	5-796640-0
	13	TIN	7 9	MARK 15 TO 28	70.00	14	4-796640-9
	13	TIN	7 9	MARK 13 TO 24	60.00	12	4-796640-8
		TIN	7 9	MARK 1 TO 14	70.00	14	4-796640-7
	13	TIN	8 9	MARK 1 TO 12	60.00	12	4-796640-6
	13	TIN	8 9	MARK 1 TO 7	35.00	7	4-796640-5
	13	TIN	8 9	MARK 1 TO 5	25.00	5	4-796640-4
		TIN	8 9	MARK 11 TO 15	25.00	5	4-796640-3
		TIN	-	DETAIL S	35.00	7	4-796640-2
		TIN	7 9	MARK 1 TO 3	15.00	3	4-796640-1
		TIN	-	10	20.00	4	4-796640-0
		TIN	7 9	DETAIL P	20.00	4	3-796640-9
		TIN	7 9	MARK 1 TO 8	40.00	8	3-796640-8
		TIN	7 9	MARK 37 TO 54	90.00	18	3-796640-7
		TIN	7 9	MARK 19 TO 36	90.00	18	3-796640-6
		TIN	7 9	MARK 1 TO 18	90.00	18	3-796640-5
		TIN	8 9	MARK 1 TO 10	50.00	10	3-796640-4
		TIN	8 9	MARK 1 TO 8	40.00	8	3-796640-3
		TIN	7	DETAIL N	30.00	6	3-796640-0
		TIN	7 9	MARK 1 TO 6	30.00	6	2-796640-9
		TIN	-	-	125.00	25	2-796640-5
		TIN	-	-	120.00	24	2-796640-4
		TIN	-	-	115.00	23	2-796640-3
		TIN	-	-	110.00	22	2-796640-2
		TIN	-	-	105.00	21	2-796640-1
		TIN	-	-	100.00	20	2-796640-0
		TIN	-	-	95.00	19	1-796640-9
		TIN	-	-	90.00	18	1-796640-8
		TIN	-	-	85.00	17	1-796640-7
		TIN	-	-	80.00	16	1-796640-6
		TIN	-	-	75.00	15	1-796640-5
		TIN	-	-	70.00	14	1-796640-4
		TIN	-	-	65.00	13	1-796640-3
		TIN	-	-	60.00	12	1-796640-2
		TIN	-	-	55.00	11	1-796640-1
		TIN	-	-	50.00	10	1-796640-0
		TIN	-	-	45.00	9	796640-9
		TIN	-	-	40.00	8	796640-8
		TIN	-	-	35.00	7	796640-7
		TIN	-	-	30.00	6	796640-6
		TIN	-	-	25.00	5	796640-5
	TIN	-	-	20.00	4	796640-4	
	TIN	-	-	15.00	3	796640-3	
	TIN	-	-	10.00	2	796640-2	
	TERMINAL PLATING	MARKING	SPECIAL	L	NO OF POSN	PART NUMBER	

1471-9 (3/11)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

1

A

A

GND

GND

B

B

DETAIL N

EMPTY CAVITIES

DETAIL S

1

2

3

4

DETAIL P

R

C

W

Y

B

G

DETAIL T

A

B

DETAIL U

12

11

10

9

8

7

6

5

4

3

2

1

DETAIL V

KEY

DETAIL W

DETAIL X

COM

S2

+20

COM

S1

+20

DETAIL Y

13

TIN

7

13

TIN

7

14

13

TIN

-

13

TIN

7

14

13

TIN

7

14

13

GOLD FLASH

-

13

TIN

7

13

TIN

7

13

TIN

7

9

13

TIN

7

9

TERMINAL PLATING

MARKING

SPECIAL

L

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±-

4 PLC ±-

ANGLES ±2

FINISH

MATERIAL

-

DWN S. WELDON 18OCT2000

CHK D. BLEVENOUR 18OCT2000

APVD D. BLEVENOUR 18OCT2000

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TERMINAL BLOCK, PLUG, STACKING

5.00mm PITCH

-

A200779

C-796640

SCALE 4:1

SHEET 2 OF 2

REV FILL

1

MATERIALS AND FINISH:

HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.

CLAMP: BRASS, NICKEL PLATED.

DOUBLE SIDE CONTACT SPRING: PHOSPHOR BRONZE, PLATING: SEE TABLE.

CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2.

END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.

3.

WIRE SIZE RANGE: 12-30 AWG.

4.

RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677.

5.

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

6.

NOT CUMULATIVE TOLERANCE

7.

INK MARKING: BLACK COLOR.

8.

INK MARKING: WHITE COLOR.

9.

NUMERICAL SEQUENCE: FROM LEFT TO RIGHT, WIRE ENTRY SIDE.

10.

RETENTION LATCHES REMOVED

11.

BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.

12.

WIRE ENTRY CLOSED.

13.

PRELIMINARY - NOT FOR PRODUCTION.

14.

NUMERICAL SEQUENCE: FROM RIGHT TO LEFT, WIRE ENTRY SIDE.

1471-9 (3/11)