

DATA SHEET

LEAD FREE CHIP RESISTORS

RC_P series ±0.5%, ±1%, ±5%

Sizes 0100/0201/0402/0603/0805/ 1206/1210/1218/2010/2512



YAGEO Phicomp



SCOPE

This specification describes RC series chip resistors with made by thick film process.

<u>APPLICATIONS</u>

• All general purpose application

FEATURES

- Total lead free without RoHS exemption
- Halogen Free Epoxy
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Saving of PCB space

ORDERING INFORMATION - GLOBAL PART NUMBER

Global part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

RC XXXX X X X XX XXXX P

(2) (3) (4) (5) (1)

(6)

(I) SIZE

0100/0201/0402/0603/0805/1206/1210/1218/2010/2512

(2) TOLERANCE

 $D = \pm 0.5\%$

 $F = \pm 1.0\%$

 $J = \pm 5.0\%$ (for jumper ordering, use code of J)

(3) PACKAGING TYPE

R = Paper taping reel

K = Embossed taping reel

S = ESD safe reel (0100 only)

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

- = Based on spec.

(5) TAPING REEL

07= 7 inch dia, Reel

13=13 inch dia. Reel

7N = 7 inch dia. Reel, ESD safe reel (0100 only)

(6) RESISTANCE VALUE

There are 2~4 digits indicated the resistance value.

Letter R/K/M is decimal point.

Example:

 $97R6 = 97.6\Omega$

 $9K76 = 9760\Omega$

 $IM = 1,000,000\Omega$

(7) DEFAULT CODE

Letter P is lead free (without RoHS exemption)

ORDERING EXAMPLE

The ordering code for a RC0402 0.0625W chip resistor value $100 \text{K}\Omega$ with ±5% tolerance, supplied in 7-inch tape reel of 10,000 units per reel is: RC0402JR-07100KP.




MARKING

RC0100 / RC0201 / RC0402



No Marking

RC0603



E24 series: 3 digits, 5%

First two digits for significant figure and 3rd digit for number of zeros

RC0805 / RC1206 / RC1210 / RC1218 / RC2010 / RC2512



E24/E96 series: 4 digits, 1%, 0.5%

First three digits for significant figure and 4th digit for number of zeros


Note

For further marking information, please see special data sheet "Chip resistors marking".

CONSTRUCTION

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added on each end to make the contacts to the thick film resistive element. The composition of the resistive element is a noble metal imbedded into a glass and covered by a second glass to prevent environmental influences. The resistor is laser trimmed to the rated resistance value. The resistor is covered with a protective epoxy coat, finally the two external terminations (matte tin on Nibarrier) are added, as shown in Fig.4.

Outlines





<u>DIMENSION</u>

 la	b	le	1

TYPE	L (mm)	W (mm)	H (mm)	I _I (mm)	I ₂ (mm)
RC0100	0.40±0.02	0.20±0.02	0.13±0.02	0.10±0.03	0.10±0.03
RC0201	0.60±0.03	0.30±0.03	0.23±0.03	0.10±0.05	0.15±0.05
RC0402	1.00±0.05	0.50±0.05	0.35±0.05	0.20±0.10	0.25±0.10
RC0603	1.60±0.10	0.80±0.10	0.45±0.10	0.25±0.15	0.25±0.15
RC0805	2.00±0.10	1.25±0.10	0.50±0.10	0.35±0.20	0.35±0.20
RC1206	3.10±0.10	1.60±0.10	0.55±0.10	0.45±0.20	0.40±0.20
RC1210	3.10±0.10	2.60±0.15	0.55±0.10	0.45±0.15	0.50±0.20
RC1218	3.10±0.10	4.60±0.10	0.55±0.10	0.45±0.20	0.40±0.20
RC2010	5.00±0.10	2.50±0.15	0.55±0.10	0.45±0.15	0.50±0.20
RC2512	6.35±0.10	3.10±0.15	0.55±0.10	0.60±0.20	0.50±0.20

ELECTRICAL CHARACTERISTICS

Table 2

		CHARACTERISTICS					
TYPE	resistance range	Operating Temperature Range	Max. Working Voltage	Max. Overload \ Voltage	Dielectric Vithstandin g Voltage	Temperature Coefficient of Resistance	Jumper Criteria
RC0100			15V	30V	30V	Ω≤R≤ 0Ω: -200~+600ppm/°C 10Ω <r≤ 00ω: °c<br="" ±370ppm=""> 100Ω<r≤ mω: td="" °c<="" ±250ppm=""><td>Rated Current 0.5A Max. Curren IA</td></r≤ mω:></r≤ 00ω:>	Rated Current 0.5A Max. Curren IA
RC0201	5% (E24) IΩ≦R≦22MΩ (0201: Max.10MΩ, 0100/1218: Max. IMΩ) I% (E24/E96) IΩ≦R≦10MΩ (0100/1218: Max. IMΩ)	–55 °C to +125 °C -	25V	50V	50V	Ω≤R≤10Ω: -100~+500ppm/°C 10Ω <r≤100ω: °c<br="" ±300ppm=""> 100Ω<r≤10mω: td="" °c<="" ±200ppm=""><td>Rated Current 0.5A Max. Curren IA</td></r≤10mω:></r≤100ω:>	Rated Current 0.5A Max. Curren IA
RC0402			50 V	100 V	100 V	IΩ≤R≤I0Ω: ±350ppm/°C I0Ω <r≤i00ω: °c<br="" ±200ppm="">I00Ω<r≤i0mω: °c<br="" ±150ppm="">I0MΩ<r≤22mω: td="" °c<="" ±200ppm=""><td>Rated Current IA Max. Current 2A</td></r≤22mω:></r≤i0mω:></r≤i00ω:>	Rated Current IA Max. Current 2A
RC0603		201: Max10MΩ, 0100/1218:	75V	150 V	150 V	$\begin{split} & \Omega \leq R \leq 10\Omega: \pm 300 \text{ppm/}^{\circ}\text{C} \\ & 0\Omega < R \leq 100\Omega: \pm 200 \text{ppm/}^{\circ}\text{C} \\ & 00\Omega < R \leq 10M\Omega: \pm 150 \text{ppm/}^{\circ}\text{C} \\ & 0M\Omega < R \leq 22M\Omega: \pm 200 \text{ppm/}^{\circ}\text{C} \end{split}$	Rated Current IA Max. Current 2A
RC0805		_	150 V	300 V	300 V	Ω≤R≤ 0Ω: ±300ppm/°C 0Ω <r≤ 00ω: °c<br="" ± 50ppm=""> 10Ω<r≤ 0mω: °c<br="" ± 100ppm=""> 10MΩ<r≤22mω: td="" °c<="" ±200ppm=""><td>Rated Current 2A Max. Current 5A</td></r≤22mω:></r≤ 0mω:></r≤ 00ω:>	Rated Current 2A Max. Current 5A
RC1206	0.5% (E24/E96) 10Ω≦R≦1MΩ	–55 °C to +155 °C	200 V	400 V	500 V		Rated Current 2A Max. Current 10A
RC1210	Jumper<50mΩ	_					Rated Current 2A Max. Current 10A
RC1218							Rated Current 6A Max. Current 10A
RC2010			200V	500 V	500V		Rated Current 2A Max. Current 10A
RC2512						_	Rated Current 2A Max. Current 10A

FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please refer to data sheet "Chip resistors mounting"

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION		RC0201	RC0402	RC0603	RC0805	RC1206	RC1210	RC1218	RC2010	RC2512
Paper taping reel (R)	7" (178 mm)	20,000	10,000	10,000	5,000	5,000	5,000	5,000			
	13" (330 mm)	80,000	50000	50000	20000	20000	20000	20000			
ESD safe reel (S)	7" (178 mm)	40,000									
Embossed taping ree	el 7" (178 mm)								4,000	4,000	4,000

NOTE

For tape and reel specification/dimensions, please refer to data sheet "Chip resistors packing".

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

RC0402 to RC2512 Range: -55°C to +155°C (Fig. 5-1)

RC0100 to RC0201 Range: -55°C to +125°C (Fig. 5-2)

POWER RATING

Each type rated power at 70 °C:

RC0100=1/32W

RC0201=1/20 W

RC0402=1/16 W

RC0603=1/10W

RC0805=1/8W

RC1206=1/4W

RC1210=1/2W

RC1218=1W

RC2010=3/4W

RC2512=1W

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:


$$V = \sqrt{(PxR)}$$


Where

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

 $R = Resistance value (\Omega)$





a function of the operating ambient temperature (Tamb)

8

TESTS AND REQUIREMENTS

Table 8 Test condition, procedure and requirements

TEST TEST METHOD PROCEDURE		PROCEDURE	REQUIREMENTS		
Temperature Coefficient of Resistance (T.C.R.)	IEC 60115-1 4.8	At +25/–55 °C and +25/+125 °C Formula:	Refer to table 2		
(1.C.K.)		T.C.R= $\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$			
		Where t_1 =+25 °C or specified room temperature t_2 =-55 °C or +125 °C test temperature			
		R_1 =resistance at reference temperature in ohms			
		R_2 =resistance at test temperature in ohms			
Life/ Endurance	MIL-STD-202G Method 108A IEC 60115-1 4.25.1	At 70±5°C for 1,000 hours; RCWV applied for 1.5 hours on and 0.5 hour off, still air required	$\pm (1\% + 0.05 \Omega$) for D/F tol $\pm (3\% + 0.05 \Omega$) for J tol <100mR for jumper		
High Temperature Exposure	MIL-STD-202G Method 108A IEC 60115-1 4.25.3	I,000 hours at maximum operating temperature depending on specification, unpowered.	$\pm (1\% + 0.05\Omega)$ for D/F tol $\pm (2\% + 0.05\Omega)$ for J tol <50mR for jumper		
Moisture Resistance	MIL-STD-202G Method 106F IEC 60115-1 4.24.2	Each temperature / humidity cycle is defined at 8 hours (method 106F), 3 cycles / 24 hours for 10d with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered Parts mounted on test-boards, without condensation on parts	$\pm (0.5\% + 0.05\Omega$) for D/F tol $\pm (2\% + 0.05\Omega$) for J tol $<$ 100mR for jumper		
Humidity	IEC 60115-1 4.37	Steady state for 1000 hours at 40 °C / 95% R.H. RCWV applied for 1.5 hours on and 0.5 hour off	$\pm (1\% + 0.05\Omega)$ for D/F tol $\pm (2\% + 0.05\Omega)$ for J tol < 100mR for jumper		
Thermal Shock	MIL-STD-202G Method 107G	-55/+125°C Note Number of cycles required is 300 Devices mounted Maximum transfer time is 20 seconds Dwell time is 15 minutes. Air - Air	$\pm (0.5\% + 0.05 \Omega$) for D/F tol $\pm (1\% + 0.05 \Omega$) for J tol <50mR for jumper		
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV or maximum overload voltage which is less for 5 seconds at room temperature	\pm (1%+0.05 Ω) for D/F tol \pm (2%+0.05 Ω) for J tol <50mR for jumper No visible damage		
Board Flex/ Bending	IEC 60115-1 4.33	Device mounted or as described only I board bending required bending time: 60±5 seconds 0100/0201/0402:5mm; 0603/0805:3mm; 1206 and above:2mm	$\pm (1\% + 0.05 \Omega)$ for D/F/J Tol <50mR for jumper No visible damage		

7	
8	

 Chip Resistor Surface Mount
 RC_P
 SERIES
 0100 to 2512

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS	
Solderability - Wetting	IPC/JEDECJ-STD-002B test B IEC 60068-2-58	Electrical Test not required Magnification 50X SMD conditions: Ist step: method B, aging 4 hours at 155 °C dry heat 2nd step: leadfree solder bath at 245±3 °C Dipping time: 3±0.5 seconds	W ell tinned (>95% covered) No visible damage	
-Leaching	IPC/JEDECJ-STD-002B test D IEC 60068-2-58	Leadfree solder ,260°C, 30 seconds immersion time	No visible damage	
-Resistance to Soldering Heat	MIL-STD-202F Method 210F IEC 60068-2-58	Condition B, no pre-heat of samples Leadfree solder, $260 ^{\circ}\text{C} \pm 5^{\circ}\text{C}$, 10 ± 1 seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	$\pm (0.5\% + 0.05\Omega$) for D/F tol $\pm (1\% + 0.05\Omega$) for J tol $<$ 50mR for jumper No visible damage	

YAGEO Phicomp

Chip Resistor Surface Mount RC_P SERIES 0100 to 2512

Product specification

8 8

REVISION HISTORY

REVISION DATE CHANGE NOTIFICATION DESCRIPTION

Version 0 Aug. 22, 2014 - - First issue of this specification

[&]quot;Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."