

TO-18 2 Leads, Clear Lens - 140 deg Angle

INDEX

PRODUCT TREE



SPEC! Image next to part no. indicates cad file.

- [Product Table](#)
- [Table Footnotes](#)
- [Order Samples](#)
- [Stock/Price Request](#)
- [Sales and Tech Support](#)

1. [Product Gallery](#)
2. [Opto-Electronic Components](#)
3. [Phototransistors](#)
4. [TO-18 Metal Can Packages](#)
5. [TO-18 2 Leads, Clear Lens - 140 deg Angle](#)

Lumex drawings are in PDF format. If you don't have Adobe Acrobat, click on this icon to

[download a free copy](#)



Lumex Part Number	Lens	Vceo (V) Max *	PC (mW) Max *	t-opr (deg C) *	Iceo @ 10 Vceo (nA) Max	Ic (mA) Min **	Ic (mA) Typ **	Ic (mA) Max **	Vce (V) **	lambda p (nm) Typ.	delta theta deg Typ.	lambda (nm)	tr/ta @ Vec 5V Ic 1ma
OED-ST-1MLA SPEC!	Clear Lens	40	100	- 25 ; + 85	100	-	2	-	5	880	+/- 70	550 ; 1050	8/10 mS

Table Footnotes

[\[top of page\]](#)

- * Limits of Safe Operation
- ** @ EV ~ 1000 Lx

[Home](#) |
 [What's New](#) |
 [Product Gallery](#) |
 [Product Search](#) |
 [X-Ref Search Engine](#) |
 [Tech Notes](#) |
 [Sales and Tech Support](#) |
 [Corporate Info](#)

290 East Helen Road Palatine, IL 60067 Telephone: (847) 359-2790 Facsimile: (847) 359-8904 E-mail us at

sales@lumex.com

© 1997-2001 Lumex, Inc.