





	1	2	3	4	5	6	7																																																																																																			
A	 NOTES Material 1.Terminal body(contact pin): Brass(CuZn) Tin plated 2.Insulator (housing): Thermoplastic (UL94V-0),Green Electrical cULus/CSA/VDE/TUV 1.Voltage rating: 300VAC/250VAC/300VAC/300VAC 2.Current rating: 20A/15A/20A/20A 3.Wire range: 4.Solid wire(AWG): 5.Stranded wire(AWG): 6.Withstanding Voltage: 1.6KV/1.6KV/2.5KV/2.5KV 7.Operating temperature: -40°C to +115°C 8.Soldering temperature: 250°C±10°C/5 Sec 9.Safety Approval:    							A																																																																																																		
B								B																																																																																																		
C	 N = Number of contacts RoHS compliant <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>04.05.2009</td><td>Dean</td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td></td><td></td><td>Approved</td><td>04.05.2009</td><td>Hellwig</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±1°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X°</td><td>±X°</td><td>①</td><td>Drawn</td><td>04.05.2009</td><td>Dean</td><td colspan="2" rowspan="2"></td><td>ASSMANN WSW-No. A-TB508-OQxxCV</td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td>Drawing-No. ASS 3502 CO</td><td>rev01</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>Replace</td><td>Sheet</td></tr></table>							Scale	1:1						Date	Name	Customer-No.	TOLERANCE							Drawn	04.05.2009	Dean	X.	±0.50						Approved	04.05.2009	Hellwig	X.X	±0.30									X.XX	±0.10									DIM	TOL									X.°	±1°									X.X°	±X°	①	Drawn	04.05.2009	Dean			ASSMANN WSW-No. A-TB508-OQxxCV		Angle	TOL	Id.	Modification	Date	Name	Drawing-No. ASS 3502 CO	rev01									Replace	Sheet	C
Scale	1:1						Date	Name	Customer-No.																																																																																																	
TOLERANCE							Drawn	04.05.2009	Dean																																																																																																	
X.	±0.50						Approved	04.05.2009	Hellwig																																																																																																	
X.X	±0.30																																																																																																									
X.XX	±0.10																																																																																																									
DIM	TOL																																																																																																									
X.°	±1°																																																																																																									
X.X°	±X°	①	Drawn	04.05.2009	Dean			ASSMANN WSW-No. A-TB508-OQxxCV																																																																																																		
Angle	TOL	Id.	Modification	Date	Name			Drawing-No. ASS 3502 CO	rev01																																																																																																	
								Replace	Sheet																																																																																																	
D								D																																																																																																		
E								E																																																																																																		
F								F																																																																																																		
G								G																																																																																																		
H								H																																																																																																		
	1	2	3	4	5	6	7	SV1482																																																																																																		