

PRODUCT NUMBER
73306-XXXLF

PLATING OPTION
1= GXT 0.76 μm
3= GOLD 0.76 μm
5= GOLD 1.27 μm


PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG

TERMINAL LOADING
1= FULLY LOADED

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.

NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXCEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.








CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		MOD JACK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
H	F05-0247	DLE	05.09.12	angles	linear	mm	SMT RA JACK
J	F06-0240	DLE	06.07.18				4 POS NARROW OUTSIDE
K	F09-0070	LSA	09.07.23	±2'		scale 2:1	
L	B-15798	JFA	13.09.09	dr	D LEGRAND	04.10.18	dwg no
M	F-21888	AMA	15.09.09	enr	P NIZZI	04.10.18	sheet 1 of 3
				chr	D LEGRAND	04.10.18	size
G	F04-0363	DLE	04.10.18	appd	P NZ	04.10.18	73306 A3
sheet				revision	M	F	B
index				sheet	1	2	3



PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	280
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3

CUSTOMER COPY FOR REFERENCE ONLY


mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		MOD-JACK
ltr	ecn no	dr	date	title
E	F90120	DLE	99.02.01	SMT RA JACK
F	F06.0240	DLE	06.07.18	4 POS. NARROW OUTSIDE
			angles	scale 1:1
			linear	
			dr	D LEGRAND 06.07.18
			enrg	P NIZZI 06.07.18
			chr	D LEGRAND 06.07.18
			appd	P NIZZI 06.07.18
sheet index	revision sheet			dwg no
				73306
				type
				CUSTOMER Drawing





FCIconnect.com

Copyright FCI



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406 ISO 1101				MOD JACK	
ltr		ecr no		date		tolerances unless otherwise specified		title	
A		F04.0363		DLE 04.10.18		±0.13		SMT RA JACK	
B		F06-0240		DLE 06.07.18		mm		4 POS NARROW OUTSIDE	
				angles		linear		scale 2:1	
				±2°					
				dr		D LEGRAND		04.10.18	
				engr		P NIZZI		04.10.18	
				chr		D LEGRAND		04.10.18	
				appd		P NZ		04.10.18	
sheet		revision						dwg no	
index		sheet						sheet 3 of - size	
								73306 A4	
								type	
								CUSTOMER Drawing	

form: A4