


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		B1	REVISED PER ECO-11-004917	11MAR11	RK HMR

CONVERSION CHART	
INCH	MM
.010	0,25
.020	0,51
.030	0,76
.040	1,01
.100	2,54
.105	2,67
.110	2,79
.130	3,30
.200	5,08
.206	5,23
.220	5,59
.320	8,13
.360	9,14
.380	9,65
.400	10,16



SPECIFICATIONS:


MATERIALS:
CASE: LCP, 94V-0.
ACTUATOR: PBT, 94V-0.
MOVING CONTACT: COPPER, GOLD PLATE OVER NICKEL.
FIXED CONTACT/TERMINAL: COPPER, GOLD PLATE OVER NICKEL.

ELECTRICAL:
CONTACT RATING: 0.4 VA MAX. @ 20 VDC OR PEAK AC.
INITIAL CONTACT RESISTANCE: 20 MILLIOHMS MAX. @ 100 MV & 1 MA.
INSULATION RESISTANCE: 1,000 M. MIN. AT 500 VDC.
DIELECTRIC STRENGTH: 1000 VOLTS RMS AT SEA LEVEL.
LIFE: 60,000 - 80,000 CYCLES.

MECHANICAL:
ACTUATION FORCE: (EG OPTION ONLY)
LEFT TO CENTER & RIGHT TO CENTER: 160 TO 665 GRAMS WITH AN AVERAGE OF 412 GRAMS WHILE UTILIZING A 3 SIGMA VARIATION.
CENTER TO RIGHT & CENTER TO LEFT: 170 TO 685 GRAMS WITH AN AVERAGE OF 428 GRAMS WHILE UTILIZING A 3 SIGMA VARIATION.

ENVIRONMENTAL:
OPERATING TEMPERATURE: -4°F TO +176°F (-20°C TO +80°F).
STORAGE TEMPERATURE: -4°F TO +176°F (-20°C TO +80°F).

- NOTES:**
- 1. INTERPRET DRAWING PER ASME Y14.5M-1994.
 - 2. SOLDERABILITY PER EIA 364-52, CLASS 2, CATEGORY 1



** CENTER TERMINAL NOT FURNISHED WITH A & K ACTION CODES.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 06SEP2007		 TE Connectivity							
		CHK M SARVER 06SEPT2007									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		APVD M SARVER 06SEP2007		SLIDE SWITCH							
		PRODUCT SPEC									
		APPLICATION SPEC									
MATERIAL -		FINISH		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		-		A2		00779		C=1437579-8		-	
		CUSTOMER DRAWING		SCALE		4:1		SHEET		1 of 1	
										B1	