








LOC		DIST	P		ZONE	LTR	REVISIONS		
CM	52						DESCRIPTION	DATE	APPD
						J	REV & REDWN PER EC 0730-0059-95	3-21-95	KS RS

- 1 WIRE RANGE: 0.13-0.8mm² (26-18 AWG).
- 2 INSULATION RANGE: 1.27-2.92 [.050-.115] MAX. DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 TIP PLATE WITH 0.00076-0.00091 [.000030-.000036] MIN GOLD IN THE LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES: ON: 2 PLC DEC ±0.13 [.005] 3 PLC DEC ±- ANGLES ± -		DR 3-21-95 K. SALMON	AMP Incorporated Harrisburg, PA 17105-3608	
CHK 3-21-95 R. SWING		APPD 3-21-95 W. LONG	NAME	
MATERIAL		APPD 3-21-95 W. LONG	MR GROUNDING PIN	
SEE TABLE		PRODUCT SPEC	-	
FINISH		APPLICATION SPEC	-	
SEE TABLE		WEIGHT	-	
GOLD PLATE		0.20 [.008] PH05 BRZ	350969-2	
PRE-TIN		0.20 [.008] PH05 BRZ	350969-1	
FINISH		MATERIAL	PART NO	
SIZE		CAGE CODE	DRAWING NO	
D		00779	C=350969	
SCALE		5:1	SHEET	
			1 OF 1	

CUSTOMER DRAWING