




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		D	REVISED PER ECO-12-015665	26SEP12	KH	MZ



- 1 NYLON, UL 94V-0 RATED, BLACK.
- 2 STAINLESS STEEL.
- 3 BRASS.
- 4 CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN-LEAD OVER 1.27um [.000050] MIN NICKEL.
- 5 RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST = 0.89±0.08 [.035±.003] DIA..
- 6 CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END. GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN OVER 1.27um [.000050] MIN NICKEL.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	6	YES	213855-4
	6	NO	213855-3
7 OBSOLETE	4	YES	213855-2
	4	NO	213855-1
FINISH		THREADED INSERTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D.HARDY
01-03-95

CHK
R.STONE
01-09-95

APVD
-

PRODUCT SPEC
108-10024

APPLICATION SPEC
114-10038

WEIGHT
-

CUSTOMER DRAWING

RECEPTACLE ASSEMBLY, POSTED,
STANDARD SEX, 17-16, CPC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=213855

RESTRICTED TO
-


SCALE
2:1

SHEET
1 of 2

REV
D

1471-9 (3/11)

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		—	SEE SHEET 1	—	—	—



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL:
HOUSING:
CONTACT SPRING:
CONTACT BODY & POST:

1

2

3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.25 [.010]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

4

DWN
D.HARDY
01-03-95

CHK
R.STONE
01-09-95

APVD
-

PRODUCT SPEC
108-10024

APPLICATION SPEC
114-10038

WEIGHT
-

CUSTOMER DRAWING

NAME

RECEPTACLE ASSEMBLY, POSTED,
STANDARD SEX, 17-16, CPC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=213855

RESTRICTED TO
-

SCALE
2:1

SHEET
2 OF 2

REV
D

TE Connectivity