

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2004.

© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
JDIST
/

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

A1

REVISED PER ECO-10-000444







19JAN10

KK

HMR

40,60 POS

30,50 POS



- 1 USE A P.C.B. WHOSE ARE TREATED WITH SOLDER RESIST.
- 2 SHOW P.C.B LAYOUT FROM ON BOARD SURFACE SIDE.
- 3 NUMBER THE CONTACT IN THE P.C.B OR CONNECTOR CONSECUTIVELY FROM "DATUM" SIDE.
- 4 THE RETENTION LEG IS A TEMPORARY FIX BEFORE SOLDERING
- 5 HOUSING MATERIAL : P.B.T(UL94V-0) / BLACK
- 6 CONTACT MATERIAL : PHO-BRONZE
- 7 CONTACT FINISH : NICKEL 0.00127 MIN THK. OVERALL SELECTIVE GOLD 0.00076 MIN OR 0.0002 MIN. THK ON CONTACT AREA AND TIN 0.001 MIN THK. ON TINE AREA.
- 8 RETENTION LEG FINISH:0.002 MIN TIN PL. OVER 0.001 MIN NICKEL PL.
- 9 RETENTION LEG MATERIAL:BRASS
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

Au PL. 0.00076 MIN.	6-	-3	50	24	30.48	36.45	37.88	41.79
	6-	-2	40	19	24.13	30.10	31.53	35.44
	6-	-1	30	14	17.78	23.75	25.18	29.09
Au PL. 0.0002 MIN.		-4	60	29	36.83	42.80	44.23	48.14
		-3	50	24	30.48	36.45	37.88	41.79
		-2	40	19	24.13	30.10	31.53	35.44
	5174218-1		30	14	17.78	23.75	25.18	29.09
REMARK	PART NUMBER	POS	n	A	B	C	D	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
COREL WANG

20AUG04

CHK
STEVEN YAO

20AUG04

APVD
I.ENOMOTO

20AUG04

PRODUCT SPEC

108-60036

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki,JapanNAME
CAP ASSY (HORIZONTAL / W/LEG)
AMPLIMITE .050 SERIES I B-TO-B CONN.SIZE
A3CAGE CODE
00779DRAWING NO
C-5174218

RESTRICTED TO

GENERAL TOLERANCE

10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

DIMENSIONS:
MM

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL
SEE NOTE 5, 6, 9

SEE NOTE 7, 8