

International
IOR Rectifier

QUIETIR Series 30EPF12PbF, 30CPF12PbF

**FAST SOFT RECOVERY
RECTIFIER DIODE**
Lead-Free ("PbF" suffix)

	$V_F < 1.41V @ 30A$
	$t_{rr} = 95 \text{ ns}$
	$V_{RRM} = 1200V$

Description/ Features

The 30EPF12PbF & 30CPF12PbF soft recovery *QUIETIR* rectifier series has been optimized for combined short reverse recovery time and low forward voltage drop.

The glass passivation ensures stable reliable operation in the most severe temperature and power cycling conditions.


Typical applications are:

- Output rectification and freewheeling in inverters, choppers and converters
- and input rectifications where severe restrictions on conducted EMI should be met.
- 30CPF series is a drop in replacement for 25CPF Series (parallel connection only)

Major Ratings and Characteristics

Characteristics	Values	Units
$I_{F(AV)}$ Sinusoidal waveform	30	A
V_{RRM}	1200	V
I_{FSM}	350	A
$V_F @ 30A, T_J = 25^\circ C$	1.41	V
$t_{rr} @ 1A, 100A/\mu s$	95	ns
T_J	-40 to 150	$^\circ C$

Package Outline



Voltage Ratings

Part Number	V_{RRM} , maximum peak reverse voltage V	V_{RSM} , maximum non repetitive peak reverse voltage V	I_{RRM} 150°C mA
30EPF12PbF, 30CPF12PbF	1200	1300	6

Absolute Maximum Ratings

Parameters	30.PF..	Units	Conditions
$I_{F(AV)}$ Max. Average Forward Current	30	A	@ $T_C = 95^\circ\text{C}$, 180° conduction half sine wave
I_{FSM} Max. Peak One Cycle Non-Repetitive Surge Current	300	A	10ms Sine pulse, rated V_{RRM} applied
	350		10ms Sine pulse, no voltage reapplied
I^2t Max. I^2t for fusing	450	A^2s	10ms Sine pulse, rated V_{RRM} applied
	636		10ms Sine pulse, no voltage reapplied
$I^2\sqrt{t}$ Max. $I^2\sqrt{t}$ for fusing	6360	$A^2\sqrt{s}$	$t = 0.1$ to 10ms, no voltage reapplied


Electrical Specifications

Parameters	30.PF..	Units	Conditions
V_{FM} Max. Forward Voltage Drop	1.41	V	@ 30A, $T_J = 25^\circ\text{C}$
r_t Forward slope resistance	10.09	$m\Omega$	$T_J = 150^\circ\text{C}$
$V_{F(TO)}$ Threshold voltage	0.992	V	
I_{RM} Max. Reverse Leakage Current	0.1	mA	$T_J = 25^\circ\text{C}$
	6		$T_J = 150^\circ\text{C}$

$V_R = \text{rated } V_{RRM}$

Typical Recovery Characteristics

Parameters	30.PF..	Units	Conditions
t_{rr} Reverse Recovery Time	450	ns	$I_F @ 30\text{Apk}$ @ 25A/ μs @ 25°C
I_{rr} Reverse Recovery Current	6.1	A	
Q_{rr} Reverse Recovery Charge	2.16	μC	
S Snap Factor t_b/t_a	0.6	typical	



Thermal-Mechanical Specifications

Parameters			30.PF..	Units	Conditions
T _j	Max. Junction Temperature Range		- 40 to 150	°C	
T _{stg}	Max. Storage Temperature Range		- 40 to 150	°C	
R _{thJC}	Max. Thermal Resistance Junction to Case		0.8	°C/W	DC operation
R _{thJA}	Max. Thermal Resistance Junction to Ambient		40	°C/W	
R _{thCS}	Typical Thermal Resistance, Case to Heatsink		0.2	°C/W	Mounting surface , smooth and greased
wt	Approximate Weight		6 (0.21)	g (oz.)	
T	Mounting Torque	Min.	6 (5)	Kg-cm (lbf-in)	
		Max.	12 (10)		
Case Style			TO-247AC		JEDEC (Modified)
Marking Device			30EPF12,30CPF12		




Fig. 1 - Current Rating Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 4 - Forward Power Loss Characteristics

30EPF12PbF, 30CPF12PbF *QUIETIR* Series

Bulletin I2170 10/04

International
IOR Rectifier




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - Forward Voltage Drop Characteristics




Fig. 8 - Recovery Time Characteristics, $T_J = 25^\circ\text{C}$




Fig. 9 - Recovery Time Characteristics, $T_J = 150^\circ\text{C}$




Fig. 10 - Recovery Charge Characteristics, $T_j = 25^\circ\text{C}$




Fig. 11 - Recovery Charge Characteristics, $T_j = 150^\circ\text{C}$




Fig. 12 - Recovery Current Characteristics, $T_j = 25^\circ\text{C}$




Fig. 13 - Recovery Current Characteristics, $T_j = 150^\circ\text{C}$





Fig. 14 - Thermal Impedance Z_{thJC} Characteristics

30EPF12PbF, 30CPF12PbF *QUIETIR* Series


Bulletin I2170 10/04

International
IOR Rectifier

Outline Table



Marking Information



Ordering Information Table

Device Code					
30	E	P	F	12	PbF
1	2	3	4	5	6
1	-	Current Rating (30 = 30A)			
2	-	Circuit Configuration:			
		E = Single Diode			
		C = Single Diode, 3 pins			
3	-	Package:			
		P = TO-247AC (Modified)			
4	-	Type of Silicon:			
		F = Fast Recovery			
5	-	Voltage Rating (12 = 1200V)			
6	-	• none = Standard Production • PbF = Lead-Free			

30EPF12PbF, 30CPF12PbF *QUIETIR* Series

Bulletin I2170 10/04

International
IOR Rectifier

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level and Lead-Free.
Qualification Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
10/04



Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.