


| LOC | DIST | REVISIONS |     |                       |         |     |      |
|-----|------|-----------|-----|-----------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION           | DATE    | DWN | APVD |
|     |      |           | U   | REV PER ECO 13-009837 | 6-13-13 | CT  | DM   |
|     |      |           |     |                       |         |     |      |
|     |      |           |     |                       |         |     |      |



-  COLOR CODE: AS SHOWN IN APPROXIMATE LOCATION SHOWN.  
THE YELLOW BAND SHALL BE APPROXIMATELY TWICE THE WIDTH OF  
THE ORANGE BAND.
-  ELECTRICAL ENGAGEMENT POINT.
-  THIS AREA SOLDER DIPPED.
-  MANUFACTURERS LOGO; LACATION & ORIENTATION OPTIONAL.
-  SOLDER IS RoHS-COMPLIANT Sn.

|                                                                                                                                                                             |                 |           |             |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-----------|-------------|
| --                                                                                                                                                                          | .776            | .079-.083 | 3-448140-0  |
|                                                                                        | .617 $\pm$ .010 | .087 MAX  | 2-448140-7  |
| --                                                                                                                                                                          | .576            | .079-.083 | 2-448140-6  |
|   | .617            | .087 MAX  | 2-448140-3  |
| --                                                                                                                                                                          | .606            | .079-.083 | 2-448140-2  |
|                                                                                        | .651            | .087 MAX  | 1-448140-9  |
| --                                                                                                                                                                          | .505            | .079-.083 | 1-448140-8  |
| --                                                                                                                                                                          | .617            | .079-.083 | 1-448140-5  |
| --                                                                                                                                                                          | .404            | .079-.083 | 1-448140-2  |
|                                                                                        | .536            | .087 MAX  | 448140-9    |
| --                                                                                                                                                                          | .415            | .079-.083 | 448140-8    |
| --                                                                                                                                                                          | .651            | .079-.083 | 448140-6    |
| --                                                                                                                                                                          | .536            | .079-.083 | 448140-3    |
| --                                                                                                                                                                          | .536            | .079-.083 | 448140-2    |
| REMARKS                                                                                                                                                                     | DIM G           | DIM F     | PART NUMBER |

|                                                                                                                                                                                        |  |                                                                                |                                     |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------|-------------------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                                                                                                 |  | DWN<br>C.C. THOMAS<br>CHK<br>K. THACKSTON<br>APVD<br>K. THACKSTON              | 27OCT2009<br>27OCT2009<br>27OCT2009 |
| DIMENSIONS:<br>INCHES                                                                                                                                                                  |  | NAME<br>POSTED PIN CONTACT, SIZE 12,<br>ARINC 600                              |                                     |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC $\pm$ .010<br>1 PLC $\pm$ .005<br>2 PLC $\pm$ .005<br>3 PLC $\pm$ .005<br>4 PLC $\pm$ .005<br>ANGLES $\pm$ .010<br>FINISH SEE CALLOUTS |  | PRODUCT SPEC<br>APPLICATION SPEC<br>WEIGHT<br>CUSTOMER DRAWING                 |                                     |
| MATERIAL<br>SEE CALLOUTS                                                                                                                                                               |  | SIZE<br>A1<br>CAGE CODE<br>00779<br>DRAWING NO<br>448140<br>RESTRICTED TO<br>- |                                     |
| SCALE<br>12:1                                                                                                                                                                          |  | SHEET<br>1<br>OF<br>1<br>REV<br>U                                              |                                     |