






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
CM	00	J		REVISED PER 063B-0144-04	17JUN04	KW


1. INSULATION RANGE- 4.57 [.180] MAX DIA.
WIRE RANGE- 0.6-2mm² [20-14] AWG.
2. NOT RECOMMENDED FOR USE IN 1,5,6,9,12,&15
POSITION STANDARD 2.36 [.093] COMMERCIAL PIN &
SOCKET HOUSINGS WITH INSULATION DIAMETERS GREATER
THAN 4.06 [.160].
3. DIMENSIONS IN BRACKETS ARE IN INCHES.




SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1



SECTION D-D
SCALE 10:1

METRIC

770530-1
PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN K. WHITAKER	17JUN04		Tyco Electronics Corporation Greensboro, NC 27409				
DIMENSIONS: mm [INCHES]			CHK D. COLEY	17JUN04		NAME .093 PIN, COMMERCIAL PIN AND SOCKET				
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROD D. COLEY					
			0 PLC ± -		PRODUCT SPEC					
			1 PLC ± -							
			2 PLC ± -							
			3 PLC ± .005							
MATERIAL -			4 PLC ± -		APPLICATION SPEC					
			ANGLES FINISH ± 0°30'							
			WEIGHT		SIZE					
			-		CAGE CODE					
					DRAWING NO					
					RESTRICTED TO					
					A1 00779 ©770530					
			CUSTOMER DRAWING			SCALE 5:1 SHEET 1 OF 1 REV J				