


SPECIFICATIONS

Material: Boot: APM-RUBRGLAS (transparent silicone rubber) conforms to A-A-59588, Class III Grade 50.
Temperature Range: HEXSEALS: -94°F to +400°F
Pressure Range: Dust tight and splashproof.
Resistant to: Salt spray, weather, sunlight, ozone, corona and most acids.
Shelf Life: Excess of 25 years.
Operational Life: 10,000 actuations, minimum.

Notes:

1. Mounting screws are supplied in lengths shown unless otherwise specified.
2. New sizes and types of RUBRGLAS-SEELS® are being added regularly. Please request other types and styles as required.

Agency Recognition: Front Panel mounted Circuit Breaker Boots are UL-listed to UL Std. 50, types 1, 2, 3, 12, 12K, and 13. Back-of-Panel mounted Circuit Breaker boots are UL-listed to UL Std. 50, type 1. Also meet CSA standards.



REV.	DESCRIPTION	DATE
B	MAT'L CHANGED and WALL THICKNESS TOL. CHANGED FROM 0.010" to 0.005	12-18-09
A	CAD COMPUTER GENERATED	1-3-03
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.		
MAT'L: APM RUBRGLASS® CONFORMS TO A-A-59588, CL III	TITLE: CIRCUIT BREAKER BOOT - BACK-OF-PANEL MOUNTED	ENG. DWN. CARBONE 6-13-69
FINISH: GRADE 50 CLEAR	APM-HEXSEAL CORPORATION	CHKD. SCALE 3 : 2 DWG. NO. 1113/42

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
 THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[1113/42](#)