

Metallized Polyester (PET) Capacitors in PCM 5 mm

Special Features

- High volume/capacitance ratio
- Self-healing
- According to RoHS 2011/65/EC

Typical Applications

For general DC-applications e.g.

- By-pass
- Blocking
- Coupling and decoupling
- Timing

Construction


Dielectric:

Polyethylene-terephthalate (PET) film

Capacitor electrodes:

Vacuum-deposited

Internal construction:



Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

Terminations:

Tinned wire.

Marking:

Colour: Red. Marking: Silver/White.
Epoxy resin seal: Red

Electrical Data

Capacitance range:

0.01 μF to 10 μF (E12-values on request)

Rated voltages:

50 VDC, 63 VDC, 100 VDC, 250 VDC,
400 VDC, 630 VDC

Capacitance tolerances:

$\pm 20\%$, $\pm 10\%$, $\pm 5\%$

Operating temperature range:

-55°C to $+100^\circ\text{C}$ ($+125^\circ\text{C}$ available
subject to special enquiry)

Climatic test category:

55/100/21 in accordance with IEC

Insulation resistance at $+20^\circ\text{C}$:

U_r	U_{test}	$C \leq 0.33 \mu\text{F}$	$0.33 \mu\text{F} < C \leq 10 \mu\text{F}$
50 VDC	10V	$\geq 5 \times 10^3 \text{ M}\Omega$ (mean value: $3 \times 10^4 \text{ M}\Omega$)	$\geq 1000 \text{ sec (M}\Omega \times \mu\text{F)}$ (mean value: 3000 sec)
63 VDC	50V	$\geq 1 \times 10^4 \text{ M}\Omega$ (mean value: $5 \times 10^4 \text{ M}\Omega$)	$\geq 1250 \text{ sec (M}\Omega \times \mu\text{F)}$ (mean value: 3000 sec)
$\geq 100 \text{ VDC}$	100V	$\geq 1.5 \times 10^4 \text{ M}\Omega$ (mean value: $1 \times 10^5 \text{ M}\Omega$)	$\geq 3000 \text{ sec (M}\Omega \times \mu\text{F)}$ (mean value: 6000 sec)

Measuring time: 1 min.

Dissipation factors at $+20^\circ\text{C}$: $\tan \delta$

at f	$C \leq 0.1 \mu\text{F}$	$0.1 \mu\text{F} < C \leq 1.0 \mu\text{F}$	$C > 1.0 \mu\text{F}$
1 kHz	$\leq 8 \times 10^{-3}$	$\leq 8 \times 10^{-3}$	$\leq 10 \times 10^{-3}$
10 kHz	$\leq 15 \times 10^{-3}$	$\leq 15 \times 10^{-3}$	–
100 kHz	$\leq 30 \times 10^{-3}$	–	–

Maximum pulse rise time: for pulses equal to the rated voltage

Capacitance μF	Pulse rise time V/ μsec max. operation/test					
	50 VDC	63 VDC	100 VDC	250 VDC	400 VDC	630 VDC
0.01 ... 0.022	–	35/350	35/350	50/500	80/800	110/1100
0.033 ... 0.068	–	20/200	25/250	50/500	80/800	90/900
0.1 ... 0.47	10/100	15/150	20/200	50/500	80/800	–
0.68 ... 1.0	8/80	12/120	15/150	25/250	–	–
1.5 ... 3.3	8/80	7.5/75	10/100	–	–	–
4.7	5/50	5/50	–	–	–	–
6.8	3/30	3/30	–	–	–	–
10	2.5/25	–	–	–	–	–

Mechanical Tests

Pull test on pins:

10 N in direction of pins according to
IEC 60068-2-21

Vibration:

6 hours at 10 ... 2000 Hz and 0.75 mm
displacement amplitude or 10 g in
accordance with IEC 60068-2-6

Low air density:

1 kPa = 10 mbar in accordance with
IEC 60068-2-13

Bump test:

4000 bumps at 390 m/sec² in
accordance with IEC 60068-2-29

Packing

Available taped and reeled.

Detailed taping information and graphs
at the end of the catalogue.

For further details and graphs please
refer to Technical Information.

Continuation

General Data


Capacitance	50 VDC/30 VAC*					63 VDC/40 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 μF						2.5	6.5	7.2	5	MKS2C021001A00_____
0.015 "						2.5	6.5	7.2	5	MKS2C021501A00_____
0.022 "						2.5	6.5	7.2	5	MKS2C022201A00_____
0.033 "						2.5	6.5	7.2	5	MKS2C023301A00_____
0.047 "						2.5	6.5	7.2	5	MKS2C024701A00_____
0.068 "						2.5	6.5	7.2	5	MKS2C026801A00_____
0.1 μF						2.5	6.5	7.2	5	MKS2C031001A00_____
0.15 "						2.5	6.5	7.2	5	MKS2C031501A00_____
0.22 "						3	7.5	7.2	5	MKS2C032201B00_____
0.33 "	2.5	6.5	7.2	5	MKS2B033301A00_____	3.5	8.5	7.2	5	MKS2C033301C00_____
0.47 "	3	7.5	7.2	5	MKS2B034701B00_____	3.5	8.5	7.2	5	MKS2C034701C00_____
0.68 "	3.5	8.5	7.2	5	MKS2B036801C00_____	4.5	9.5	7.2	5	MKS2C036801E00_____
1.0 μF	3.5	8.5	7.2	5	MKS2B041001C00_____	5	10	7.2	5	MKS2C041001F00_____
1.5 "	4.5	9.5	7.2	5	MKS2B041501E00_____	5.5	11.5	7.2	5	MKS2C041501H00_____
2.2 "	5	10	7.2	5	MKS2B042201F00_____	7.2	13	7.2	5	MKS2C042201K00_____
3.3 "	5.5	11.5	7.2	5	MKS2B043301H00_____	7.2	13	7.2	5	MKS2C043301K00_____
4.7 "	7.2	13	7.2	5	MKS2B044701K00_____	8.5	14	7.2	5	MKS2C044701M00_____
6.8 "	8.5	14	7.2	5	MKS2B046801M00_____	11	16	7.2	5	MKS2C046801N00_____
10 μF	11	16	7.2	5	MKS2B051001N00_____					

Capacitance	100 VDC/63 VAC*					250 VDC/160 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 μF	2.5	6.5	7.2	5	MKS2D021001A00_____	2.5	6.5	7.2	5	MKS2F021001A00_____
0.015 "	2.5	6.5	7.2	5	MKS2D021501A00_____	2.5	6.5	7.2	5	MKS2F021501A00_____
0.022 "	2.5	6.5	7.2	5	MKS2D022201A00_____	2.5	6.5	7.2	5	MKS2F022201A00_____
0.033 "	2.5	6.5	7.2	5	MKS2D023301A00_____	3.5	8.5	7.2	5	MKS2F023301C00_____
0.047 "	2.5	6.5	7.2	5	MKS2D024701A00_____	3.5	8.5	7.2	5	MKS2F024701C00_____
0.068 "	2.5	6.5	7.2	5	MKS2D026801A00_____	3.5	8.5	7.2	5	MKS2F026801C00_____
0.1 μF	2.5	6.5	7.2	5	MKS2D031001A00_____	4.5	9.5	7.2	5	MKS2F031001E00_____
0.15 "	3.5	8.5	7.2	5	MKS2D031501C00_____	5	10	7.2	5	MKS2F031501F00_____
0.22 "	3.5	8.5	7.2	5	MKS2D032201C00_____	5.5	11.5	7.2	5	MKS2F032201H00_____
0.33 "	4.5	9.5	7.2	5	MKS2D033301E00_____	7.2	13	7.2	5	MKS2F033301K00_____
0.47 "	4.5	9.5	7.2	5	MKS2D034701E00_____	8.5	14	7.2	5	MKS2F034701M00_____
0.68 "	5	10	7.2	5	MKS2D036801F00_____	11	16	7.2	5	MKS2F036801N00_____
1.0 μF	7.2	13	7.2	5	MKS2D041001K00_____					
1.5 "	8.5	14	7.2	5	MKS2D041501M00_____					
2.2 "	11	16	7.2	5	MKS2D042201N00_____					

* AC voltage: $f = 50 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

** PCM = Printed circuit module = pin spacing.

Dims. in mm.



Part number completion:

Tolerance: 20 % = M
10 % = K
5 % = J
Packing: bulk = S
Pin length: 6-2 = SD
Taped version see page 148.

Rights reserved to amend design data without prior notification.

Continuation page 35

Continuation

General Data

Capacitance	400 VDC/200 VAC*					630 VDC/220 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 μF	2.5	6.5	7.2	5	MKS2G021001A00_	5.5	11.5	7.2	5	MKS2J021001H00_
0.015 "	2.5	6.5	7.2	5	MKS2G021501A00_	7.2	13	7.2	5	MKS2J021501K00_
0.022 "	3.5	8.5	7.2	5	MKS2G022201C00_	7.2	13	7.2	5	MKS2J022201K00_
0.033 "	4.5	9.5	7.2	5	MKS2G023301E00_	7.2	13	7.2	5	MKS2J023301K00_
0.047 "	4.5	9.5	7.2	5	MKS2G024701E00_	8.5	14	7.2	5	MKS2J024701M00_
0.068 "	5.5	11.5	7.2	5	MKS2G026801H00_					
0.1 μF	7.2	13	7.2	5	MKS2G031001K00_					
0.15 "	8.5	14	7.2	5	MKS2G031501M00_					
0.22 "	11	16	7.2	5	MKS2G032201N00_					

* AC voltage: $f = 50 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

** PCM = Printed circuit module = pin spacing.

Dims. in mm.

The values of the WIMA MKM 2 and WIMA MKI 2 ranges according to the main catalogue 2009 are still available on request.

Part number completion:

Tolerance: 20 % = M


10 % = K

5 % = J

Packing: bulk = S

Pin length: 6-2 = SD






Taped version see page 148.



Impedance change with frequency (general guide).

Rights reserved to amend design data without prior notification.

Permissible AC voltage in relation to frequency at 10° C internal temperature rise (general guide).



Recommendation for Processing and Application of Through-Hole Capacitors

Soldering Process

A preheating of through-hole WIMA capacitors is allowed for temperatures $T_{\max} < 100^{\circ}\text{C}$. In practice a preheating duration of $t < 5 \text{ min.}$ has been proven to be best.


Single wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$
Immersion time: $t < 5 \text{ sec}$

Double wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$
Immersion time: $2 \times t < 3 \text{ sec}$

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



WIMA Quality and Environmental Philosophy

ISO 9001:2008 Certification

ISO 9001:2008 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2008 of our factories by the VDE inspectorate certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application of WPCS during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- AQL check

WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- | | |
|------------------------|------------|
| – Lead | – PBB/PBDE |
| – PCB | – Arsenic |
| – CFC | – Cadmium |
| – Hydrocarbon chloride | – Mercury |
| – Chromium 6+ | – etc. |

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- foamed polystyrene (Styropor®)
- adhesive tapes made of plastic
- metal clips

RoHS Compliance

According to the RoHS Directive 2011/65/EC certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei
konform RoHS 2011/65/EC
WIMA capacitors are lead free
in accordance with RoHS 2011/65/EC

Tape for lead-free WIMA capacitors

DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

Typical Dimensions for Taping Configuration




Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5*mm

*PCM 27.5 tapping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 tapping	PCM 5 tapping	PCM 7.5 tapping	PCM 10 tapping*	PCM 15 tapping*	PCM 22.5 tapping	PCM 27.5 tapping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W ₀	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W ₁	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W ₂	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D ₀	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P ₀	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to pin	P ₁	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P ₂	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H ₁	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 24.5 to 31.5	H+H _{component} < H ₁ 25.0 to 31.5	H+H _{component} < H ₁ 26.0 to 37.0	H+H _{component} < H ₁ 30.0 to 43.0	H+H _{component} < H ₁ 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 ^{+0.8} _{-0.2}	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2
Package (see also page 149)		ROLL/AMMO			AMMO			
		REEL ø 360 max. ø 30 ±1	B 52 ±2 58 ±2 } depending on comp. dimensions		REEL ø 360 max. ø 30 ±1	52 ±2 B 58 ±2 or 66 ±2	REEL ø 500 max. ø 25 ±1	54 ±2 B 60 ±2 68 ±2 } depending on PCM and component dimensions
Unit		see details page 150.						

Dims in mm.

* Diameter of pins see General Data.


* PCM 10 and PCM 15 can be crimped to PCM 7.5.

Position of components according to PCM 7.5 (sketch 11). P₀ = 12.7 or 15.0 is possible


Please clarify customer-specific deviations with the manufacturer.

Types of Tape Packaging of Capacitors for Automatic Radial Insertion


■ ROLL Packaging



■ AMMO Packaging



■ REEL Packaging



BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumerical Bar Code

Scanner decoding of

- WIMA supplier number
- Customer's P/O number
- Customer's part number
- WIMA confirmation number
- WIMA part number
- Lot number
- Date code
- Quantity

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- capacitance tolerance
- packing

as well as gross weight and customer's name are indicated in plain text.

WIMA Best Capacitors Made in Germany		Werk Unna	
Supplier-ID: 123456789	RoHS 2011/65/EC	Date Code: 08.10.10	
Purchase Order No. (P/O): Bestellung xyz		Quantity: 5.000	
Customer Part No.: KUNDETEILENUMMER		Customer No.: 0000100002	
WIMA Confirmation No.: 0001004063000100		Gross Weight [g]: 1870	
WIMA Part No.: MKS2C034701C00K88D			
Handling Unit:	MKS 2	QTY: 5.000	COO: DE
1000067326	MKS 2 0.47 μ F 63 VDC 3.5x8.5x7.2 RMS		
	Standard 10% Loss - Standard Drähte 6-2		
	Vorlage Debitur Inland	Week 03/2011	

BARCODE „Code 39“



Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm

PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
	H16.5	H18.5	ø 360	ø 500		340 × 340		490 × 370							
	W	H	L	Codes	S	N	O	F	I	H	J	A	C	B	D
2.5 mm	2.5	7	4.6	0B	5000			2500		—		2800		—	
	3	7.5	4.6	0C	5000	2200		2300		—		2300		—	
	3.8	8.5	4.6	0D	5000	2000		1800		—		1800		—	
	4.6	9	4.6	0E	5000	1500		1500		—		1500		—	
	5.5	10	4.6	0F	5000	1200		1200		—		1200		—	
5 mm	2.5	6.5	7.2	1A	5000	900		2500		—		2800		—	
	3	7.5	7.2	1B	5000	2200		2300		—		2300		—	
	3.5	8.5	7.2	1C	5000	2000		2000		—		2000		—	
	4.5	6	7.2	1D	6000	1600		1500		—		1500		—	
	4.5	9.5	7.2	1E	4000	1300		1500		—		1500		—	
	5	10	7.2	1F	3500	1300		1400		—		1400		—	
	5.5	7	7.2	1G	4000	1100		1200		—		1200		—	
	5.5	11.5	7.2	1H	2500	1000		1200		—		1200		—	
	6.5	8	7.2	1I	2500	1000		1000		—		1000		—	
	7.2	8.5	7.2	1J	2500	800		1000		—		1000		—	
	7.2	13	7.2	1K	2000	700		950		—		1000		—	
	8.5	10	7.2	1L	2000	700		800		—		800		—	
	8.5	14	7.2	1M	1500	800		800		—		800		—	
	11	16	7.2	1N	1000	600		600		—		400		—	
7.5 mm	2.5	7	10	2A	5000	—		2500		4400		2500		—	
	3	8.5	10	2B	5000	—		2200		4300		2300		4150	
	4	9	10	2C	4000	—		1700		3200		1700		3100	
	4.5	9.5	10.3	2D	3500	—		1500		2900		1400		2800	
	5	10.5	10.3	2E	3000	—		1300		2500		1300		—	
	5.7	12.5	10.3	2F	2000	—		1000		2200		1100		—	
	7.2	12.5	10.3	2G	1500	—		900		1800		1000		—	
10 mm	3	9	13	3A	3000	—		1100		2200		—		1900	
	4	8.5	13.5	FA	3000	—		900		1600		—		1450	
	4	9	13	3C	3000	—		900		1600		—		1450	
	4	9.5	13	3D	3000	—		900		1600		—		1400	
	5	10	13.5	FB	2000	—		700		1300		—		1200	
	5	11	13	3F	3000	—		700		1300		—		1200	
	6	12	13	3G	2400	—		550		1100		—		1000	
	6	12.5	13	3H	2400	—		550		1100		—		1000	
15 mm	8	12	13	3I	2000	—		400		800		—		740	
	5	11	18	4B	2400	—		600		1200		—		1150	
	5	13	19	FC	1000	—		600		1200		—		1200	
	6	12.5	18	4C	2000	—		500		1000		—		1000	
	6	14	19	FD	1000	—		500		1000		—		1000	
	7	14	18	4D	1600	—		450		900		—		850	
	7	15	19	FE	1000	—		450		900		—		850	
	8	15	18	4F	1200	—		400		800		—		740	
	8	17	19	FF	500	—		400		800		—		740	
	9	14	18	4H	1200	—		350		700		—		650	
	9	16	18	4J	900	—		350		700		—		650	
	10	18	19	FG	500	—		300		650		—		590	
22.5 mm	11	14	18	4M	1000	—		300		600		—		540	
	5	14	26.5	5A	1200	—		—		800		—		770	
	6	15	26.5	5B	1000	—		—		700		—		640	
	7	16.5	26.5	5D	760	—		—		600		—		550	
	8	20	28	FH	500	—		—		500		—		480	
	8.5	18.5	26.5	5F	500	—		—		480		—		450	
	10	22	28	FI	540*	—		—		420		—		380	
	10.5	19	26.5	5G	680*	—		—		400		—		360	
	10.5	20.5	26.5	5H	680*	—		—		400		—		360	
	11	21	26.5	5I	680*	—		—		380		—		350	
12	24	28	FJ	450*	—		—		350		—		310		

* TPS (Tray-Packing-System). Plate versions may have different packing units.
Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.

Packing Quantities for Capacitors with Radial Pins in PCM 27.5 mm to 52.5 mm

PCM	Size				bulk	ROLL		pcs. per packing unit				AMMO			
								REEL							
	W	H	L	Codes		H16.5	H18.5	ø 360	ø 500	340 × 340	490 × 370	H16.5	H18.5	H16.5	H18.5
					S	N	O	F	I	H	J	A	C	B	D
27.5 mm	9	19	31.5	6A	640*	–	–	–	–	460/340*	–	–	–	420	–
	11	21	31.5	6B	544*	–	–	–	–	380/280*	–	–	–	350	–
	13	24	31.5	6D	448*	–	–	–	–	300	–	–	–	290	–
	13	25	33	FK	336*	–	–	–	–	–	–	–	–	–	–
	15	26	31.5	6F	384*	–	–	–	–	270	–	–	–	250	–
	15	26	33	FL	288*	–	–	–	–	–	–	–	–	–	–
	17	29	31.5	6G	176*	–	–	–	–	–	–	–	–	–	–
	17	34.5	31.5	6I	176*	–	–	–	–	–	–	–	–	–	–
	19	30	31.5	6L	50*	–	–	–	–	–	–	–	–	–	–
	20	32	33	FM	216*	–	–	–	–	–	–	–	–	–	–
	20	39.5	31.5	6J	144*	–	–	–	–	–	–	–	–	–	–
37.5 mm	9	19	41.5	7A	480*	–	–	–	–	–	–	–	–	–	–
	11	22	41.5	7B	408*	–	–	–	–	–	–	–	–	–	–
	13	24	41.5	7C	252*	–	–	–	–	–	–	–	–	–	–
	15	26	41.5	7D	144*	–	–	–	–	–	–	–	–	–	–
	17	29	41.5	7E	132*	–	–	–	–	–	–	–	–	–	–
	19	32	41.5	7F	108*	–	–	–	–	–	–	–	–	–	–
	20	39.5	41.5	7G	108*	–	–	–	–	–	–	–	–	–	–
	24	45.5	41.5	7H	84*	–	–	–	–	–	–	–	–	–	–
	31	46	41.5	7I	72*	–	–	–	–	–	–	–	–	–	–
	35	50	41.5	7J	35*	–	–	–	–	–	–	–	–	–	–
	40	55	41.5	7K	28*	–	–	–	–	–	–	–	–	–	–
48.5 mm	19	31	56	8D	50*	–	–	–	–	–	–	–	–	–	–
	23	34	56	8E	72*	–	–	–	–	–	–	–	–	–	–
	27	37.5	56	8H	60*	–	–	–	–	–	–	–	–	–	–
	33	48	56	8J	48*	–	–	–	–	–	–	–	–	–	–
	37	54	56	8L	25*	–	–	–	–	–	–	–	–	–	–
52.5 mm	35	50	57	9F	25*	–	–	–	–	–	–	–	–	–	–
	45	55	57	9H	20*	–	–	–	–	–	–	–	–	–	–
	45	65	57	9J	20*	–	–	–	–	–	–	–	–	–	–

* for 2-inch transport pitches.

* TPS (Tray-Packing-System). Plate versions may have different packing units.
Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.



WIMA Part Number System

A WIMA part number consists of 18 digits and is composed as follows:

Field 1 - 4: Type description
 Field 5 - 6: Rated voltage
 Field 7 - 10: Capacitance
 Field 11 - 12: Size and PCM
 Field 13 - 14: Version code (e.g. Snubber versions)
 Field 15: Capacitance tolerance
 Field 16: Packing
 Field 17 - 18: Lead length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
M	K	S	2	C	0	2	1	0	0	1	A	0	0	M	S	S	D
MKS 2				63 VDC		0.01 μF				2.5×6.5×7.2		-		20%	bulk	6 -2	
Type description:				Rated voltage:		Capacitance:				Size:				Tolerance:			
SMD-PET = SMDT				2.5 VDC = A1		22 pF = 0022				4.8×3.3×3 Size 1812 = KA				20% = M			
SMD-PPS = SMDI				4 VDC = A2		47 pF = 0047				4.8×3.3×4 Size 1812 = KB				10% = K			
FKP 02 = FKP0				14 VDC = A3		100 pF = 0100				5.7×5.1×3.5 Size 2220 = QA				5% = J			
MKS 02 = MKS0				28 VDC = A4		150 pF = 0150				5.7×5.1×4.5 Size 2220 = QB				2.5% = H			
FKS 2 = FKS2				40 VDC = A5		220 pF = 0220				7.2×6.1×3 Size 2824 = TA				1% = E			
FKP 2 = FKP2				5 VDC = A6		330 pF = 0330				7.2×6.1×5 Size 2824 = TB				...			
MKS 2 = MKS2				50 VDC = B0		470 pF = 0470				10.2×7.6×5 Size 4030 = VA				Packing:			
MKP 2 = MKP2				63 VDC = C0		680 pF = 0680				12.7×10.2×6 Size 5040 = XA							
FKS 3 = FKS3				100 VDC = D0		1000 pF = 1100				15.3×13.7×7 Size 6054 = YA				AMMO H16.5 340×340 = A			
FKP 3 = FKP3				160 VDC = E0		1500 pF = 1150				2.5×7×4.6 PCM2.5 = 0B				AMMO H16.5 490×370 = B			
MKS 4 = MKS4				250 VDC = F0		2200 pF = 1220				3×7.5×4.6 PCM2.5 = 0C				AMMO H18.5 340×340 = C			
MKP 4 = MKP4				400 VDC = G0		3300 pF = 1330				2.5×6.5×7.2 PCM5 = 1A				AMMO H18.5 490×370 = D			
MKP 10 = MKP1				450 VDC = H0		4700 pF = 1470				3×7.5×7.2 PCM5 = 1B				REEL H16.5 360 = F			
FKP 4 = FKP4				600 VDC = I0		6800 pF = 1680				2.5×7×10 PCM7.5 = 2A				REEL H16.5 500 = H			
FKP 1 = FKP1				630 VDC = J0		0.01 μF = 2100				3×8.5×10 PCM7.5 = 2B				REEL H18.5 360 = I			
MKP-X2 = MKX2				700 VDC = K0		0.022 μF = 2220				3×9×13 PCM 10 = 3A				REEL H18.5 500 = J			
MKP-X2 R = MKXR				800 VDC = L0		0.047 μF = 2470				4×9×13 PCM 10 = 3C				ROLL H16.5 = N			
MKP-Y2 = MKY2				850 VDC = M0		0.1 μF = 3100				5×11×18 PCM 15 = 4B				ROLL H18.5 = O			
MP 3-X2 = MPX2				900 VDC = N0		0.22 μF = 3220				6×12.5×18 PCM 15 = 4C				BLISTER W12 180 = P			
MP 3-X1 = MPX1				1000 VDC = O1		0.47 μF = 3470				5×14×26.5 PCM22.5 = 5A				BLISTER W12 330 = Q			
MP 3-Y2 = MPY2				1100 VDC = P0		1 μF = 4100				6×15×26.5 PCM22.5 = 5B				BLISTER W16 330 = R			
MP 3R-Y2 = MPRY				1200 VDC = Q0		2.2 μF = 4220				9×19×31.5 PCM27.5 = 6A				BLISTER W24 330 = T			
Snubber MKP = SNMP				1250 VDC = R0		4.7 μF = 4470				11×21×31.5 PCM27.5 = 6B				Bulk/TPS Standard = S			
Snubber FKP = SNFP				1500 VDC = S0		10 μF = 5100				9×19×41.5 PCM37.5 = 7A				...			
GTO MKP = GTOM				1600 VDC = T0		22 μF = 5220				11×22×41.5 PCM37.5 = 7B				Lead length (untaped)			
DC-LINK MKP 3 = DCP3				2000 VDC = U0		47 μF = 5470				94×49×182 DCH_ = H0							
DC-LINK MKP 4 = DCP4				2500 VDC = V0		100 μF = 6100				94×77×182 DCH_ = H1				3.5 ±0.5 = C9			
DC-LINK MKP 4S = DCPS				3000 VDC = W0		220 μF = 6220				...				6 -2 = SD			
DC-LINK MKP 5 = DCP5				4000 VDC = X0		1 F = A010				Version code:				16 ±1 = P1			
DC-LINK MKP 6 = DCP6				6000 VDC = Y0		2.5 F = A025											
DC-LINK HC = DCH_				250 VAC = 0W		50 F = A500				Standard = 00				...			
DC-LINK HY = DCHY				275 VAC = 1W		100 F = B100				Version A1 = 1A							
SuperCap C = SCSC				300 VAC = 2W		110 F = B110				Version A1.1.1 = 1B							
SuperCap MC = MC_				400 VAC = 3W		600 F = B600				Version A2 = 2A							
SuperCap C60 = SCSC				440 VAC = 4W		1200 F = C120				...							
SuperCap R = SCSR				500 VAC = 5W		...											
SuperCap MR = MRPP				...													

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.