

DK/EK-Series




The DK/EK-Series toggle switches are quick-make and quick-break type switches, suitable for high amperage AC/DC motor control. These heavy-duty switches are supplied with plated brass toggles and bushings in a phenolic base.

Specifications

- Certifications*: UL, CSA
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Phenolic
- Actuator Material: Brass/Nickel Plate
- Bezel Material: Brass/Nickel Plate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



SERIES/CIRCUIT	RATING	TERMINATION	TOGGLE STYLE	TOGGLE BUSHING LENGTH	SUFFIX NO.
DK	28	4	-	73	
DA ON-OFF SINGLE POLE	28 8A 250V	4 SCREW TERMINAL	BALL	.500 .343	32
DK ON-OFF DOUBLE POLE	16A 125V		BAT	.687 .343	72
	1HP 125-250V			.687 .465	73

SERIES/CIRCUIT	RATING	TERMINATION	TOGGLE STYLE	TOGGLE BUSHING LENGTH	SUFFIX NO.
EK	20	4	-	73	
EA ON-OFF SINGLE POLE	20 10A 250V	4 SCREW TERMINAL	BALL	.500 .343	32
EK ON-OFF DOUBLE POLE	20A 125V		BAT	.687 .343	72
	1 1/2HP 125-250V			.687 .465	73

NOTES:
Shading indicates standard configurations.