

Miniature Intermediate Power Relay HY



- 7A switching capabilities (2C, 3C)
- 1.5kV dielectric strength (between coil and contacts)
- Various terminals, test button available
- Different sockets available
- 2 to 4 pole configurations
- Outline dimensions: 28 x 21.5 x 36.0 mm

Options and Ordering Codes

HY	4	1	PN	24DC
Contact arrangement				Coil voltage
2 Pole CO	2			
3 Pole CO	3			
4 Pole CO	4			
Mounting				
Plug-in		1		
PCB		2		
			PN	Mechanical indicator /test latch LED
			XN	Mechanical indicator
			PX	Test latch and flag
			XX	No indication or test



Contact Data

Contact arrangement	2C, 3C	4C
Contact resistance	100m Ω (at 1A 6VDC)	
Contact material	Silver Alloy	
Contact Rating	7A 250VAC / 30VDC	5A 250VAC / 30VDC
Max. switching voltage	250VAC / 30VDC	
Max. switching current	7A	5A
Max. switching power	210W 1750VA	150W 1250VA
Mechanical Life	2x10 ⁷ OPS	
Electrical Life	1x10 ⁵ OPS	

Characteristics

Initial Insulation Resistance	1000M Ω (at 500VAC)	
Dielectric Strength	Between coil & contacts	1500VAC 1min.
	Between open contacts	1000VAC 1min.
	Between contact sets	1500VAC 1min.
Operate time (at nomi. Volt)	25 ms max.	
Release time (at nomi. Volt)	25 ms max.	
Shock resistance	Functional	98m/s ²
	Destructive	980m/s ²
Vibration resistance	10 to 55Hz 1mm DA	
Ambient temperature	-40°C to +70°C	
Humidity	95% RH, 40°C	
Termination	PCB, Plug-in	
Unit Weight	Approx 37g	
Construction	Dust protected	

Coil Data

at 23°C

Nominal Voltage VDC	Pick-up Voltage VDC	Drop-out Voltage VDC	Max. Allowable Voltage VDC	Coil Resistance Ω
5	4	0.5	5.5	27.5 (1 $\pm$ 10%)
6	4.8	0.6	6.6	40 (1 $\pm$ 10%)
12	9.6	1.2	13.2	160 (1 $\pm$ 10%)
24	19.2	2.4	26.4	650 (1 $\pm$ 10%)
48	38.4	4.8	52.8	2600 (1 $\pm$ 15%)
110	88	11	121	11000 (1 $\pm$ 15%)

Nominal Voltage VAC	Pick-up Voltage VAC	Drop-out Voltage VAC	Max. Allowable Voltage VAC	Coil Resistance Ω
6	4.8	1.8	6.6	11.5 (1 $\pm$ 10%)
12	9.6	3.6	13.2	46 (1 $\pm$ 10%)
24	19.2	7.2	26.4	184 (1 $\pm$ 10%)
48	38.4	14.4	52.8	735 (1 $\pm$ 10%)
120	96	36	132	4550 (1 $\pm$ 15%)
240	176	66	264	14400 (1 $\pm$ 15%)

Coil

Coil power	DC type	0.9W to 1.1W
	AC type	1.2VA to 1.8VA

Safety Approval Ratings


UL/CUL	2PCO	7A 250VAC / 30VDC
	3PCO	
	4PCO	5A 250VAC / 30VDC

Miniature Intermediate Power Relay HY




Outline dimensions (mm)

2 and 3 Poles




4 Poles




PCB Layout


2 Pole C0



3 Pole C0



4 Pole C0




Miniature Intermediate Power Relay HY




Wiring diagram


2 Pole CO




3 Pole CO




4 Pole CO




2 Pole CO
(With LED)



3 Pole CO
(With LED)




4 Pole CO
(With LED)



Characteristics Curve

Maximum Switching Power
(2, 3 pole CO)



Maximum Switching Power
(4 pole CO)

