




Copyright FCI



FCIconnect.com



NOTES

- 1) REGULATORY APPROVALS:
* RECOGNIZED TO U.S. AND CANADIAN REQUIREMENTS UNDER THE COMPONENT RECOGNITION PROGRAM OF Underwriters Laboratories Inc.
* CERTIFIED BY THE Canadian Standard Association.
- 2) INSIDE CAVITIES ARE CONFORMED WITH FCC RULES PART 68, SUBPART 'F'.
- 3) THESE DIMENSIONS APPLY OVER ENTIRE PROTRUDING HEIGHT OF THE TERMINAL.
- 4) HOUSING MATERIAL: HIGH TEMP. THERMOPLASTIC , COLOR - BLACK, CLEAR OR GRAY, UL94V-0.
- 5) CONTACT MATERIAL: PHOSPHOR BRONZE
MATING AREA PLATING: Au OVER Ni
SOLDER AREA PLATING: Sn/Pb OVER Ni.
- 6) THIS PRODUCT COVERED BY PRODUCT SPEC. GS-12-083.
- 7) MATES WITH FCC PART 68 PLUGS
A0640149 (P0647991) - BLACK
A0640150 (P0706452) - GREY
A0640151 (P0746434) - CLEAR
PRESS-FIT (STANDARD) RETENTION PEGS
- 8) THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MIN THICK CIRCUIT BOARD. SLIGHT DEFORMATION MAY OCCUR FOR THE DIAMOND PEGS AT 260-265° C WHICH WILL NOT AFFECT THE FUNCTION OF THE PRODUCT.
- 9) PACKAGING OF LEAD FREE PRODUCTS MEETS LABELING AND PACKAGING SPECIFICATION GS-14-920.
- 10) LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

mat'l. code				surface		tolerance		projection	product family	MODJACK
ltr	ecn no	dr	date	ISO 1302		ISO 406	ISO 1101			
A	V20906	JRV	2002-05-10	tolerances unless otherwise specified		X±0.13				
B	I05-0255	HVN	2005-11-28	angles	linear	XX±0.13				
C	I06-0123	HVN	2006-07-26	0°±1°			XXX±0.08			
				dr	J.R.VOLSTROF	2002-05-09				
				engr	J.R.VOLSTROF	2002-05-09				
				chr	HIRAN.V.N	2006-07-26				
				appd	HIRAN.V.N	2006-07-26				
sheet	revision	C								
index	sheet	1								

