

98426-YXX-XX-XXXLF

PLATING

- G : 0.76 GXT
2μm MIN MATTE TIN ON TAIL
- S : 0.38 GXT
2μm MIN MATTE TIN ON TAIL
- F : GOLD FLASH /2μm MIN TIN ON TAIL
- T : 2μm MIN FULL TIN
1.27μm NICKEL MIN UNDERPLATING

LEAD FREE AND RoHS
COMPATIBLE, NOTE 6
BODY HEIGHT : XXX
- MIN= 104 (10.4MM)
- MAX= 290 (29.0MM)

PACKAGING, NOTE 3

NO. OF POS PER ROW, 03 TO 25

NOTES:

- MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC
UL 94V-0, COLOR CREAM (SHROUD)
AND BLACK(UNSHROUDED)
- MATERIAL TERMINAL: COPPER ALLOY
- PACKAGING
- = STANDARD PACKAGING IN BLIBOX
S = CUSTOM PACKAGING IN TUBE
ONLY FOR PIN STYLE 17, NOTE 7
- SHROUDED RETENTION FORCE 3N MIN PER POSITION
- 0.3 MAX PROTRUSION FOR -03 TO 11
- RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2μm MINIMUM MATTE TIN OVER 1.27μm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:





- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004

6 - THIS PRODUCT IS NOT INTENDED TO BE USED THROUGH REFLOW PROCESS

7 - CUSTOM SPECIAL WITH "OAL" 11.8mm AND BODY HEIGHT 8.8mm

PIN STYLE	OAL
01	12.8
02	13.5
03	14.1
04	15.6
05	16.3
06	17.1
07	18.3
08	19.1
09	20.3
10	21.1
11	22.3
12	23.3
13	26.0
14	28.0
15	30.0
16	32.0
17	NOTE 7



RECOMMENDED HOLE PATTERN

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 101		projection 		product family MINITEK			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title				
A	F09-0227	JCO	09.12.07	angles	linear	X.X ±0.3			SHR STACKING HEADER MINITEK				
B	F10-0067	JCO	10.06.29			X.XX ±0.13							
C	B-18972	LMU	14.10.01			X.XXX ±0.05							
D	B-19190	LMU	14.10.24	dr	L.MULIN		09.04.02		dwg no		sheet 1 of 1	size	
E	B-20291	BVE	15.02.19	engr	J.COMPAGNON		09.04.02		98426		A3		
				chr	JCO		09.12.07						
				appd	J.CO		09.12.07			type		CUSTOMER Drawing	
sheet index		revision sheet											