





used for: DIN 41617

Polzahl No. of pos.	A ± 0.2	B ± 0.1	C ± 0.1	Art.-Nr. Part-No.
13	45.8	40	12x2.5=30	102E10049X
21	65.8	60	20x2.5=50	102E10069X
31	90.8	85	30x2.5=75	102E10089X



Leiterplattenbohrbild P.C.B.-HOLE DRILLINGS



NOTES:

- INSULATOR: PC GF UL 94 V-0, GREY
- CONTACTS: COPPER ALLOY
PLATING: HARD SILVER PLATED
500 MATING CYCLES
- CONNECTOR IS PART MARKED: **PART-NO CONEC ABC**

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL
CUSTOMER APPROVAL DATE:
NAME: TITLE:
COMPANY NAME:
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

1 x b	Ä3723	18.08.2010	K.H.
rev.	description	date	name
a			

tolerance	dim. in mm
2008	date
drawn	19.08.
appd.	19.08.
norm	DIN 41617
d-old	

scale: 2:1
material: SEE NOTES
title: FEMALE CONNECTOR 13pos. - 31pos. with straight solder pins
dwg no: AutoCAD 2006
10K2A002
part no: SEE TABLE