





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

**SMALL PRECISION
LIMIT SWITCH**

CATALOG LISTING


914CE16-12



- NOTES
1 - ZINC HOUSING FINISHED WITH GRAY PAINT
2 - SWITCH WILL ACTUATE IN BOTH DIRECTIONS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 3 IN. LB MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — 10 IN. OZ MAX			
PRETRAVEL — — — — — 30° MAX	L109 5A 1/10HP 125 OR <u>250</u> VAC	ONE PLACE (.0)	±.030
DIFFERENTIAL TRAVEL — — — 3° MAX		TWO PLACE (.00)	±.015
OVERTRAVEL — — — — — 40° MIN		THREE PLACE (.000)	±.005
		ANGLES	±
	 	WEIGHT	

914CE16-12

M

DRAWING
NUMBER

3

ISSUE

REPLACES

RELEASE NO. PR-7861

CHECK

CHECK

REVISIONS
A OBS
C052341
S M A
5 NOV 82
B REINST
PR17749
M A M
20 OCT 89

DDM/CAD

DRAWN

CHECK

MAM

20 OCT 89