

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-05-016219	23NOV05	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Au PLATING
- 4

Ni PLATING
- 5

THIS ITEM MUST BE WHITE
- 6



HAND TOOL : 9-1478240-0
- 7

DIE SET : 9-1478242-0
- 8

ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 4 GHz
NOMINAL IMPEDANCE: 50 Ohm
INSULATION RESISTANCE: 5000 MOhm
WORKING VOLTAGE: 500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max
CONTACT RESISTANCE:
CENTRE CONTACT: 1.50 mOhm Max
OUTER CONTACT: 0.20 mOhm Max
VSWR @ 4GHz: 1.30:1 Max
INSERTION LOSS dB @ x 3 GHz: 0.20 Max
- 9

MECHANICAL CHARACTERISTICS
COUPLING NUT RETENTION FORCE: N/A
CABLE RETENTION FORCE: 170N Min
MOUNT NUT RECOMMENDED TORQUE: 4N
DURABILITY: 500 Cycles Min
- 10

ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65 to +165 DegC



		1	1	BRASS	3	CONTACT	8
		1	1	BRASS	4	FERRULE	7
		1	1	BRASS	4	CHASSIS	6
		1	1	BRASS	4	BODY	5
		1	1	PTFE		INSULATION	4
		1	1	SILICON RUBBER	5	GASKET	3
		1	1	STEEL	4	LOCKWASHER	2
		1	1	BRASS	4	HEX NUT	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		3	3				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	23NOV05	tyco Tyco Electronics Corporation Electronics Bideford EX39 4HE		
		CHK	S.PARLOW	23NOV05			
DIMENSIONS: mm		APVD	F.WHEELER-KING	23NOV05	NAME BNC BULKHEAD JACK REAR MOUNT CRIMP 50 OHM RG58C/U, 141A/U, URM43, 76, Belden 9907, KX15		
		PRODUCT SPEC	108-3435				
MATERIAL SEE TABLE		APPLICATION SPEC	411-3247		SIZE	CAGE CODE	DRAWING NO
		WEIGHT	-		A3	00779	C-1337433
		CUSTOMER DRAWING			SCALE	SHEET	REV
					NTS	1 OF 1	C