



Notes:

1. Electrical Specifications:
 - Meets EIA/TIA-568-B.2 Cat.5e Specification
 - Contact Resistance: 20mOhm max.
 - Insulation Resistance: 500MOhm min. @ 100 VDC
 - Current Rating: 1.2A max. at 25° C
 - Working Voltage: 100 VDC
 - DWV: 1000 VDC/60s Contact to Contact, 1500 VDC/60s Contact to Metal Shell
 - Operating Temperature: -40° C to +85° C
2. Material and Finish:
 - Thread Coupling Ring and Housing: Polyester (Black) or Metallized ABS, UL94 V-0 (Nickel Plated)
 - Cable Fitting: PA (Black), UL94 V-0 or Brass, Nickel Plated
 - Cable Fitting Rubber Ring: NBR, Color: Black
 - Interfacial Seal: Silicon, Color: Black
 - RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
 - RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
 - RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
3. RJ45 Plug accepts both Stranded and Solid Cables with Outer Diameter of 4.83mm to 6.73mm
4. Plastic Version Cable Fitting accepts Cable Outer Diameter Range of 4mm to 8mm
5. Metal Version Cable Gland accepts Cable Outer Diameter Range of 4.5mm to 8mm

Directive 2002/95/EC RoHS Compliant

Description	Part Number
Plastic Version with Interfacial Seal	17-100464
Plastic Version without Interfacial Seal	17-120004
Metallized Plastic Version with Interfacial Seal	17-100474
Metallized Plastic Version without Interfacial Seal	17-120014

Customer:				Tolerance Unless otherwise specified		Autodesk Inventor	Scale: 1.5:1	Dim. in mm
Name	Title	Approval Date		0 PLC	± 0.50		Material: See Notes	
e	2 x e	Jun/23/2014	Vincent Ke	1 PLC	± 0.38	Draw.	Dec. 03	Vincent Ke
d	1 x d	Jul/20/2012	Vincent ke	2 PLC	± 0.25	Appd.	Dec. 03	J. Chaudry
c	1 x c	Jul/06/2011	Vincent ke	3 PLC	± 0.10			
b		May/25/2009	Vincent Ke	ANGLES	± 3°			
a	original							
Rev.	Changes	Date	Name					

CONEC®

Title: RJ45 Cable Strain Relief Kit
with shielded Cat. 5e RJ45 Plug
with or without Interfacial Seal

Drawing No.: 39K1A365

Part No.: SEE P/N ABOVE

DIN
A3
Sheet
1/1