



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F4	REVISED PER ECO-18-001979	07FEB2018	J.Z	D.Z

- 1 WIRE RANGE: 0.13–0.32mm² (26–22 AWG).
- 2 INSULATION RANGE: 1.20–1.75 DIA.
- 3

FINISH: 0.76μm MINIMUM GOLD IN LOCALIZED GOLD PLATE AREA OVER 1.27μm MINIMUM NICKEL
- 4

FINISH: 2.54μm MINIMUM PRE-TIN IN LOCALIZED TIN PLATE AREA.
- 5

FINISH: 2.54μm MINIMUM PRE-TIN ALL OVER.



GOLD 3 4	PHOS. BRZ.	794957-4
PRE-TIN 5	PHOS. BRZ.	794957-3
GOLD 3 4	BRASS	794957-2
PRE-TIN 5	BRASS	794957-1
FINISH:	MATERIAL:	PART NO.

SECTION A-A

SECTION B-B

SECTION C-C



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HAMM 06-SEP-2001	TE Connectivity Ltd.			
DIMENSIONS: mm [INCHES]		CHK D. COLEY 07-SEP-2001				
		APVD D. COLEY 07-SEP-2001	NAME			
		PRODUCT SPEC	TERMINAL PIN VAL-U-LOK(TM)			
MATERIAL		FINISH	WEIGHT 0.000000	SIZE A2	CAGE CODE 00779	DRAWING NO C=794957
			CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV F4