





5	6	7	8	
REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3-730251			
C	LEN-7B0145	2007/11/15	Gao Ling	Modify Panel Thickness





Detail A
Scale 2:1



Gasket (2) → (1) Connector



5/8"-27UNS-



Note:

- * @DImportant Dimension.
- * Waterproof Rate: IP67
- * Housing: Nylon+GF
- * Screw Nut: Nylon+GF
- * Gasket: EPDM
- * Connector: Mini USB Dip Type
- * Wafer: 1.27mm Pitch 90°
- * Use with waterproof cap or dust cap
For Panel Thickness Max: 1.3mm
- * Use without waterproof cap or dust cap
For Panel Thickness Max: 2.5mm

UNIT:mm		TITLE	Mini USB Panel 90°			
TOLERANCE		SCALE	Free	SHEET	1	OF 1
.X	±0.25	REV.	C	SIZE	A4	(QC) :Inspection Item
.XX	±0.1					
.XXX	±0.05					
ANGLES	±1°					

LTW

ITEM NO <u>LTWNUB-20PMFR-SC7001</u>	DRAWN BY <u>Gao Ling</u>	DATE <u>2007/11/15</u>	HOR/REV BY <u></u>
DWG NO <u>LTWNUB-20PMFR-SC7001</u>	CHECKED BY <u>Jill</u>	DATE <u>2007/11/19</u>	
CUSTOMER	APPROVED BY <u>Lion</u>	DATE <u>2007/11/20</u>	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[LTWNUB-20PMFR-SC7001](#)