

**Relay compatible
with sockets:**

S9-M, S9-L, S9-P, S9-PO




Table 1 Electrical Life, ops. x 10⁶






Table 2 Max. DC Load



Dimensions - mm



FASTON .102

C9-A41



General purpose

Four pole, change-over contacts

5 A 250 V AC1

5 A 30 V DC1 0.2 A 110 V DC1

Contacts

Materials:	Standard, code 1	AgNi + 0.2μAu
	Optional, code 2	AgNi + 10μAu
Max. switching current		5 A
Max. peak inrush current (2.5 ms)		15 A
Max. switching voltage		250 V
Max. AC load (Table 1)		1250 KVA
Max. DC load (Table 2)		

Coils (Ohms ±10% @ 20°C)

Pull-in voltage	≤0.8 x U _n
Drop-out voltage	≥0.1 x U _n
Nominal coil power	1.2 VA (AC)/1 W (DC)

VAC	Ω	mA	VDC	Ω	mA
24	174	50	12	148	85
48	686	25	24	594	43
115	4K3	10.4	48	2K3	21
230	18K6	5.2	110	11K4	11

Insulation

Dielectric strength (1 minute):	Open contacts	1,000 V
	Between adjacent poles	2 KV
	Between contacts and coil	2.5 KV
Isolation resistance at 500 V		≥1 GΩ
Isolation, IEC 61810-5:		2.5 KV

Specifications

Operate time + bounce time	10 ms
Release time + bounce time	6 ms
Ambient temperature	-40°C (no ice) to +70°C
Mechanical life ops.	10 Mill. AC, 20 Mill. DC relays
Electrical life at nominal load	≥100,000 ops.
Operating frequency at nominal load	1,200/hour
Protection degree	IP 40/RT1
Weight avg.	43 g

Standard Types

AC 50 Hz, (60 Hz): 24, 48, 72, 115, (120), 230, (240)

X = LED (standard)

C9-A41X.....VAC

DC 12, 24, 48, 72, 110

X = LED, no polarity (standard)

C9-A41X.....VDC

Free-wheeling diode

C9-A41DXVDC

Polarity and free-wheeling diodes

C9-A41FX.....VDC

AC/DC bridge rectifier (24, 48 or 60 V)

C9-A41BXVDC