


MATERIALS	
BODY	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
INSULATOR	PTFE



SPECIFICATIONS

ELECTRICAL.....(@25°C AMBIENT)
 FREQUENCY RANGE.....500 MHz – 2 GHz
 ATTENUATION ACURACY..... ±1.0 dB MAX.
 IMPEDANCE..... 50 OHMS
 VSWR:.....1.35:1 MAX.
 VOLTAGE RATING.....100 VOLTS MAX.
 DC CURRENT.....2 AMPS MAX.
 RF POWER (AVG).....2 WATTS MAX.
 OPERATING TEMP. RANGE.....-55°C TO ±125°C



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE
PE7063-6

DES. 50 OHM TNC DC BIAS PASSING
 ATTENUATOR, 6 dB

REV. A **FSCM NO. 53919**

CAD FILE 030409

SCALE N/A

SIZE A 147

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.