

Search Results

- Evaluate
- FAQ's

- Press Releases

-PANDUIT Keye ..

- White Papers

- PDF-Managing Phy ..
- Design a Solution
- Part Drawings

- DWG-Keyed LC Opt ..

- DXF-Keyed LC Opt ..

- PDF-Keyed LC Opt ..
- How to Buy
- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove)    Search Tips 

 Text Search: 'FLCDMC5FDB'

Your search criteria matched only one product, shown below

FLCDMC5FDB



- Exceed TIA/EIA-568-B.3 requirements
- Insertion loss: 0.3dB average (multimode and singlemode)
- Return loss: >26dB (10Gig™ multimode), >20dB (multimode), >50dB (singlemode)
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete Keyed LC System that includes Opti-Core® Patch Cords and Pigtails, OptiCam® Pre-Polished Cam Connectors, Opticom® Fiber Adapter Panels (FAPs) and Mini-Com® Adapter Modules
- Translucent housing assembly is laser marked to identify fiber stub fiber type (9µm, 62.5, 50 or 50X)
- Spring-loaded "Senior" rear pivot latch LC connector
- Quick installation; provide field termination in less than half the time of field polish connectors
- Patented re-termination capability provides yield rates approaching 100%

- Factory pre-polished fiber endface eliminates time-consuming field polishing to reduce installation costs, labor, scrap, and the number of tools required
- Cam activated fiber and buffer clamp mechanisms provide superior fiber and buffer retention – less sensitivity to fiber tensile loading
- No separate clamps, tools, or steps are required to secure both the fiber and the buffer
- OptiCam® Termination Tool simplifies tooling and termination, and virtually eliminates operator error by providing visual indication of proper termination after the cam step has been completed
- Cable retention boot assemblies consistently provide higher than industry standard cable retention
- Non-optical disconnect maintains data transmission under tensile loads for jacketed cable
- Fiber cable size: accept 900µm tight-buffered fiber with included boot(s); accepts 1.6mm – 2.0mm and 3.0mm jacketed cable with available OptiCam® Cable Retention Boot Assemblies (ten per package)
- For 250µm coated fiber termination, use 250 micron fiber build-up tube kit or fan-out kits
- Ferrule type: 1.25mm zirconia ceramic (highest durability for repeated matings)
- Use OptiCam® Termination Kit (FCAMKIT)

*Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.*

|                                |                                                                                                                                |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| ▪ Part Number                  | FLCDMC5FDB                                                                                                                     |
| ▪ RoHS Compliancy Status       | RoHS directive is not applicable                                                                                               |
| ▪ Note                         | Intended for use in fixed installations which are outside the scope of RoHS                                                    |
| ▪ Part Description             | LC (keyed F – dark blue) OptiCam® 50/125µm Multimode Duplex Fiber Optic Connector for 900µm tight-buffered fiber installation. |
| ▪ Product Type                 | Keyed LC Duplex Connectors                                                                                                     |
| ▪ Fiber Compatibility          | 50/125µm                                                                                                                       |
| ▪ Fiber Cable Size             | 900µm                                                                                                                          |
| ▪ Fiber Cable Type             | Tight-buffered                                                                                                                 |
| ▪ Fiber Type                   | Multimode                                                                                                                      |
| ▪ Termination Style            | Pre-Polished Cam                                                                                                               |
| ▪ Boot Color                   | Black                                                                                                                          |
| ▪ CE Compliant                 | No                                                                                                                             |
| ▪ Ferrule Type                 | Zirconia Ceramic                                                                                                               |
| ▪ Key Type and Color           | Keyed F – Dark Blue                                                                                                            |
| ▪ Pricing Description          | LC Opticam (Keyed F-Dark Blue) 50/125µm Multimode Duplex Connector                                                             |
| ▪ Min. Order UOM               | PC                                                                                                                             |
| ▪ Min. Order Qty.              | 1                                                                                                                              |
| ▪ BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>                                                                                                 |
| ▪ Add to Favorite Product List | <input type="checkbox"/>                                                                                                       |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.