

H G F E D C B A

NOTES

Materiel and finish:

Housings:

Shells: steel, bright tin plated

Insulators: glass filled thermoplastic UL94V0

Contacts:




brass, gold plated over nickel

on mating end, bright tin plated over nickel

on termination end

Operating temperature range

+55°C +125°C



Dimensions are in millimeters

Shell size	Number of contacts	A ^{+0.76 0}	B ^{+0.25 0}	C ^{±0.12}	F ^{+0.51 0}	G ^{+0.25 0}	H ^{+0.51 0}	L ^{+0.22}	K _{max}
E	09	30.43	16.21	24.99	10.64	6.05	19.02	0.80	1.50
A	15	38.76	24.54	33.32	10.64	6.05	27.25	0.80	1.50
B	25	52.65	38.25	47.04	10.64	6.05	41.02	0.80	1.50
C	37	68.94	54.71	63.50	10.64	6.05	57.45	0.80	1.50

Part number	D*P**S600T		
b	07/08/00	change the dimension K change the business number	--
ISS	DATE	Latest modification by : MASSON	MOD N°
Designed by: JARRY date: 10/10/91			Type of drawing: CLIENT
TITLE : SOCKETS CONNECTORS D SUBMINIATURE WITH WIRE WRAP			SHEET 1/1
SCALE: 1.5	FRAMATOME CONNECTORS FRANCE Rue Louis Breguet - BP 05 72024 LE MANS Cedex Tel. 33 (16) 43.84.08.43		This document is the property of FRAMATOME CONNECTORS FRANCE It must not be reproduced or communicated without permission in writing from the owners
FORMAT A3	SOURIAU DRG N° C-8637-508		PROJECT M94D001